

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-28-4023

Status:

Active

Overview:

KK® Interconnection System

Description:

2.54mm Pitch KK® Header, Breakaway, Vertical, 2 Circuits, 0.38µm Gold (Au)
Selective Plating, Mating Pin Length 6.09mm

Documents:

3D Model

Drawing (PDF)

Product Specification PS-10-07 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

42375

Application

Board-to-Board, Signal, Wire-to-Board

Overview

KK® Interconnection System

Product Name

KK®

Physical

Breakaway

Yes

Circuits (Loaded)

2

Circuits (maximum)

2

Color - Resin

Black

Durability (mating cycles max)

100

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.18mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Plating min - Mating

0.381µm

Plating min - Termination

2.540µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

No

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

0°C to +75°C

Termination Interface: Style

Through Hole

Electrical



image - Reference onlySeries

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
42375Series

Mates With
KK® Crimp Housing [2695](#) , [6471](#) , [7880](#) ,
KK® PC Board Connector [4455](#)

Current - Maximum per Contact	4A
Voltage - Maximum	250V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	260
Material Info	
Old Part Number	42375-0037
UPC	800753589377
Reference - Drawing Numbers	
Product Specification	PS-10-07
Sales Drawing	SD-42375-001

This document was generated on 06/13/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION