

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [71439-2864](#)
Status: **Active**
Overview: [PMC](#)
Description: 1.00mm Pitch Mezzanine IEEE 1386 Receptacle, Surface Mount, Dual Row, Vertical Stacking, Embossed Tape on Reel, 0.76µm Gold (Au), 64 Circuits Pick and Place Cap

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-71436-9999 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Receptacles
Series [71439](#)
Application Board-to-Board, Signal
Comments Plugs
Overview [PMC](#)
Product Name Mezzanine

Physical


Circuits (Loaded) 64
Circuits (maximum) 64
Color - Resin Natural
Flammability 94V-0
Glow-Wire Compliant No
Lock to Mating Part Yes
Mated Height 13.00mm
Material - Metal Phosphor Bronze
Material - Plating Mating Gold
Material - Plating Termination Tin
Material - Resin High Temperature Thermoplastic
Number of Rows 2
Orientation Vertical
PCB Locator Yes
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 1.00mm
Plating min - Mating 0.762µm
Plating min - Termination 1.905µm
Polarized to PCB No
Robotic Placement Pick and Place Cap
Surface Mount Compatible (SMC) N/A
Temperature Range - Operating -55°C to +85°C
Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 1A
Voltage - Maximum 100V

Solder Process Data

Duration at Max. Process Temperature (seconds) 40
Lead-free Process Capability Reflow Capable (SMT only)
Max. Cycles at Max. Process Temperature 3



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[71439Series](#)

Mates With
[714362](#) for Stack Height 13.00mm

Process Temperature max. C	260
Material Info	
UPC	800754350105
Reference - Drawing Numbers	
Product Specification	PS-71436-9999
Sales Drawing	SDA-71439-2***

This document was generated on 06/19/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION