

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [52808-2370](#)
Status: **Active**
Overview: FFC-FPC (SMT)
Description: 1.00mm Pitch FFC/FPC Connector, SMT, Vertical, Non-ZIF Receptacle, 23 Circuits, Lead-Free

Documents:

[3D Model](#)
[Drawing \(PDF\)](#)
[Product Specification PS-52808-004 \(PDF\)](#)
[Packaging Specification SPK-52808-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family FFC/FPC Connectors
Series [52808](#)
Overview [FFC-FPC \(SMT\)](#)
Product Name N/A

Physical

Circuits (Loaded) 23
Circuits (maximum) 23
Color - Resin Natural
Contact Position N/A
Durability (mating cycles max) 10
Entry Angle Vertical
Mated Height 5.05mm
Material - Metal Phosphor Bronze
Material - Plating Mating Nickel
Material - Plating Termination Tin-Bismuth
Material - Resin High Temperature Thermoplastic
Number of Rows 1
Orientation Vertical
PCB Locator No
PCB Retention None
Packaging Type Embossed Tape on Reel
Pitch - Mating Interface 1.00mm
Pitch - Termination Interface 1.00mm
Polarized to PCB No
Stackable No
Surface Mount Compatible (SMC) Yes
Temperature Range - Operating -20°C to +80°C
Termination Interface: Style Surface Mount
Wire/Cable Type FFC/FPC


Electrical

Current - Maximum per Contact 0.5A
Voltage - Maximum 125V AC (RMS)/DC

Material Info

Reference - Drawing Numbers

[Packaging Specification](#) SPK-52808-001
[Product Specification](#) PS-52808-004, RPS-52808-039, RPS-52808-044, RPS-52808-045, RPS-52808-047, RPS-52808-048, RPS-52808-049
[Sales Drawing](#) SD-52808-027, SD-52808-028



EU RoHS

**ELV and RoHS
Compliant**
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series
[52808Series](#)

This document was generated on 04/23/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION