

Rev	Change order	Change: A = Added W = Was D = Deleted	Date	Sign
1	1022154000	A 4x 4101-3490	050214	TGW



För icke direkt toleranssatta mått gäller toleransklass
 General tolerances if not otherwise stated

NOM DIM MM		TOL CLASS		
From	To	A	B	C
(1)	6	±0.05	±0.1	±0.2
(6)	30	±0.1	±0.2	±0.5
(30)	100	±0.15	±0.3	±0.8
(100)	300	±0.2	±0.5	±1.2
(300)	1000	±0.3	±0.8	±2

Hål / Holes H13

Skarpa kanter brutna där ej annat anges.
 No sharp edges unless otherwise specified.

Övriga generella toleranser enligt ritning 4100-4644.
 Additional general tolerances in accordance with drawing 4100-4644.



Packas enligt förpackningsritning 4101-3770
 Packed according to drawing 4101-3770

4101-3495
 A
 B

4300-3165/AAA	4101-3769B POSITION A	4101-3583	4101-3585	4101-3036	4101-3490
ART.NR.VAR.	A	B	C	D	E

Material		Behandling/Treatment		Status	
Konstr./Design		Ritad/Drawn		Date/Date	
TGW	TGW	2005-02-14	⊕	Skala/Scale	1:1
pressmaster®			Kontr./Checked	Godk./Approved	Anne/Blank
Verktygssats Mobile tool			SE	NE	
Automotive			Vikt/Weight,gram		Art grp
REG NR F413607			84003165		012
			Ritn nr./Drawing no		REV
			43003165		001

Denna ritning är Pressmaster AB:s egendom. Skyddad av gällande lag.
 This drawing is the property of Pressmaster AB. Protected in accordance with prevailing law.