

### 1. Product and Company Identification

ting by ting ackard Company over Street CA 94304-1185 ates e 650-857-1501 ackard health effects line within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 D09 with skin and eyes may result in irritation. tital hazards are presumed to be due to exposure to the components. <i>mediol</i>
ting ackard Company over Street CA 94304-1185 ates e 650-857-1501 ackard health effects line within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 009
ting ackard Company over Street CA 94304-1185 ates e 650-857-1501 ackard health effects line within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 009
A grad Company over Street CA 94304-1185 ates e 650-857-1501 ackard health effects line within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 009
A grad Company over Street CA 94304-1185 ates e 650-857-1501 ackard health effects line within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 009
over Street CA 94304-1185 ates e 650-857-1501 ackard health effects line within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 009
within the US) 1-800-457-4209 -503-494-7199 mer Care Line within the US) 1-800-474-6836 -208-323-2551 009 rith skin and eyes may result in irritation.
rith skin and eyes may result in irritation. Itial hazards are presumed to be due to exposure to the components.
ntial hazards are presumed to be due to exposure to the components.
ntial hazards are presumed to be due to exposure to the components.
ntial hazards are presumed to be due to exposure to the components.
ntial hazards are presumed to be due to exposure to the components.
nediol
ith skin may result in irritation.
<i>diol</i> ith skin may result in irritation.
ate # 2 ith skin may result in irritation.
ed naphthalenesulfonate salt # 13 ith skin may result in irritation.
<i>nediol</i> ith eyes may result in irritation.
<i>diol</i> ith eyes may result in irritation.
ate # 2 ith eyes may result in irritation.
ed naphthalenesulfonate salt # 13 ith eyes may result in irritation.
<i>diol</i> may result in respiratory irritation.
ate # 2 may result in respiratory irritation.
ed naphthalenesulfonate salt # 13 may result in respiratory irritation.
tra



Potential health effects	
Routes of exposure	Potential routes of overexposure to this product are skin and eye contact
	Inhalation of vapor and ingestion are not expected to be significant routes of exposure for this product under normal use conditions.
	Complete toxicity data are not available for this specific formulation
Chronic health effects	None known.
Carcinogenicity	None of the components present in this formulation at concentrations equal to or greater than 0.1% are listed by EU, MAK, IARC, NTP or OSHA.

### 3. Composition / Information on Ingredients

Component/substance	CAS number	% by weight
- Water 1,5-pentanediol Aliphatic diol Metal nitrate # 2 Substituted naphthalenesulfonate	7732-18-5 111-29-5 Proprietary Proprietary salt # 13 Proprietary	< 80 < 20 < 20 < 10 < 10
Composition comments	This ink supply contains an aqueous ink form This product has been evaluated using criteria Communication Standard).	
. First Aid Measures		
First aid procedures		
Eye contact		amounts of clean, warm water (low pressure) five ved. If irritation persists get medical attention.
Skin contact	Wash affected areas thoroughly with mild soa attention.	ap and water. If irritation persists get medical
Inhalation	Move to fresh air. If symptoms persist, get me	edical attention.
Ingestion	If ingestion of a large amount does occur, see	ek medical attention.
5. Fire Fighting Measures		
Flash point and method	> 200 °F (> 93.3 °C); Pensky-Martens Closed	l Cup
Hazardous combustion products	Refer to section 10.	
Flammable properties	None known.	
Extinguishing media		
Suitable extinguishing media	CO2, water, dry chemical, or foam	
Unsuitable extinguishing media	None known.	
Unusual fire and explosion hazard	None known.	
Special firefighting procedures	None established.	
6. Accidental Release Measures		
Personal precautions	Wear appropriate personal protective equipm	ent.
Environmental precautions	Do not let product enter drains. Do not flush i	nto surface water or sanitary sewer system.
Methods for containment	Dike the spilled material, where this is possibl sand or diatomaceous earth, commercial sort	le. Absorb with inert absorbent such as dry clay pents, or recover using pumps.
Methods for cleaning up	Soak up with inert absorbent material.	



Soak up with inert absorbent material. Slowly vacuum or sweep the material into a bag or other sealed container. Dispose of in compliance with federal, state, and local regulations. See also section 13 Disposal considerations.

### 7. Handling and Storage

Other information

Handling	Avoid contact with skin, eyes and clothing.
Storage	Keep out of the reach of children. Keep away from excessive heat or cold.

#### 8. Exposure Controls / Personal Protection

Exposure guidelines	Exposure limits have not been established for this product.
Personal protective equipment	
General	Use personal protective equipment to minimize exposure to skin and eye.
General hygeine considerations	Handle in accordance with good industrial hygiene and safety practice.

#### 9. Physical & Chemical Properties

Color	Yellow
Odor threshold	Not available.
Physical state	Not available.
Form	liquid
рН	7.2 - 7.4
Melting point	Not available.
Freezing point	Not available.
Boiling point	Not determined
Flash point	> 200 °F (> 93.3 °C); Pensky-Martens Closed Cup
Evaporation rate	Not determined
Flammability	Not available.
Flammability limits in air, upper, % by volume	Not available.
Flammability limits in air, lower, % by volume	Not determined
Vapor pressure	Not determined
Vapor density	> 1 (air = 1.0)
Specific gravity	1 - 1.2
Relative density	Not available.
Solubility (water)	Soluble in water
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not determined
Decomposition temperature	Not available.
VOC	< 3 %
Viscosity	> 2 cp

#### 10. Chemical Stability & Reactivity Information

Chemical stability	Stable under recommended storage conditions.
Incompatible materials	Incompatible with strong bases and oxidizing agents.
Hazardous decomposition products	Upon decomposition, this product may yield gaseous nitrogen oxides, carbon monoxide, carbon dioxide and/or low molecular weight hydrocarbons.



inve	n t	
Possibility reactions	y of hazardous	Will not occur.
11. Toxicolog	gical Information	
Toxicolog	ical information	Refer to Section 3 for potential health effects and Section 4 for first aid measures.
12. Ecologica	al Information	
Aquatic to	oxicity	LC50/96h/Fathead minnows =434 mg/L Static acute toxicity (trout), survival (100 mg/L) = 100% Static acute toxicity (trout), survival (10 mg/L) = 100%
Persistend	ce and degradability	Not available.
13. Disposal	Considerations	
Disposal i	nstructions	Dispose of in compliance with federal, state, and local regulations. HP's Planet Partners (trademark) supplies recycling program enables simple, convenient recycling of HP original inkjet and LaserJet supplies. For more information and to determine if this service is available in your location, please visit http://www.hp.com/recycle.
14. Transpor	t Information	
ΙΑΤΑ		
Proper sh	ipping name	Not applicable
Hazard cla	ass	Not applicable
UN numbe	ər	None
Packing g	roup	N/A
Packaging	g exceptions	None
Packaging	g non bulk	None
Labels rec	quired	None
General		Not a regulated article under United States DOT, IATA, ADR, IMDG, or RID.
15. Regulator	ry Information	
US federa	l regulations	US TSCA 12(b): Does not contain listed chemicals.
CERCLA ( None	Superfund) reportable	e quantity
Superfund	d Amendments and Re	eauthorization Act of 1986 (SARA)
Hazar	d categories	Immediate Hazard - No Delayed Hazard - No Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No
	on 302 extremely dous substance	No
Sectio chemi	on 311 hazardous ical	No
Internation	nal regulations	All chemical substances in this HP product have been notified or are exempt from notification under chemical substances notification laws in the following countries: US (TSCA), EU (EINECS/ELINCS), Switzerland, Canada (DSL/NDSL), Australia, Japan, Philippines, South Korea, New Zealand, and China.
16. Other Info	ormation	
HMIS® rat	ings	Health: 1 Flammability: 1 Physical hazard: 0



NFPA ratings	Health: 1 Flammability: 1 Instability: 0
Issue date	Jan 27 2009 11:52AM
Revision	4
Replaces sheet dated	Aug 6 2008 1:15PM
Disclaimer	This Safety Data Sheet document is provided without charge to customers of Hewlett-Packard Company. Data is the most current known to Hewlett-Packard Company at the time of preparation of this document and is believed to be accurate. It should not be construed as guaranteeing specific properties of the products as described or suitability for a particular application. This document was prepared to the requirements of the jurisdiction specified in

Section 1 above and may not meet regulatory requirements in other countries.

#### Explanation of abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS	Chemical Abstracts Service
CERCLA	Comprehensive Environmental Response Compensation and Liability Act
CFR	Code of Federal Regulations
COC	Cleveland Open Cup
DOT	Department of Transportation
EPCRA	Emergency Planning and Community Right-to-Know Act (aka SARA)
IARC	International Agency for Research on Cancer
NIOSH	National Institute for Occupational Safety and Health
NTP	National Toxicology Program
OSHA	Occupational Safety and Health Administration
PEL	Permissible Exposure Limit
RCRA	Resource Conservation and Recovery Act
REC	Recommended
REL	Recommended Exposure Limit
SARA	Superfund Amendments and Reauthorization Act of 1986
STEL	Short-Term Exposure Limit
TCLP	Toxicity Characteristics Leaching Procedure
TLV	Threshold Limit Value
TSCA	Toxic Substances Control Act
VOC	Volatile Organic Compounds
Manufacturer information	Hewlett-Packard Company 1000 NE Circle Boulevard Corvallis, OR 97330-4239 US (Direct) 1-503-494-7199 (Toll-free within the US) 1-800-457-4209