

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 1/9



1. Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier: KODAK COMBO COLOR AND BLACK INK CARTRIDGE

Product code: 8898033

Synonyms: None.

1.2. Relevant identified uses of the substance or mixture and uses advised against:

1.2.1. Identified uses: ink or inkjet chemical

1.3. Details of the supplier of the safety data sheet: KODAK LIMITED, Hemel One, Boundary Way, Hemel Hempstead, HP2 7YU, Great Britain

For further information about this product, telephone 0870-2430270 or email kes@kodak.com.

1.4. Emergency telephone number:

IN EMERGENCY, telephone: 0870-2430270. Available during office hours only.

2. Hazards identification

2.1. Classification of the substance or mixture

Classification according to EU Directives 67/548/EEC or 1999/45/EC:

Not a hazardous substance or preparation according to EC-directives 67/548/EEC or 1999/45/EC

2.2. Label elements:

The data below reflects current legislative requirements whereas the product in your possession may carry a different version of the label depending on the date of manufacture.

Labelling according to 67/548/EEC or 1999/45/EC:

Not a hazardous substance or preparation according to EC-directives 67/548/EEC or 1999/45/EC.*

*Safety data sheet available for professional user on request.

2.3. Other hazards

None known.

3. Composition/information on ingredients

Weight percent	Component	CAS-No. EC No. REACH Reg. No.	Classification according to 1272/2008/EC	Classification according to 67/548/EEC
10 - 15	glycerol	56-81-5 200-289-5 not available	**	**
1 - 5	Ethanesulfonic acid, 2-(methyl((9Z)-1-oxo-9-octadecenyl)amino)-, potassium salt			

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 2/9

	130976-49-7 not available not available	**	Xi, N; R41, R51/53 **
0.1 - < 1	1-methoxypropan-2-ol 107-98-2 203-539-1 not available	Flam. Liq. 3 H226 STOT SE 3 H336 *	R10, R67 *

Full text of R- and H-phrases: see Section 16.

* **Substance classification as listed in Annex VI to Regulation (EC) No 1272/2008**

** **Substance not listed in Annex VI to Regulation (EC) No 1272/2008**

4. First aid measures

4.1. Description of first aid measures

4.1.1. Inhalation: If symptomatic, move to fresh air. Get medical attention if symptoms occur.

4.1.2. Skin: Immediately flush with plenty of water for at least 15 minutes and wash using soap. Get medical attention if symptoms occur.

4.1.3. Eyes: In case of contact with eyes, flush immediately with plenty of water and seek medical attention.

4.1.4. Ingestion: Do NOT induce vomiting. Give victim a glass of water. Get medical attention immediately. Never give anything by mouth to an unconscious person.

4.2. Most important symptoms and effects, both acute and delayed: No information available.

4.3. Indication of immediate medical attention and special treatment needed: No information available.

5. Fire-fighting measures

5.1. Extinguishing Media: Use appropriate agent for adjacent fire.

5.2. Special hazards arising from the substance or mixture

5.2.1. Hazardous Combustion Products: Fire or excessive heat may produce hazardous decomposition products., (see also Stability and Reactivity section).

5.2.2. Unusual Fire and Explosion Hazards: None.

5.3. Advice for firefighters: Wear self-contained breathing apparatus and protective clothing.

6. Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures: Refer to protective measures listed in sections 7 and 8.

6.2. Environmental precautions: Contaminated absorbent should be disposed of in accordance with local regulations.

6.3. Methods and materials for containment and cleaning up: Prevent spillage from entering drains. Absorb spill with vermiculite or other inert absorbant material such as sand or earth, then place in a suitable container for proper disposal. Clean surface thoroughly with water to remove residual contamination.

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 3/9

6.4. Reference to other sections: See Section 8 for recommendations on the use of personal protective equipment.

7. Handling and storage

7.1. Precautions for safe handling

7.1.1. Personal precautions: Avoid prolonged or repeated breathing of mist or vapour. Avoid contact with eyes, skin, and clothing. Use with adequate ventilation. Wash thoroughly after handling.

7.1.2. Prevention of Fire and Explosion: The physical-chemical properties of this material have not been fully investigated. Use only with adequate ventilation. Keep from contact with oxidizing materials.

7.1.3. Ventilation: Match ventilation rates to conditions of use so as not to exceed any applicable exposure limits (see Section 8).

7.2. Conditions for safe storage, including any incompatibilities: Cool conditions (5 - 30°C). Keep container tightly closed. Keep away from incompatible substances (see Incompatibility section.)

7.3. Specific end uses: No information available.

8. Exposure controls/personal protection

8.1. Control parameters

8.1.1. Occupational exposure controls

Chemical Name	Regulatory List	Value Type	Value
Glycerol	EH40	time weighted average	10 mg/m ³ <i>Form of exposure: mist</i>
		Short term exposure limit	30 mg/m ³ <i>Form of exposure: mist</i> <i>Remarks: calculated</i>
Glycerol	HSA	time weighted average	10 mg/m ³

8.2. Exposure controls

8.2.1. Appropriate engineering controls: For use other than intended use (such as in the event of a large spill), proper ventilation may be required.

8.2.2. Individual protection measures, such as personal protective equipment

Eye protection: None should be needed under normal conditions of use.

Hand protection:

Respiratory protection: None should be needed under normal conditions of use.

General health and safety measures: Safety shower, eye wash, washing facilities as appropriate to condition of use.

8.2.3. Environmental exposure controls: No information available.

9. Physical and chemical properties

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 4/9

9.1. Information on basic physical and chemical properties

Appearance

Physical state: liquid

Colour: magenta

Odour: no data available

Odour Threshold: no data available

pH: no data available

Melting point/freezing point: no data available

Initial boiling point and boiling range: no data available

Flash point: > 93.33 °C(> 200.0 °F) (estimated)

Evaporation rate: no data available

Flammability (Solid; gas) : no data available

Upper explosion limit: no data available

Lower explosion limit: no data available

Vapour pressure: no data available

Vapour density: no data available

Specific gravity: no data available

Volatile fraction by weight: 85 - 90 %

Water solubility: soluble

Partition coefficient: n-octanol/water: no data available

Autoignition temperature: no data available

Decomposition temperature: no data available

Viscosity: no data available

Explosive properties: no data available

Oxidizing properties: no data available

10. Stability and reactivity

10.1. Reactivity: no data available

10.2. Chemical stability: Stable under normal conditions.

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 5/9

10.3. Possibility of hazardous reactions: Hazardous polymerisation does not occur.

10.4. Conditions to avoid: no data available

10.5. Incompatible materials: Strong oxidizing agents.

10.6. Hazardous decomposition products: Carbon oxides

11. Toxicological information

Effects of Exposure

Toxicokinetics, metabolism and distribution

no data available

Acute toxicity

no data available

Corrosivity and irritation

no data available

Sensitisation

no data available

CMR effects

Germ cell mutagenicity

No information available.

Carcinogenicity

No information available.

Reproductive toxicity

No information available.

Specific target organ toxicity - single exposure

No information available.

Specific target organ toxicity - repeated exposure

No information available.

Aspiration hazard

No information available.

Information on likely routes of exposure

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 6/9

Inhalation: Expected to be a low hazard for recommended handling.

Eyes: No specific hazard known. May cause transient irritation.

Skin: Expected to be a low hazard for recommended handling.

Ingestion: Expected to be a low ingestion hazard.

Data for glycerol (CAS 56-81-5):

Acute Toxicity Data:

Oral LD50 (rat): 17,000 - 27,200 mg/kg

- Dermal LD50 (rat): > 21,900 mg/kg
- Skin irritation: Mild skin irritation
- Eye irritation: mild

Data for Ethanesulfonic acid, 2-(methyl((9Z)-1-oxo-9-octadecenyl)amino)-, potassium salt (CAS 130976-49-7):

Acute Toxicity Data:

Oral LD50 (female rat): > 2,000 mg/kg OECD Test Guideline 401

- Oral LD50 (male rat): > 2,000 mg/kg OECD Test Guideline 401
- Skin irritation: slight
- Eye irritation (unwashed eyes): strong
- Eye irritation (washed eyes): strong
- Skin Sensitization: negative

Mutagenicity/Genotoxicity Data:

Salmonella-E.coli/Mammalian-Microsome Reverse Mutation Assay with a Confirmatory Assay (TA98, TA100, TA1535, TA1537, E. coli WP2uvrA (pKM101)): negative (in presence and absence of activation)

12. Ecological information

The following properties are ESTIMATED from the components of the preparations.

12.1. Toxicity

Toxicity to fish (LC50): > 100 mg/l

Toxicity to daphnia (EC50): > 100 mg/l

12.2. Persistence and degradability

Persistence and degradability: Not readily biodegradable.

12.3. Bioaccumulative potential

no data available

12.4. Mobility in soil

No information available.

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 7/9

12.5. Results of PBT and vPvB assessment

No information available.

12.6. Other adverse effects

No information available.

13. Disposal considerations

13.1. Waste treatment methods

Dispose according to the local regulations or guidelines that apply to the category of waste. Ensure the use of properly authorised waste management companies.

14. Transport information

Not regulated for all modes of transportation.

For more transportation information, go to: www.kodak.com/go/ship.

15. Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Notification status

Regulatory List	Notification status
TSCA	Not all listed
DSL	Not all listed
NDSL	Listed
EINECS	Not all listed
ELINCS	None listed
NLP	Listed
AICS	Not all listed
IECS	Not all listed
ENCS	Not all listed
ECI	Not all listed
NZIoC	Not all listed
PICCS	Not all listed
TSCA 12(b)	Listed

"Not all listed" indicates one or more component is either not on the public Inventory or is subject to exemption requirements. If additional information is needed contact Kodak.

15.2. Chemical safety assessment

Chemical safety assessment has not been performed.

Safety Data Sheet

Approval/Revision date: 12.01.2012
Print Date: 16.05.2012
000000034622/Version: 1.2
Page: 8/9

16. Other information

16.1. Indication of changes

Minor changes may be present due to component or regulatory data updates.

16.2. Key or legend to abbreviations and acronyms used in the safety data sheet

ADR = European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS = Australian Inventory of Chemical Substances; CAS = Chemical Abstracts Service; CLP = Classification, Labelling, and Packaging; DSL = Canada Domestic Substances List; EC = European Commission; EC50 = Effective Concentration 50%; ECI = Korea Existing Chemicals list; EINECS = European Inventory of Existing Commercial chemical Substances; ELINCS = European List of Notified Chemical Substances; ENCS = Japan Existing and New Chemical Substances; GHS = Globally Harmonized System of Classification and Labelling of Chemicals; IARC = International Agency for Research on Cancer; IATA = International Air Transport Association; IC50 = Inhibitory Concentration 50%; IECS = China Inventory of Existing Chemical Substances; IMDG = International Maritime Dangerous Goods; LC50 = Lethal Concentration 50%; LD50 = Lethal Dose 50%; mg/Kg = milligrams per Kilogram; mg/L = milligrams per Liter; mg/m³ = milligrams per Cubic Meter; NDSL = Canada Non-Domestic Substances List; NLP = Europe No Longer Polymers; NZIoC = New Zealand Inventory of Chemicals; PBT = Persistent, Bioaccumulative and Toxic substances; PICCS = Philippines Inventory of Chemicals and Chemical Substances; ppm = parts per million; REACH= Registration, Evaluation and Authorization of Chemicals; RID = European Agreement concerning the International Carriage of Dangerous Goods by Rail; TSCA = Toxic Substances Control Act; vPvB = very Persistent, very Bioaccumulative substances

16.3. Key literature references and sources for data

Available upon request.

16.4. Methods used for classification of mixture according to Regulation (EC) No 1272/2008

The determination of classifications is derived via expert judgment and/or weight of evidence.

16.5. Relevant R- and H-phrases

H226	Flammable liquid and vapour.
H336	May cause drowsiness or dizziness.
R10	Flammable.
R41	Risk of serious damage to eyes.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.

16.6. Training advice

Review Safety Data Sheet before using product.

16.7. Further information

Users should consider these data only as a supplement to other information gathered by them and must make independent determinations of suitability and completeness of information from all sources to assure proper use and disposal of these materials and the safety and health of employees and customers and the protection of the environment. The information relating to the working solution is for guidance purposes only, and is based on correct mixing and use of the product according to instructions.

Safety Data Sheet

Approval/Revision date: 12.01.2012

Print Date: 16.05.2012

000000034622/Version: 1.2

Page: 9/9
