

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [62201-8602](#)  
**Status:** **Active**  
**Description:** Press-In Tool for Vertical Header 11-Row, 6-Column

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)


**General**

Product Family	Application Tooling
Series	<a href="#">T3002</a>
Comments	See Tooling Specification (PDF) Above, Press-In Tool
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Product Name	N/A
Survey	<a href="http://www.molex.com//review/apptool_survey.html">www.molex.com//review/apptool_survey.html</a>
Tool Type	Handtool

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents ATS-622018602, TM-622018699, TM-622022099



*image - Reference only*

**EU RoHS** **China RoHS**

**Compliance Status**

**Not Reviewed**

**REACH SVHC**

**Not Reviewed**

**Low-Halogen Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[T3002Series](#)

**Use With**

GbX I-Trac™ Backplane Signal Module,  
[75705 Series](#)

<b>Application Tooling</b>	<b>FAQ</b>
<b>Description</b>	<b>Product #</b>

1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Open Ends, 11 Rows, 6 Columns, 132 Circuits, Mating Pin Length 4.70mm	0757051603
1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Dual End Wall, 11 Rows, 6 Columns, 132 Circuits, Mating	0757051623

Pin Length 4.70mm,  
Orientation Key B  
1.85mm by 3.70mm 0757057603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm  
1.85mm by 3.70mm 0757050603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Open Ends, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm  
1.85mm by 3.70mm 0757050604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Open Ends, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm  
1.85mm by 3.70mm 0757050605  
Pitch, GbX I-  
Trac™ Vertical  
Header Module,  
Unguided, Open  
Ends, 11 Rows,  
6 Columns, 132  
Circuits, Staggered  
Mating Pin Length  
4.70mm & 5.70mm  
1.85mm by 3.70mm 0757050615  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Left End Wall, 11  
Rows, 6 Columns,  
132 Circuits,  
Staggered Mating  
Pin Length 4.70mm  
& 5.70mm  
1.85mm by 3.70mm 0757050635  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Right End Wall, 11  
Rows, 6 Columns,  
132 Circuits,  
Staggered Mating  
Pin Length 4.70mm  
& 5.70mm  
1.85mm by 3.70mm 0757051624  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Dual End Walls, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm,  
Orientation Key B

1.85mm by 3.70mm 0757051634  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Right End Wall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm

1.85mm by 3.70mm 0757052604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Open, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm

1.85mm by 3.70mm 0757054602  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Mating Pin  
Length 3.90mm

1.85mm by 3.70mm 0757054605  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Staggered  
Mating Pin Length  
4.70mm & 5.70mm

1.85mm by 3.70mm 0757055602  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Mating Pin  
Length 3.90mm

1.85mm by 3.70mm 0757056604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm

1.85mm by 3.70mm 0757057604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm

1.85mm by 3.70mm 0757059603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm

1.85mm by 3.70mm 0757050623  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Dual End Walls, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm

1.85mm by 3.70mm 0757050624  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Dual End Walls, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm

1.85mm by 3.70mm 0757050625  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Dual End Walls, 11  
Rows, 6 Columns,  
132 Circuits,  
Staggered Mating  
Pin Length 4.70mm  
& 5.70mm

1.85mm by 3.70mm 0757051602  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Open Ends, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 3.90mm

1.85mm by 3.70mm 0757051604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Open Ends, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm

1.85mm by 3.70mm 0757051614  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Left End Wall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm,  
Orientation Key A

1.85mm by 3.70mm 0757051615  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Left End Wall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm  
& 4.70mm Staggered  
Pins

1.85mm by 3.70mm 0757051625  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,

Dual End Walls, 11  
Rows, 6 Columns,  
132 Circuits,  
Staggered Mating  
Pin Length 4.70mm  
& 5.70mm,  
1.85mm by 3.70mm 0757051633  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Unguided,  
Right End Wall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm  
1.85mm by 3.70mm 0757052603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Open, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm  
1.85mm by 3.70mm 0757052605  
Pitch, GbX I-  
Trac™ Vertical  
Header Module,  
Left Guide, Right  
Open, 11 Rows,  
6 Columns, 132  
Circuits, Staggered  
Mating Pin Length  
4.70mm & 5.70mm  
1.85mm by 3.70mm 0757053602  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Open, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 3.90mm  
1.85mm by 3.70mm 0757053603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Open, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm  
1.85mm by 3.70mm 0757053604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Open, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm  
1.85mm by 3.70mm 0757054603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Mating Pin  
Length 4.70mm

1.85mm by 3.70mm 0757054604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Mating Pin  
Length 5.70mm

1.85mm by 3.70mm 0757055603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Mating Pin  
Length 4.70mm

1.85mm by 3.70mm 0757055604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Mating Pin  
Length 5.70mm

1.85mm by 3.70mm 0757055605  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Open, 11 Rows,  
6 Columns, 132  
Circuits, Staggered  
Mating Pin Length  
4.70mm & 5.70mm

1.85mm by 3.70mm 0757056603  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 4.70mm

1.85mm by 3.70mm 0757056605  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Endwall, 11  
Rows, 6 Columns,  
132 Circuits,  
Staggered Mating  
Pin Length 4.70mm  
& 5.70mm

1.85mm by 3.70mm 0757057605  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Left Guide,  
Right Endwall, 11  
Rows, 6 Columns,  
132 Circuits,  
Staggered Mating  
Pin Length 4.70mm  
& 5.70mm

1.85mm by 3.70mm 0757058605  
Pitch, GbX I-  
Trac™ Vertical  
Header Module,

Right Guide, Left  
Endwall, 11 Rows,  
6 Columns, 132  
Circuits, Staggered  
Mating Pin Length  
4.70mm & 5.70mm  
1.85mm by 3.70mm 0757059604  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm  
1.85mm by 3.70mm 0757059605  
Pitch, GbX I-  
Trac™ Vertical  
Header Module,  
Right Guide, Left  
Endwall, 11 Rows,  
6 Columns, 132  
Circuits, Staggered  
Mating Pin Length  
4.70mm & 5.70mm  
1.85mm by 3.70mm 0757059614  
Pitch, GbX I-Trac™  
Vertical Header  
Module, Right Guide,  
Left Endwall, 11  
Rows, 6 Columns,  
132 Circuits, Mating  
Pin Length 5.70mm,  
Orientation Key A

This document was generated on 04/13/2012

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**