

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [75705-1623](#)
Status: **Active**
Overview: GbX I-Trac™ Backplane Connector System
Description: 1.85mm by 3.70mm Pitch, GbX I-Trac™ Vertical Header Module, Unguided, Dual End Wall, 11 Rows, 6 Columns, 132 Circuits, Mating Pin Length 4.70mm, Orientation Key B

Documents:

[3D Model](#) [Product Specification PS-75710-999 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E29179

General


Product Family Backplane Connectors
 Series [75705](#)
 Application Backplane, Midplane, Orthogonal
 Component Type PCB Header
 Overview [GbX I-Trac™ Backplane Connector System](#)
 Product Name GbX I-Trac™
 Style N/A

Physical

Circuits (Loaded) 132
 Circuits (maximum) 132
 Color - Resin Black
 Durability (mating cycles max) 200
 First Mate / Last Break No
 Flammability 94V-0
 Guide to Mating Part No
 Keying to Mating Part None
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Number of Columns 6
 Number of Pairs 6, Open Pin Field
 Number of Rows 11
 Orientation Vertical
 PC Tail Length 2.10mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 1.60mm
 Packaging Type Tray
 Pitch - Mating Interface 1.85mm, 3.70mm
 Pitch - Termination Interface 1.00mm, 2.70mm
 Plating min - Mating 0.762µm
 Plating min - Termination 0.762µm
 Polarized to PCB No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -55°C to +80°C
 Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 1A



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[75705Series](#)

Mates With

[75710 GbX I-Trac™ Right Angle Receptacle Module](#)

Use With

[78232 GbX I-Trac™ Vertical Power Receptacle](#). [75234 Backplane Free Standing Guide Pin](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Press-In Tool for Vertical Header 11-Row, 6-Column	0622018602

Data Rate	12.0 Gbps
Real Signals (per 25mm)	148
Shield Type	N/A
Shielded	No
Voltage - Maximum	120V AC (RMS)/DC

Material Info

UPC	800756720036
-----	--------------

Reference - Drawing Numbers

Product Specification	PS-75710-999
Sales Drawing	SD-75705-001

This document was generated on 06/25/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION