## **BNC Jack Crimp**







## **Specifications:**

Impedance	: 50Ω
Frequency Range	: 0-4 GHz
VSWR	: 1.3 max.
Working Voltage	: 500V rms @ Sea level
Temperature Range	: -65°C to 165°C
Insulation Resistance	e : 5K MΩ min.
	141 141A Doldon 9240 9

For RG-58, 58A, 58C, 141, 141A, Belden 8240, 8262, 9201, 9203, 9310, 9311 & comm/scope 0268






5

Recommended Crimp Die : .068"

Recommended Crimp Die : .213"



Recommended Stripping Dimensions

Dimensions : Inches (Millimeters)

## Part Number Table

Description	Part Number
BNC Jack Crimp	SPC20553

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com www.farnell.com www.newark.com

Item

1

2

3

4

5

Description

Body

Contact

Dielectric

Washer

Ferrule

Qty

1

Material

Brass

Brass

PTFE

Brass

Brass

Finish

Nickel, 80µ"

Gold, 3µ"

Nickel, 80µ"

Nickel, 80µ"

