

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-50-8023

Status:

Active

Overview:

KK® Interconnection System

Description:

3.96mm Pitch KK® Crimp Terminal Housing, Friction Ramp, 2 Circuits



image - Reference only

Series

Documents:

- 3D Model

Packaging Specification PK-41695-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-08-50 (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

Crimp Housings

Series

41695

Application

Power, Wire-to-Board

Comments

Glow Wire Equivalent Part Number 416952001

MolexKits

Yes

Overview

KK® Interconnection System

Product Name

KK®

Physical

Breakaway

No

Circuits (maximum)

2

Color - Resin

Natural

Flammability

94V-0

Gender

Female

Glow-Wire Compliant

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Resin

Polyester

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm

Polarized to Mating Part

Yes

Temperature Range - Operating

0°C to +75°C

Material Info

Old Part Number

41695-N-D02

UPC

800755490503

Reference - Drawing Numbers

Packaging Specification

PK-41695-001

Product Specification

PS-08-50

Sales Drawing

SD-41695

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
41695Series

Use With
KK® Crimp Terminal 2478 , 2578 , 8818.
Trifurcon™ Crimp Terminal 7258 , 6438 , 6838

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION