


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19211-0001](#)  
**Status:** **Active**  
**Overview:** [Wire Pins](#)  
**Description:** Krimptite™ Wire Pin Terminal for 12-10 AWG Wire



**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013 (PDF)</a>
<a href="#">Product Specification PS-19902-011 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR18689
UL	E32244

**General**

Product Family	Crimp Terminals
Series	<a href="#">19211</a>
Application	Power
Comments	Pin Length 11.43mm
Crimp Quality Equipment	Yes
Overview	<a href="#">Wire Pins</a>
Product Name	Wire Pin

**Physical**


Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Packaging Type	Bag
Plating min - Mating	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	3.45mm max.
Wire Size AWG	10, 12
Wire Size mm²	12-10

**Material Info**

Old Part Number	WP-1210
-----------------	---------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19211-002

<b>EU RoHS</b> <b>ELV and RoHS</b> <b>Compliant</b> <b>REACH SVHC</b> Not Reviewed <b>Low-Halogen Status</b> <b>Not Reviewed</b>	<b>China RoHS</b> 
--	--

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**  
[19211Series](#)

**Application Tooling | FAQ**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

<b>Global</b>	
<b>Description</b>	<b>Product #</b>
Hand Crimp Tool	<a href="#">0640030100</a>
Crimp Head for the AT-200™ Pneumatic Hand Tool	<a href="#">0640070100</a>

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**