

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [46557-2145](#)  
**Status:** **Active**  
**Overview:** [SEARAY\\*](#)  
**Description:** 1.27mm by 1.27mm Pitch SEARAY\* Slim Receptacle, 80 Circuits, 5.00mm Unmated Height, 4 Rows, with Pegs, Solder Charge™ Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-45970-990 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-45970-001 (PDF)</a>
<a href="#">Product Specification PS-45970-001 (PDF)</a>	<a href="#">Test Summary TS-45970-002 (PDF)</a>
<a href="#">Application Specification AS-45970-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-45970-002 (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Receptacles
Series	<a href="#">46557</a>
Application	Board-to-Board, Signal
MolexKits	Yes
Overview	<a href="#">SEARAY*</a>
Product Name	SEARAY*

**Physical**

Circuits (Loaded)	80
Circuits (maximum)	80
Color - Resin	Black
Durability (mating cycles max)	100
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	Copper Alloy
Material - Plating Mating	Gold, Nickel
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Number of Rows	4
Orientation	Vertical
PC Tail Length	1.60mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.18mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +125°C




image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**

**REACH SVHC Contains SVHC: No Low-Halogen Status Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[46557Series](#)

**Mates With**

[46556](#) Searay\* Slim Plug Connector

Termination Interface: Style Through Hole  
Unmated Height 5.00mm

### Electrical

Current - Maximum per Contact 2.7A  
Grounding to PCB No  
Voltage - Maximum 240V AC

### Solder Process Data

Duration at Max. Process Temperature (seconds) 20  
Lead-free Process Capability Reflow Capable (SMT only)  
Max. Cycles at Max. Process Temperature 3  
Process Temperature max. C 260

### Material Info

UPC 800756911830

### Reference - Drawing Numbers

Application Specification AS-45970-001, AS-45970-002, AS-45970-990  
Product Specification PS-45970-001  
Sales Drawing SD-46557-001  
Test Summary TS-45970-001, TS-45970-002

\*SEARAY is a trademark of Samtec, Inc.

This document was generated on 06/19/2012

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**