



by Schneider Electric

List Price \$182.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Application	Specifically designed to handle high inrush associated with contactors and relays for applications such as conveyor systems, paint lines, punch presses or overhead cranes
Approvals	UL Listed File Number: E61239 - CSA Certified File Number: LR37055 Guide: 184-N-90 - CE Marked
Fuse Block	None
Terminal Type	Screw Clamp
Type	T
Mounting Type	Panel
Phase	1-Phase
Enclosure Type	Open
Temperature Rise	55 Degrees C
Primary	120x240V
Insulation Temperature	105 Degrees C
Rating	100VA
Secondary	24V
Depth	3.34 Inches
Width	3.38 Inches
Winding Material	Copper
Height	2.89 Inches

Shipping and Ordering

Category	16200 - Transformers, Industrial Control, 50 - 200 va, Type T
Discount Schedule	CP8
GTIN	00785901905066
Package Quantity	1
Weight	3.85 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.