

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [46114-1033](#)
Status: **Active**
Overview: [EXTreme LPHPower™](#)
Description: 1.27mm, 12.00mm Pitch, EXTreme LPHPower™ Receptacle Header, Vertical, 10 Power Contacts, 38 Signal Contacts, Select Gold (Au) Plating, without BMI Guides

Documents:

[3D Model](#) [Application Specification AS-46114-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-46114-001 \(PDF\)](#)

Agency Certification


CSA LR19880
 UL E29179

General

Product Family PCB Receptacles
 Series [46114](#)
 Application Board-to-Board, Power
 Application Tooling Part Link [621006300](#)
 Application Tooling Part Link [622018672](#)
 Comments Press Fit Pin
 Overview [EXTreme LPHPower™](#)
 Product Name EXTreme LPHPower™

Physical

(p)ower-(s)ignal Configuration 10p - 32s
 Circuits (Loaded) 42
 Circuits (maximum) 42
 Color - Resin Black
 Durability (mating cycles max) 250
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part None
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Number of Rows 2
 Orientation Vertical
 PC Tail Length 2.52mm, 2.58mm
 PCB Locator No
 PCB Retention None
 Packaging Type Tray
 Pitch - Mating Interface 1.27mm, 12.00mm
 Pitch - Termination Interface 1.27mm, 2.50mm
 Plating min - Mating 0.762µm
 Plating min - Termination 2.540µm
 Polarized to Mating Part Yes
 Polarized to PCB Yes
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -40°C to +105°C
 Termination Interface: Style Through Hole - Compliant Pin



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[46114Series](#)

Mates With

[45985](#) EXTreme LPHPower™ Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Vertical Receptacle	0622018672
Press-In Tool	
LPH Vertical	0621006300
Receptacle Power	
Terminal Removal	
Tool	

Electrical

Current - Maximum per Contact	30A
Grounding to PCB	No
Voltage - Maximum	250V AC (RMS)/DC

Material Info

UPC	756054922842
-----	--------------

Reference - Drawing Numbers

Application Specification	AS-46114-001
Product Specification	PS-46114-001
Sales Drawing	SD-46114-100

This document was generated on 06/19/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION