### **PCB Power Relay - G5CA**

### Flat Relays that Switch 10-A/15-A Loads with New Quick-connect **Terminals**

- ROHS compliant.
- Ideal for switching power in household appliances or for outputs from industrial devices.
- Sub-miniature dimensions: 22 x 16 x 11 mm  $(L \times W \times H).$
- High-sensitivity models available with low power consumption (150 mW).
- UL and CSA approved.
- Fully sealed models and quick-connect terminal models available (#187 load contact terminals).





# Ordering Information -

Contact form	Enclosure ratings	General purpose	High-sensitivity	High-capacity	Quick-connect terminals
SPST-NO	Flux protection	G5CA-1A	G5CA-1AH	G5CA-1A-E	G5CA-1AE-TP-E
_	Fully sealed	G5CA-1A4	G5CA-1A4H	_	-

Note: 1. When ordering, add the rated coil voltage to the model number.

Example: G5C-1 12 VDC

Rated coil voltage

- 2. High-capacity models with a Fully sealed structure are not available.
- 3. Standard or high-sensitivity models with quick-connect terminals are not available.

#### Model Number Legend

2

1. Number of Poles

1 pole (SPST-NO)

4. Special functions

5. Coil Consumption

None: Standard

High sensitivity

None: Standard E: High capacity

2. 2. Enclosure Ratings

None: Flux protection

Fully sealed

3. 3. Terminal Form

None: PCB Terminal Quick-connect terminal (#187)

6. 6. Rated coil voltage

5. 12. 24 VDC

Standard Specifications

Contact configuration: SPST-NO Enclosure ratings: Flux protection Terminal form: PCB terminal

# Specifications -

# **■ Coil Ratings**

Item	Standard, high-capacity, or quick-connect terminals			High-sensitivity		
	5 VDC	12 VDC	24 VDC	5 VDC	12 VDC	24 VDC
Rated current	40 mA	16.7 mA	8.3 mA	30 mA	12.5 mA	6.25 mA
Coil resistance	125 Ω	720 Ω	2,880 Ω	167 Ω	960 Ω	3,840 Ω
Must operate voltage	75% max. of rated voltage			80% max. of rated voltage		
Must release voltage	10% min. of rated voltage					
Max. voltage	150% (standard)/130% (high-capacity, quick-connect terminals) of rated voltage (at 23°C)			150% (at 23°C)		
Power consumption	Approx. 200 mW			Approx. 150 mW		

### **■ Contact Ratings**

Item	Stan	dard	High-sensitivity		High-capacity, or quick-connect terminals	
	Resistive load	Inductive load (cos	Resistive load	Inductive load (cosφ = 0.4, L/R = 7 ms)	Resistive load	Inductive load (cosφ = 0.4, L/R = 7 ms)
Contact Material	AgSnIn		AgSnIn		AgSnIn	
Rated load	10 A at 250 VAC; 10 A at 30 VDC	3 A at 250 VAC; 3 A at 30 VDC	10 A at 250 VAC; 10 A at 30 VDC	3 A at 250 VAC; 3 A at 30 VDC	15 A at 110 VAC; 10 A at 30 VDC	5 A at 110 VAC; 3 A at 30 VDC
Rated carry current	10 A		10 A		15 A	
Max. switching voltage	250 VAC, 125 VDC					
Max. switching current	10 A		10 A		15 A	
Max. switching	2,500 VA, 300 W	750 VA, 90 W	2,500 VA, 300 W	750 VA, 90 W	2,500 VA, 300 W	750 VA, 90 W
Max. switching	100mA at 5VDC					
Failure rate (reference value)	100mA at 5VDC					

### **■** Characteristics

Contact resistance	•	30 m $Ω$ max. (Quick-connect terminals type: 100 m $Ω$ max.)		
Operate time		10 ms max. (High-sensitivity type: 15 ms max.)		
Release time		10 ms max.		
Insulation resistance		1,000 M $\Omega$ min.		
Dielectric strength		2,500 VAC, 50/60 Hz for 1 min between coil and contacts 1,000 VAC, 50/60 Hz for 1 min between contacts of same polarity		
Insulation	Creepage (Typ)	3.5 mm		
Distance	Clearance (Typ)	2.8 mm		
Tracking Resistance	e (CTI)	250 V		
Impulse withstand	voltage	4,500 V (1.2 x 50 μs) between coil and contacts		
Vibration resistanc	е	Destruction: 10 to 55 to 10 Hz, 0.75-mm single amplitude (1.5-mm double amplitude) Malfunction: 10 to 55 to 10 Hz, 0.75-mm single amplitude (1.5-mm double amplitude)		
Shock resistance		Destruction: 1,000 m/s <sup>2</sup> Malfunction: 200 m/s <sup>2</sup>		
Endurance		Mechanical: 20,000,000 operations min. at 18,000 operations/hr Electrical: 300,000 operations min. (100,000 operations min. for Fully sealed Type) at 1,200 operations/hr under rated load of 10 A at 250 VAC; 100,000 operations min. under load of 15 A at 110 VAC for high-capacity models 100,000 operations min. at 1,200 operations/hr under rated load of 10 A at 30 VDC		
Ambient temperature		Operating: -25°C to 70°C (with no icing)		
Ambient humidity		Operating: 5% to 85%		
Weight		Approx. 8 g (for TP model: Approx. 9.6 g)		

Note: 1. The rated current and coil resistance are measured at a coil temperature of 23°C with a tolerance of ±10%.

2. Operating characteristics are measured at a coil temperature of 23°C.

### **PCB Power Relay - G5CA**

### ■ Approved Standards

UL Standard: UL508 (File No. E41515)

CSA Standard: CSA C22.2 No. 14 (File No. LR31928)

Model	No of Poles	Coil Rating	Contact Rating	No of Operations
G5CA	1	3 to 100VDC	15A, 125VAC (General Purpose) 10A, 250VAC (General Purpose) 15A, 250VDC (Resistive) 10A, 30VDC (Resistive)	100,000


### **EN Standard/TUV Certificated:**

### EN61810-1 (Certification No. R50030053)


Model	No of Poles	Coil Rating	Contact Rating	No of Operations
G5CA	1	3, 5, 6, 12, 24, 48VDC	15A, 125VAC (cosφ = 1.0) 10A, 250VAC (cosφ = 1.0) 10A, 30VDC (0ms)	100,000

### **■** Engineering Data


### Maximum Switching Power




### Endurance



### Ambient Temperature vs. Maximum Coil Voltage




#### Operating Temperature vs. Must-operate/Must-release Voltage



Note: The "maximum voltage" is the maximum voltage that can be applied to the relay coil.

### **Malfunction Shock**



No. of samples: 10

Measured value: The value at which malfunction occurs in the contact when

in the contact when the contact is subjected to shock three times each in six directions for three axes.

Standard: 200 m/s<sup>2</sup>

# **PCB Power Relay - G5CA**


# **Dimensions**


Note: 1. All units are in millimetres unless otherwise indicated.

2. Orientation marks are indicated as follows:

G5CA-1A(-E) G5CA-1A4(-H)







Terminal Arrangement/

**Mounting Holes** 


#### G5CA-1A-TP-E (BOTTOM VIEW) Internal Connections Tolerance: ±0.1 mm (BOTTOM VIEW) 1.8 Four, 1.2 dia. 25.1max (24.9)\* Two, 1 dia. (21.9)\* 10'-- 0.5 elliptic holes 11 (10,9)\* 17.78 (TOP VIEW) 4.9 6.25 0.3 0.3 1.35 0.5 16.1 14 25 -21.1 (BOTTOM VIEW) \* Average value -17.78 (No coil polarity)

### **Precautions**

### ■ Precautions for Correct Use

#### Installation

Make sure that sufficient space is provided between relays when installing two or more relays side by side to facilitate heat dissipation. Insufficient heat dissipation may result in the relay malfunctioning.



### **Quick-connect Terminal Connections**

- Do not pass current through the PCB of the load contactterminals (quick-connect terminals).
- The terminals are compatible with Faston receptacle #187 and are suitable for positive-lock mounting.


Use only Faston terminals with the specified numbers. Select leads for connecting Faston receptacles with wire diameters that are within the allowable range for the load current. Do not apply excessive force to the terminals when mounting or dismounting the Faston receptacle.

Insert and remove terminals carefully one at a time. Do not insert terminals on an angle, or insert/remove multiple terminals at the same time

The following positive-lock connectors made by AMP are recommended. Contact the manufacturer directly for details on connectors including availability.

#### **Charged Terminals**

The section marked with dotted circles (indicated by arrows) in the following diagram includes the charged terminals of the relay. When the relay is mounted on a PCB, make sure that there are no metal patterns on the section of the PCB facing the portion of the relay shaded in the following diagram.



#### Other Precautions

- The G5CA is a power relay designed for applications switching power loads such as heaters in electric household appliances.
   Do not use the G5CA to switch micro loads less than 100 mA, such as in signal applications.
- Use fully sealed models if the relays will require washing. Fluxprotection models may malfunction or the relay's performance may be otherwise adversely affected if cleaning fluid enters the relay.

Type Receptacle terminals (See note.)		Positive housing
#187 terminals (width: 4.75 mm)	AMP 170330-1 (170324-1)	AMP 172074-1 (natural color)
	AMP 170331-1 (170325-1)	AMP 172074-4 (yellow)
	AMP 170332-1 (170326-1)	AMP 172074-5 (green)
		AMP 172074-6 (blue)

Note: The numbers shown in parentheses are for air-feeding

To convert millimetres into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.