

Oscilloscope



Features:

- 4 in 1 multifunctional testing instrument: Oscilloscope / Arb. Waveform Generator / FFT Spectrum Analysis / Frequency Counter
- 16M memory depth oscilloscope
- 200MSa/s DDS arb. waveform generator

Specifications:

	Model	72-10179
Acquisition	Sample Mode	Real-Time Sample
	Sample Rate	200MSPS
	Average	N acquisitions, all channels simultaneously, N is selectable from 2, 4, 8, 16, 64, and 128
Input	Input Coupling	DC, AC, GND
	Input Impedance	Resistance: 1MΩ; Capacitance: 25pF
	PP-80,PP-150,PP-200 Probe Attenuation	10X
	Support Current Measure	1X, 10X
	Maximum Input Voltage	400Vpk (DC + peak)
Horizontal	Scanning Speed Range(Sec/Div)	5ns/div ~ 1,000s/div(1-2-5 sequences)
	Sample Rate and Delay Time Accuracy	±50ppm(any interval ≥1ms)
	Wave form Interpolation	Step, Linear, Sin(x)/x
	Memory Depth(Sample Points)	10K ~ 16M for each channel; 16M: 5ns/div-1000s/div
	Analog Bandwidth	60MHz (-3dB)
	A/D converter	8 bit resolution
Vertical	Vertical Scale(Volt/div) Range	10mV ~ 5V/div @ x1 probe(1,2,5 sequence); 100mV ~ 50V/div @ x10 probe
	Position Range	±4division
	Selectable Analog Bandwidth Limit(typical)	20MHz
	Lower Frequency Response(-3dB)	≤ 10Hz(at input BNC)
	Rise Time at BNC(typical)	≤5.8ns
	DC Gain Accuracy	±3%



Oscilloscope



Trigger	Trigger Source	CH1,CH2, EXT	
	Trigger Mode	Auto, Normal and Single	
	Trigger Type	Edge, Pulse, Video, Alternative	
	Trigger Sensitivity	0.02 div increments	
	Trigger Level Range	±4V	
	Trigger Level Accuracy	±4 division	
	Edge Trigger Slope	Rising, Falling	
	Pulse Width Trigger	Trigger Condition: Trigger when <, >, =, or ≠; Positive pulse or Negative pulse Pulse Width Range: Selectable from 20ns to 10s	
	Video Trigger Type (Signal Formats and Field Rates)	Supports NTSC, PAL and SECAM broadcast systems for any field or any line	
	Alternative Trigger	CH1/CH2/CH3/CH4: Internal Trigger, Edge, Pulse Width, Video	
Measurement	Cursor Measure	Amplitude difference between cursors (ΔV); Time difference between cursors (Δt); Reciprocal of Δt in Hertz ($1/\Delta t$) (Cross, Trace, Horizontal, Vertical)	
	Auto Measure	Voltage	Vp-p, Vmax, Vmin, Vmean, Vamp, Vtop, Vbase, Vmid, Vrms, Vcrms, Preshoot, Overshoot
		Time	Frequency, Period, Rise Time(10%~90%), Fall Time(10%~90%), Positive Width, Negative Width, Duty Cycle
Arbitrary Waveform Generator	Waveform Frequency	DC ~ 25MHz	
	DAC clock	2K ~ 200MHz adjustable	
	Frequency Resolution	0.10%	
	Waveform Depth	4K Sample	
	Vertical Resolution	12 bit	
	Frequency Stability	<30ppm	
	Wave Amplitude	±3.5V Max.	
	Output Impedance	50Ω	
	Output Current	50mA ,Ipeak=50mA	
	System BW	25MHz	
	Harmonic Distortion	-50dB(1KHz), -40dB(10KHz)	
Environmental	Temperature	Operating: 0°C to 40°C Non-operating: -20°C to +60°C)	
	Cooling Method	Forced air	
	Humidity	Below +35°C, ≤90% relative humidity; +35°C to +40°C, ≤60% relative humidity	
	Altitude	Operating: 3,000m or below; Non-operating: 15,000m or below	

Oscilloscope



Mechanical	Size	190mm(L)×100mm(W)×35mm(H)
	Heavy	Without Packaged 0.29kg; Packaged 0.9kg;
Accessories	Probe	X1, X10 two passive probes. The passive probes have a 6MHz bandwidth (rated 100Vrms CAT III) when the switch is in the X1 position, and a maximum bandwidth (rated 300Vrms CAT II) when the switch is in the X10 position. Each probe consists of all necessary fittings.
	Adapter	A power adapter special for this product. In addition to the power adapter shipped with your instrument, you may purchase another one certified for the country of use.
	USB Line	A USB A-B line, used to connect external devices with USB-B interface like a printer or to establish communications between PC and the oscilloscope.
	Installation CD	A software installation CD and it also contains the user manual for the Tenma Oscilloscope.

Part Number Table

Description	Part Number
Oscilloscope, PC, 2 CH, 60MHz, AFG	72-10179

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

