



REVISIONS

DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1453	A	RELEASED	JWM	12/30/03	HO	1/13/04	CG	2/2/04

**NOTES**

- Ground Fault Interrupter Ratings: 10, 15, 20, 25, 30 & 35 mA
- Checks Receptacles for:
 - Correct wiring
 - No Ground
 - Live and Neutral Reversed
 - Neutral Fault
 - Live and Ground Reversed
 - Live Fault
- Dimensions: 85mm(L) x 56mm(W) x 31mm(D)
- Supplied complete with 15 Amp molded plug
- Test Current Accuracy $\pm 1.75\text{mA}$ at 110VAC
- Weight: 250g

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:				
	Jeff McVicker	12/30/03	Combined Receptacle and Ground Fault Interrupter Tester				
	CHECKED BY:	DATE:	SIZE	DWG. NO.		ELECTRONIC FILE	REV
	Hisham Odish	1/13/04	A	72-6791		19C6769.dwg	A
	APPROVED BY:	DATE:	SCALE: NTS		U.O.M.: Millimeters		SHEET: 1 OF 1
	Chris Gloger	2/2/04					

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.