

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

34803-0211

Status:

Active

Description:

CTX64 Female Terminal, D-Wind, Left Payoff, SAE 22



image - Reference only

Series

Documents:

- Drawing (PDF)

Application Specification AS-34803-001 (PDF)
- RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	34803
Application	Power
Crimp Quality Equipment	Yes
Product Literature Order No	987650-4561
Product Name	CTX64

Physical

Durability (mating cycles max)	10
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.10 to 1.65mm
Wire Size AWG	22
Wire Size mm²	0.22-0.35

Electrical

Current - Maximum per Contact	7A
Voltage - Maximum	250V

Material Info

UPC	884982186613
-----	--------------

Reference - Drawing Numbers

Application Specification	AS-34803-001
Sales Drawing	SD-34803-001

EU RoHS

ELV and RoHS  
Compliant  
REACH SVHC  
Contains SVHC: No  
Low-Halogen Status  
Not Reviewed

China RoHS



Need more information on product  
environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

Search Parts in this Series

34803Series

Mates With

0.64 by 0.64mm blade

Use With

34729 2.54mm Pitch Stac64™ Right Angle  
Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are  
found by selecting the products below.  
Crimp Height Specifications are then  
contained in the Application Tooling  
Specification document.

Global

Description	Product #
FineAdjust™	0639010100
Applicator for CTX64 Receptacle Terminals	
Hand Crimp Tool for	0638193700
CTX64 Receptacle	

Terminal, 0.22, 0.30,  
0.35mm<sup>2</sup> and 22  
AWG

This document was generated on 06/19/2012

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**