

Micro Relay A/VFMA

- High current version with limiting continuous current 30A at 85°C
- Pin assignment according to ISO 7588 part 3
- Customized versions on request
 - 24VDC versions with special contact gap
 - Integrated components (e.g. diode)
 - Customized marking
 - Special covers (e.g. notches, release features)
 - For latching version refer to Micro Relay Latching
 - For low noise version refer to Micro Relay Low Noise
 - For high current version refer to part number table

Typical applications

Cross carline up to 30A for example: ABS control, blower fans, cooling fan, door control, door lock, fuel pump, heated front screen, immobilizer, interior lights, seat control, seatbelt pretensioner, sun roof, trunk lock, valves, window lifter, wiper control.




FVFMA_fcw1c

Contact Data	Form A -	- Standard	For	m C	Form A – HC
Contact arrangement	1 form A, 1 NO	1 form A, 1 NO	1 form C, 1 CO	1 form C, 1 CO	1 form A, 1 NO
Rated voltage	12VDC	24VDC	12VDC	24VDC	12VDC
Limiting continuous current, form A/form	В	NO/NC	NO/NC		
23°C	30A	30A	30/20A	30/20A	35A
85°C	25A	25A	25/15A	25/15A	30A
125°C	10A	10A	10/8A	10/8A	15A
Limiting making current ¹⁾²⁾ , A/B (NO/NC)	120A	120A	120/40A	120/20A	120A
Limiting breaking current	30A	20A	30/15A	20/10A	30A
Limiting short-time current,					
overload current, ISO 8820-33)	1.35 x 2	5A, 1800s	1.35 x 25	5A, 1800s	1.35 x 30A, 1800s
	2.00 x	25A, 5s	2.00 x	25A, 5s	2.00 x 30A, 5s
	3.50 x 2	25A, 0.5s	3.50 x 2	5A, 0.5s	3.50 x 30A, 0.5s
	6.00 x 2	25A, 0.1s	6.00 x 2	6.00 x 30A, 0.1s	
Jump start test		24VDC for 5min condu	cting nominal current at 2	23°C	
Contact material			silver based		
Min. recommended contact load ⁴⁾			1A at 5VDC		
Initial voltage drop					
NO contact at 10A, typ./max.			15/20	00mV	
NC contact at 10A, typ./max.				20/250mV	
Frequency of operation			6 ops./min (0.1Hz)		
Electrical endurance ⁵⁾					
resistive load at 14VDC	>1x10 ⁵ ops.		>1x10 ⁵ ops.		>1x10 ⁵ ops.
	25A		25A (NO)		30A
resistive load at 28VDC		>1x10 ⁵ ops.		>1x10 ⁵ ops.	
		15A		15A (NO)	
				>1x10 ⁵ ops.	
				10A (NC)	

Mechanical endurance

Max. DC load breaking capacity



06-2012, Rev. 0612 www.te.com © 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company. Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. typ. 10⁷ ops.

- The values apply to a resistive or inductive load with suitable spark suppression and at maximum 13.5VDC for 12VDC or 27VDC for 24VDC load voltages.
- 2) For a load current duration of maximum 3s for a make/break ratio of 1:10.
- Current and time are compatible with circuit protection by a typical automotive fuse. Relay will make, carry and break the specified current.
- See chapter Diagnostics of Relays in our Application Notes or consult the internet at http://relays.te.com/appnotes/
- 5) Electrical endurance data are only valid for the variants with resistor.

Load limit curve 1: arc extinguishes during transit time (CO contact). Load limit curve 2: safe shutdown, no stationary arc (NO contact). Load limit curves measured with low inductive resistors verified for 1000 switching events.

Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change. 1



12/24VDC


Micro Relay A/VFMA (Continued)

Coil Data Coil voltage range

Coil vers	sions, DC co	il			
Coil	Rated	Operate	Release	Coil	Rated coil
code	voltage	voltage	voltage	resistance ⁶⁾	power ⁶⁾
	VDC	VDC	VDC	Ω±10%	W
001	12	7.2	1.6	119	1.20
002	24	14.4	3.6	430	1.34
005	12	7.2	1.6	144	1.00
F	12	7.2	1.2	90	1.60
Н	24	14.4	3.6	430	1.34

All figures are given for coil without pre-energization, at ambient temperature +23°C. 6) Without components in parallel.

Coil operating range



Does not take into account the temperature rise due to the contact current E = pre-energization.

Insulation Data

moulation Bata		
Initial dielectric strength		
between open contacts	500VAC _{rms}	
between contact and coil	500VAC _{rms}	
Load dump test		
ISO 7637-1 (12VDC), test pulse 5	Vs=+86.5VDC	
ISO 7637-2 (24VDC), test pulse 5	Vs=+200VDC	

compliant
COMPliant
-40 to +125°C
6 cycles, storage 8/16h
10 cycles, -40/+85°C (5°C/min)
6 cycles, upper air temp. 55°C
56 days
RT I – dustproof
IP54
10±2cm ³ /m ³ SO ₂ , 10 days
1±0.3cm ³ /m ³ H ₂ S, 10 days
10 to 500Hz min. 5g ⁷⁾
C C
min. 20g 11ms ⁷⁾
1m onto concrete
plug-in, QC
150N
150N
200N
100N
100N
10N ⁸⁾
10N ⁸⁾
0.3Nm
approx. 16 to 20g (0.5 to 0.7oz)
480 pcs.
600 pcs.


 No change in the switching state >10µs. Valid for NC contacts, NO contact values significantly higher.


 Values apply 2mm from the end of the terminal. When the force is removed, the terminal must not have moved by more than 0.3mm

Accessories


For details see datasheet	Connectors for Micro ISO Relays

Terminal Assignment





COD 1 form C, 1 CO with diode




06-2012, Rev. 0612 www.te.com © 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. company. Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at http://relays.te.com/definitions

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.




Micro Relay A/VFMA (Continued)



Quick connect terminal similar to ISO 8092-1. Micro A: Terminals without holes

View of the terminals (bottom view)



3



Micro Relay A/VFMA (Continued)

Prod	uct co	ode structure			Тур	ical product code V23074	-A	1	001	-A4	02
Туре											
	V230	74 Micro Relay A									
Versio	n						-				
	Α	Standard	Н	High current							
Coil s	uppres	ssion									
	1	Resistor	2	Diode							
Coil											
	001	12VDC	002	24VDC 00	05	12VDC for high current version	n				
Conta	ct mat	terial									
	- A 4	Silver based	-A5	Silver based for high current	vers	ion					
Conta	ct arra	angement									
	02	1 form A, 1 NO	03	1 form C, 1 CO							

Product code structure	Typical product code VFMA -1	1 F	4 1 -	-S01
Type VFMA VFMA Series				
Version				
1 Standard				
Contact arrangement				
1 1 form A, 1 NO	I form C, 1 CO			
Coil				
F 12VDC	24VDC			
Contact material				
4 Silver based	Silver based for high current version			
Terminals				
1 Plug-in				
Coil suppression				
S01 Resistor				

Product code	Equivalent to	Version	Coil suppr.	Circuit ¹⁾	Coil	Arrangement	Terminals	Part number
V23074-A1001-A402	VFMA-11F41-S01	Standard	Resistor 680Ω	NOR	12VDC	1 form A, 1 NO	Plug-in, QC	1393292-5
VEGOT TYTTOOT YTTOE		otaridard		Nort	12120	1 101117 (, 1 1 10	r lag in, do	9-1414992-1
VFMA-11F41-S01	V23074-A1001-A402							9-1393292-9
V23074-A1001-A403	VFMA-15F41-S01			COR		1 form C, 1 CO		8-1393292-4
VFMA-15F41-S01	V23074-A1001-A403							1393293-8
V23074-A2001-A402			Diode	NOD		1 form A, 1 NO		5-1393292-8
V23074-A2001-A403				COD]	1 form C, 1 CO		6-1419137-4
V23074-H1005-A502	VFMA-11F71-S01	High current	Resistor 1000Ω	NOR		1 form A, 1 NO		2-1414971-4
VFMA-11F71-S01	V23074-H1005-A502		Resistor 680Ω					1432885-1
V23074-A1002-A402	VFMA-11H41-S01	Standard	Resistor 1800Ω		24VDC			8-1393292-9
VFMA-11H41-S01	V23074-A1002-A402							6-1415008-2
V23074-A1002-A403				COR		1 form C, 1 CO		3-1393292-8
V23074-A2002-A402			Diode	NOD		1 form A, 1 NO		6-1393292-2
V23074-A2002-A403				COD		1 form C, 1 CO		6-1393292-3

1) See terminal assignment diagrams.

Other types on request.

This list represents the most common types and does not show all variants covered by this datasheet.

4

Datasheets and product specification according to IEC 61810-1 and to be used only together with the 'Definitions' section. Datasheets and product data is subject to the terms of the disclaimer and all chapters of the 'Definitions' section, available at <u>http://relays.te.com/definitions</u>

Datasheets, product data, 'Definitions' section, application notes and all specifications are subject to change.