

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [34803-0212](#)
Status: **Active**
Description: CTX64 Female Terminal, D-Wind, Left Payoff, SAE 20

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Application Specification AS-34803-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	34803
Application	Power
Crimp Quality Equipment	Yes
Product Literature Order No	987650-4561
Product Name	CTX64

Physical

Durability (mating cycles max)	10
Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40 to 1.90mm
Wire Size AWG	20
Wire Size mm ²	0.50-0.75

Electrical

Current - Maximum per Contact	7A
Voltage - Maximum	250V

Material Info

UPC	884982186828
-----	--------------

Reference - Drawing Numbers

Application Specification	AS-34803-001
Sales Drawing	SD-34803-001



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[34803Series](#)

Mates With

0.64 by 0.64mm blade

Use With

[34729](#) 2.54mm Pitch Stac64™ Right Angle Receptacle

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for CTX64 Receptacle Terminals, 0.50mm ² , 0.75mm ² & 0.85mm ² and TXL 20 AWG	0639010300

Hand Crimp Tool for [0638193800](#)
CTX64 Receptacle
Terminal, 0.50, 0.75,
0.85mm² and 20
AWG

This document was generated on 06/19/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION