

CFPT-123 SMD TCVCXO

ISSUE 7; 17 JANUARY 2011 - RoHS 2002/95/EC

Description

- Surface mount temperature compensated voltage controlled crystal oscillator (TCVCXO) in a hermetically sealed ceramic package

Standard Frequencies

- 10, 12.8, 13, 14.4, 15.36, 19.2, 19.44, 19.68, 20, 26MHz

Output Compatibility & Load

- Clipped Sine 0.8V_{pk-pk} minimum
- 10kΩ // 10pF ±10%

Frequency Tolerance

- ±0.5ppm max

Frequency Stability

- See table

Supply Voltage Variation

- ±0.2ppm (5% change)

Load Variation

- ±0.2ppm (10% change)

Ageing

- ±1ppm typ in 1st year @ 25°C

Voltage Control

- 1.5V±1.0V applied to pad 1 (frequency movement is positive sense)

Frequency Adjustment

- ±5ppm min

Input Impedance

- 1.0MΩ min

Phase Noise (typical @ 10MHz)

- 90dBc/Hz @ 10Hz
- 110dBc/Hz @ 100Hz
- 140dBc/Hz @ 1kHz
- 145dBc/Hz @ 10kHz

Storage Temperature Range

- 55 to 125°C


Environmental

- Shock: MIL-STD-883D, Method 2002.3, Test Condition B: 1500G, 0.5ms, 1/2 sine wave, 3 shocks in each of 3 mutually perpendicular planes
- Vibration: MIL-STD-883D, Method 2005.2, Test Condition B: 20G (20Hz-2000Hz), 1.5mm amplitude, in 3 mutually perpendicular planes, 4hrs in each plane

Packaging


- Loose in bulk pack, 100pcs per pack
- Tape and reel in accordance with EIA-481-D, 1kpcs per reel (please see pages 372 & 373)

Outline (mm)




- Pad Connections
- Voltage Control
 - GND
 - Output
 - +VS

Solder Pad Layout



Test Circuit



Ordering Information (*minimum required)

- Frequency*
- Model*
- Output
- Frequency Stability (over operating temperature range)*
- Operating Temperature Range*
- Supply Voltage

Example

- 13.0MHz CFPT-123
Clipped Sine ±2.5ppm -30 to 80C 3.0V



Electrical Specification - maximum limiting values

Frequency Range	Supply Voltage	Supply Current	Frequency Adjustment	Output Waveform	Output	Model Number
10.0 to 26.0MHz	3.0V±0.3V	2.5mA	±5.0ppm min. / 1.5V±1.0V	Clipped Sine	0.8V _{pk-pk} min	CFPT-123

Note: For other frequencies / specifications combinatins, please contact our sales offices

Frequency Stabilities over Operating Temperature Range

Operating Temperature Ranges	Frequency Stabilities v Operating Temperature Range			
	±1.5ppm	±2.0ppm	±2.5ppm	±5.0ppm
0 to 50°C	✓	✓	✓	✓
-10 to 60°C	✓	✓	✓	✓
-20 to 70°C	-	✓	✓	✓
-30 to 80°C	-	✓	Standard*	✓
-30 to 85°C	-	-	✓	✓
-40 to 85°C	-	-	✓	✓

* Note: ±2.5ppm over -30 to 80°C is the standard frequency stability vs operating temperature range

