

**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

ACRYLIC PAINT  
all solid colours  
Aerosol

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Paints

### 1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.  
Ambersil House - Wylde Road  
Castlefield Industrial Estate  
TA6 4DD Bridgwater Somerset  
United Kingdom  
Tel.: +44 1278 727200  
Fax.: +44 1278 425644  
E-mail : hse.uk@crcind.com

### 1.4. Emergency telephone number

(+44)(0)1278 72 7200

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to 67/548/EEC or 1999/45/EC:

<b>Health:</b>	R36: Irritating to eyes. R66: Repeated exposure may cause skin dryness or cracking. R67: Vapours may cause drowsiness and dizziness.
<b>Physical:</b>	EXTREMELY FLAMMABLE
<b>Environment:</b>	not classified

### 2.2. Label elements

**Warning symbol(s) :** EXTREMELY FLAMMABLE



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

Xi : IRRITANT



<b>Risk-phrase(s) :</b>	R36: Irritating to eyes. R66: Repeated exposure may cause skin dryness or cracking. R67: Vapours may cause drowsiness and dizziness.
<b>Safety-phrase(s) :</b>	S2: Keep out of the reach of children. S16: Keep away from sources of ignition - No smoking. S23: Do not breathe vapours/spray. S24/25: Avoid contact with skin and eyes. S29/56: Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. S46: If swallowed, seek medical advice immediately and show this container or label. S51: Use only in well-ventilated areas.
<b>Extra label elements according to Aerosol Dispenser Directive 75/324/EC:</b>	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material. Without adequate ventilation formation of explosive mixtures may be possible.

### 2.3. Other hazards

None

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable.

### 3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
acetone; propan-2-one; propanone	67-64-1	200-662-2	25-50	F,Xi	11-36-66-67	A
butane (<= 0,1 % butadiene)	106-97-8	203-448-7	10-25	F+	12	
dimethyl ether	115-10-6	204-065-8	10-25	F+	12	A
n-butyl acetate	123-86-4	204-658-1	10-25		10-66-67	
propane	74-98-6	200-827-9	10-25	F+	12	B
2-methoxy-1-methylethyl acetate	108-65-6	203-603-9	5-10		10	A
Solvent naphtha (petroleum), light arom. (benzene<0.1%)	64742-95-6	265-199-0	<1	Xn,N	10-37-51/53-65-66-67	B,P

#### Explanation notes

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

P : not classified as carcinogen, less than 0.1% w/w benzene (Einecs-nr. 200-753-7)

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
acetone; propan-2-one;	01-2119471330-49	67-64-1	200-662-	25-50	Flam. Liq. 2, Eye Irrit. 2, STOT	H225,H319,H336	A

**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

propanone			2		SE 3		
butane (<= 0,1 % butadiene)		106-97-8	203-448-7	10-25	Flam. Gas 1, Press. Gas	H220	
dimethyl ether	01-2119472128-37	115-10-6	204-065-8	10-25	Flam. Gas 1, Press. Gas	H220,H280	A
n-butyl acetate	01-2119485493-29	123-86-4	204-658-1	10-25	Flam. Liq. 3, STOT SE 3	H226,H336	
propane		74-98-6	200-827-9	10-25	Flam. Gas 1, Press. Gas	H220	B
2-methoxy-1-methylethyl acetate	01-2110475791-29	108-65-6	203-603-9	5-10	Flam. Liq. 3	H226	A

**Explanation notes**

A : substance with Community workplace exposure limit

B : substance with national established workplace exposure limit

(\* Explanation phrases : see chapter 16)

**SECTION 4: First aid measures****4.1. Description of first aid measures**

<b>Contact with eyes :</b>	If substance has got into eyes, immediately wash out with water for at least 15 minutes Seek medical advice
<b>Contact with skin :</b>	Remove contaminated clothing immediately and drench affected skin with plenty of water. Then wash with soap and water Seek medical attention if irritation persists
<b>Inhalation :</b>	Remove patient to fresh air Keep warm and at rest, in a half upright position. Loosen clothing Seek medical attention if ill effects occur
<b>Ingestion :</b>	If swallowed accidentally, do not induce vomiting and seek medical advice.

**4.2. Most important symptoms and effects, both acute and delayed**

<b>Inhalation :</b>	Excessive inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances Symptoms : sore throat, abdominal pain, nausea, vomiting
<b>Skin contact :</b>	May cause irritation. Symptoms : redness and pain
<b>Eye contact :</b>	Irritating to eyes Symptoms : redness and pain

**4.3. Indication of any immediate medical attention and special treatment needed**

<b>General Advice :</b>	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

**SECTION 5: Firefighting measures****5.1. Extinguishing media**


3 / 9

CRC Industries UK Limited

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD

Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

foam, carbon dioxide or dry agent

## 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C  
Forms hazardous decomposition products  
CO,CO2

## 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water  
In case of fire, do not breathe fumes

# SECTION 6: Accidental release measures

## 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources  
Ensure adequate ventilation  
Wear suitable protective clothing and gloves.

## 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses  
If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

## 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material  
Place in appropriate container

## 6.4. Reference to other sections

For further information see section 8

# SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

Keep away from heat and sources of ignition  
Take precautionary measures against static discharges  
Equipment should be earthed  
Use explosion-proof electrical/ventilating/lighting/.../equipment.  
Use only non-sparking tools.  
Do not breathe aerosols or vapours.  
Ensure adequate ventilation  
Avoid contact with skin and eyes.  
Wash thoroughly after use  
Wear protective gloves/protective clothing/eye protection/face protection.



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

Eyewash bottles should be available

## 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.  
 Keep out of reach of children.

## 7.3. Specific end use(s)

Paints

# SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

### Exposure limits :

Hazardous ingredient	CAS-nr.	method	
<b>EU established exposure limits:</b>			
2-methoxy-1-methylethyl acetate	108-65-6	TWA	50 ppm
		STEL	100 ppm
dimethyl ether	115-10-6	TWA	1000 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
<b>National established exposure limits, United Kingdom</b>			
butane (<= 0,1 % butadiene)	106-97-8	TWA	600 ppm
		STEL	750 ppm
dimethyl ether	115-10-6	TWA	400 ppm
		STEL	500 ppm
n-butyl acetate	123-86-4	TWA	150 ppm
		STEL	200 ppm
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm
		STEL	1500 ppm

## 8.2. Exposure controls

<b>Control procedures :</b>	Ensure adequate ventilation Keep away from heat and sources of ignition Take precautionary measures against static discharges
<b>Personal protection :</b>	Take precautions to avoid contact with skin and eyes when handling the product. Ensure adequate ventilation
<b>inhalation :</b>	In case of insufficient ventilation, wear suitable respiratory equipment. Air purifying respirator equipped with organic gas/vapor cartridge (type A or AX)
<b>hands and skin :</b>	Wear suitable protective gloves against chemicals (butyl rubber)
<b>eyes :</b>	Wear safety goggles.

**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

<b>Apperance : physical state :</b>	Liquid under pressure.
<b>colour :</b>	See color cap.
<b>odour :</b>	Characteristic odor.
<b>pH :</b>	Not applicable.
<b>Boiling point/range :</b>	Not available.
<b>Flash point :</b>	< 0 °C
<b>Evaporation rate :</b>	Not available.
<b>Explosion limits : upper limit :</b>	18.6 %
<b>lower limit :</b>	1.2 %
<b>Vapour pressure :</b>	830 kPa (@ 20°C).
<b>Relative density :</b>	0.868 g/cm <sup>3</sup> (@ 20°C).
<b>Solubility in water :</b>	Not available.
<b>Auto-ignition :</b>	> 200 °C
<b>Viscosity :</b>	Not applicable.

### 9.2. Other information

**VOC:** 830.5 g/l

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

### 10.2. Chemical stability

Stable

### 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

### 10.4. Conditions to avoid

Avoid overheating

### 10.5. Incompatible materials

Strong oxidising agent

### 10.6. Hazardous decomposition products



6 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

CO,CO2

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

<b>Inhalation :</b>	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
<b>Ingestion :</b>	May cause gastrointestinal disturbances
<b>Skin contact :</b>	May cause irritation.
<b>Eye contact :</b>	Irritating to eyes

### Toxicological data :

Hazardous ingredient	CAS-nr.	method	
n-butyl acetate	123-86-4	LD50 oral rat	> 2000 mg/kg
		LC50 inhal.rat	> 20 mg/l
acetone; propan-2-one; propanone	67-64-1	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 2000 mg/kg

## SECTION 12: Ecological information

### 12.1. Toxicity

not classified

### Ecotoxicological data:

Hazardous ingredient	CAS-nr.	method	
n-butyl acetate	123-86-4	IC50 algae	647 mg/l
		LC50 fish	18 mg/l
		EC50 daphnia	44 mg/l
acetone; propan-2-one; propanone	67-64-1	IC50 algae	> 100 mg/l
		LC50 fish	> 100 mg/l
		EC50 daphnia	> 100 mg/l

### 12.2. Persistence and degradability

No experimental data available

### 12.3. Bioaccumulative potential

No experimental data available



7 / 9

**CRC Industries UK Limited**  
 Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
 Somerset, TA6 4DD  
 Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

Productname : ACRYLIC PAINT  
Ref.Nr.: BDS000794\_3\_20120614

Creationdate : 14.06.12 Version : 1.1  
Replaces: BDS000794\_20111114

#### 12.4. Mobility in soil

No experimental data available

#### 12.5. Results of PBT and vPvB assessment

No information available

#### 12.6. Other adverse effects

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**Product :** This material and its container must be disposed of in a safe way. Do not discharge into drains or the environment, dispose to an authorised waste collection point.

**Contaminated packaging :** Disposal should be in accordance with local, state or national legislation

### SECTION 14: Transport information

#### 14.1. UN number

UN-number : 1950

#### 14.2. UN proper shipping name

Proper shipping name: AEROSOLS

#### 14.3. Transport hazard class(es)

Class: 2.1  
ADR/RID - Classification code: 5F

#### 14.4. Packing group

Packing group: Not applicable.

#### 14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No  
IMDG - Marine pollutant: No  
IATA/ICAO - Environmentally hazardous: No

#### 14.6. Special precautions for user



8 / 9

**CRC Industries UK Limited**  
Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater,  
Somerset, TA6 4DD  
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com



**Productname :** ACRYLIC PAINT  
**Ref.Nr.:** BDS000794\_3\_20120614

**Creationdate :** 14.06.12 Version : 1.1  
**Replaces:** BDS000794\_20111114

ADR/RID - Tunnelcode:	(D)
IMDG - Ems:	F-D, S-U
IATA/ICAO - PAX:	203
IATA/ICAO - CAO	203

#### 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.  
Dir. 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.  
EU-directive 99/45/EC  
Regulation (EC) No 1907/2006 (REACH)

#### 15.2. Chemical safety assessment

No information available

### SECTION 16: Other information

\*Explanation risk-phrases:

- R10: Flammable.
- R11: Highly flammable.
- R12: Extremely flammable.
- R36: Irritating to eyes.
- R37: Irritating to respiratory system.
- R65: Harmful: may cause lung damage if swallowed.
- R66: Repeated exposure may cause skin dryness or cracking.
- R67: Vapours may cause drowsiness and dizziness.
- R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

\*Explanation hazard statements:

- H220 : Extremely flammable gas.
- H225 : Highly flammable liquid and vapour.
- H226 : Flammable liquid and vapour.
- H280 : Contains gas under pressure; may explode if heated.
- H319 : Causes serious eye irritation.
- H336 : May cause drowsiness or dizziness.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.