

Round Yellow Through-hole LED

OVLFY3C7



Absolute Maximum Ratings

T_A = 25° C unless otherwise noted

Storage Temperature Range	-40 ~ +100° C
Operating Temperature Range	-40 ~ +85° C
Reverse Voltage	5 V
Continuous Forward Current ²	30 mA
Peak Forward Current (10% Duty Cycle, 1 KHz)	100 mA
Power Dissipation	78 mW
Lead Soldering Temperature (3 mm from the base of the epoxy bulb) ¹	260° C
Current Linearity vs. Ambient Temperature	-0.5 mA/° C
LED Junction Temperature	125° C

Notes:

- Solder time less than 5 seconds at temperature extreme.
- Design of Heat Dissipation should be considered.


Electrical Characteristics

T_A = 25° C unless otherwise noted

SYMBOL	PARAMETER	MIN	TYP	MAX	UNITS	CONDITIONS
I _V	Luminous Intensity	3115	5700	----	mcd	I _F = 20 mA
V _F	Forward Voltage	----	2.2	2.6	V	I _F = 20 mA
I _R	Reverse Current	----	----	10	μA	V _R = 5 V
λ _P	Peak Wavelength	----	593	----	nm	I _F = 20 mA
λ _D	Dominant Wavelength	----	589	----	nm	I _F = 20 mA
Δλ	Spectra Half Width	----	25	----	nm	I _F = 20 mA
2Θ _{1/2}	50% Power Angle	----	30	----	deg	I _F = 20 mA

Standard Bins (I_F = 20 mA)

Lamps are sorted to luminous intensity (I_V) and dominant wavelength (λ_D) bins shown. Orders for OVLFY3C7 may be filled with any or all bins contained as below.



Forward Voltage (V_F)

Rank	G	H	J	6
Voltage	1.8–2.0	2.0–2.2	2.2–2.4	2.4–2.6

Notes:


- All ranks will be included per delivery, rank ratio will be based on the chip distribution.
- To designate luminous intensity ranks, please contact OPTEK.
- Pb content <1000 PPM.

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.


Round Yellow Through-hole LED

OVLFY3C7


Typical Electro-Optical Characteristics Curves




Forward Current vs Forward Voltage




Relative Luminous Intensity vs Forward Current




Reverse Current vs Reverse Voltage




Forward Current vs Ambient Temperature



Relative Luminous Intensity vs Wavelength



Relative Luminous Intensity vs Ambient Temperature




Beam Pattern

OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.


Round Yellow Through-hole LED

OVLFY3C7

Packing Information: Available in bulk or reel




Bulk: 500 pcs/bag




13-inch reel: 1000 pcs/reel

Carrier Tape Dimensions: Loaded quantity 1000 pieces per reel



DIMENSIONS ARE IN INCHES AND [MILLIMETERS].

Moisture Resistant Packaging



OPTEK reserves the right to make changes at any time in order to improve design and to supply the best product possible.