

Snap-in Type

Series: **UQ** Type: **TS**



■ Features


- Endurance : 85 °C 2000 h
- 30 % Smaller than series TS-UP
- RoHS directive compliant

■ Specifications

| | | | | | | | | |
|------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------|----------------------|------|------|------|------|---------|
| Category Temp. Range | -40 °C to +85 °C | | -25 °C to +85 °C | | | | | |
| Rated W.V. Range | 16 V.DC to 100 V.DC | 160 V.DC to 250 V.DC | 315 V.DC to 450 V.DC | | | | | |
| Nominal Cap. Range | 1000 μF to 100000 μF | 270 μF to 3900 μF | 82 μF to 1000 μF | | | | | |
| Capacitance Tolerance | ±20 % (120 Hz/+20 °C) | | | | | | | |
| DC Leakage Current | 3√CV (μA) max. After 5 minutes application of rated working voltage at +20 °C C : Capacitance (μF) V: W.V. (V.DC) | | | | | | | |
| tan δ | Please see the attached standard products list. | | | | | | | |
| Frequency Correction Factor for Ripple Current | Frequency (Hz) | 50 | 60 | 100 | 120 | 500 | 1 k | 10 k to |
| | 16 V.DC to 100 V.DC /C.F. | 0.93 | 0.95 | 0.99 | 1.00 | 1.05 | 1.08 | 1.15 |
| | 160 V.DC to 450 V.DC /C.F. | 0.75 | 0.80 | 0.95 | 1.00 | 1.20 | 1.25 | 1.40 |
| Endurance | After 2000 hours application of DC voltage with specified ripple current (≤ rated DC working voltage) at +85 °C±2 °C, the capacitors shall meet the following limits. | | | | | | | |
| | Capacitance change | ≤ ±20 % of initial measured value | | | | | | |
| | tan δ | ≤ 200 % of initial specified value | | | | | | |
| Shelf Life | After storage for 1000 hours at +85 °C±2 °C within no voltage applied and then being stabilized at +20 °C, capacitors shall meet the limits specified in Endurance. (With voltage treatment) | | | | | | | |
| | DC leakage current | ≤ initial specified value | | | | | | |

■ Dimensions in mm (not to scale)

(mm)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

00 Sep. 2010

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|--------------------------------------------------------------------------------|------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 16 | 12000 | 22 | 25 | EETUQ1C123HJ | 4.5 | 0.50 | 200 |
| | 15000 | 22 | 30 | EETUQ1C153HJ | 5.3 | 0.50 | 200 |
| | 18000 | 22 | 35 | EETUQ1C183HJ | 5.6 | 0.50 | 200 |
| | | 25 | 25 | EETUQ1C183JJ | 5.6 | 0.50 | 200 |
| | 22000 | 22 | 40 | EETUQ1C223HJ | 6.1 | 0.50 | 200 |
| | | 25 | 30 | EETUQ1C223JJ | 6.1 | 0.50 | 200 |
| | 27000 | 22 | 45 | EETUQ1C273HJ | 6.3 | 0.50 | 200 |
| | | 25 | 35 | EETUQ1C273JJ | 6.3 | 0.50 | 200 |
| | | 30 | 25 | EETUQ1C273KJ | 6.3 | 0.50 | 200 |
| | 33000 | 22 | 50 | EETUQ1C333HJ | 6.8 | 0.50 | 200 |
| | | 25 | 40 | EETUQ1C333JJ | 6.8 | 0.50 | 200 |
| | | 30 | 30 | EETUQ1C333KJ | 6.8 | 0.50 | 200 |
| | | 35 | 25 | EETUQ1C333LJ | 6.8 | 0.50 | 200 |
| | 39000 | 25 | 45 | EETUQ1C393JJ | 6.9 | 0.56 | 200 |
| | | 30 | 35 | EETUQ1C393KJ | 6.9 | 0.56 | 100 |
| | 47000 | 25 | 50 | EETUQ1C473JJ | 7.5 | 0.64 | 200 |
| | | 30 | 40 | EETUQ1C473KJ | 7.5 | 0.64 | 100 |
| | | 35 | 30 | EETUQ1C473LJ | 7.5 | 0.64 | 200 |
| | 56000 | 30 | 45 | EETUQ1C563KJ | 8.7 | 0.73 | 100 |
| | | 35 | 35 | EETUQ1C563LJ | 8.7 | 0.73 | 100 |
| 68000 | 30 | 50 | EETUQ1C683KJ | 9.1 | 0.85 | 100 | |
| | 35 | 40 | EETUQ1C683LJ | 9.1 | 0.85 | 100 | |
| * | 82000 | 35 | 45 | EETUQ1C823LJ | 9.5 | 0.99 | 100 |
| * | 100000 | 35 | 50 | EETUQ1C104LJ | 10.2 | 1.17 | 100 |
| 25 | 8200 | 22 | 25 | EETUQ1E822HJ | 3.6 | 0.40 | 200 |
| | 10000 | 22 | 30 | EETUQ1E103HJ | 3.8 | 0.40 | 200 |
| | 12000 | 22 | 30 | EETUQ1E123HJ | 4.1 | 0.40 | 200 |
| | | 25 | 25 | EETUQ1E123JJ | 4.1 | 0.40 | 200 |
| | 15000 | 22 | 35 | EETUQ1E153HJ | 4.6 | 0.40 | 200 |
| | | 25 | 30 | EETUQ1E153JJ | 4.6 | 0.40 | 200 |
| | 18000 | 22 | 40 | EETUQ1E183HJ | 5.5 | 0.40 | 200 |
| | | 25 | 35 | EETUQ1E183JJ | 5.5 | 0.40 | 200 |
| | | 30 | 25 | EETUQ1E183KJ | 5.5 | 0.40 | 200 |
| | 22000 | 22 | 45 | EETUQ1E223HJ | 6.1 | 0.40 | 200 |
| | | 25 | 40 | EETUQ1E223JJ | 6.1 | 0.40 | 200 |
| | | 30 | 30 | EETUQ1E223KJ | 6.1 | 0.40 | 200 |
| | | 35 | 25 | EETUQ1E223LJ | 6.1 | 0.40 | 200 |
| | 27000 | 25 | 45 | EETUQ1E273JJ | 6.2 | 0.40 | 200 |
| | | 30 | 35 | EETUQ1E273KJ | 6.2 | 0.40 | 100 |
| | 33000 | 25 | 50 | EETUQ1E333JJ | 6.8 | 0.40 | 200 |
| | | 30 | 40 | EETUQ1E333KJ | 6.8 | 0.40 | 100 |
| | | 35 | 30 | EETUQ1E333LJ | 6.8 | 0.40 | 200 |
| | 39000 | 30 | 45 | EETUQ1E393KJ | 7.4 | 0.46 | 100 |
| | | 35 | 35 | EETUQ1E393LJ | 7.4 | 0.46 | 100 |
| 47000 | 30 | 50 | EETUQ1E473KJ | 8.0 | 0.54 | 100 | |
| | 35 | 40 | EETUQ1E473LJ | 8.0 | 0.54 | 100 | |
| * | 56000 | 35 | 45 | EETUQ1E563LJ | 8.7 | 0.63 | 100 |
| * | 68000 | 35 | 50 | EETUQ1E683LJ | 9.6 | 0.75 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. | Cap. (120 Hz) (±20 %) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-------|-----------------------------|--------------|----------------|--------------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 35 | 5600 | 22 | 25 | EETUQ1V562HJ | 3.4 | 0.35 | 200 |
| | 6800 | 22 | 30 | EETUQ1V682HJ | 3.7 | 0.35 | 200 |
| | 8200 | 22 | 30 | EETUQ1V822HJ | 4.0 | 0.35 | 200 |
| | | 25 | 25 | EETUQ1V822JJ | 4.0 | 0.35 | 200 |
| | 10000 | 22 | 35 | EETUQ1V103HJ | 4.4 | 0.35 | 200 |
| | | 25 | 30 | EETUQ1V103JJ | 4.4 | 0.35 | 200 |
| | 12000 | 22 | 40 | EETUQ1V123HJ | 5.1 | 0.35 | 200 |
| | | 25 | 35 | EETUQ1V123JJ | 5.1 | 0.35 | 200 |
| | | 30 | 25 | EETUQ1V123KJ | 5.1 | 0.35 | 200 |
| | 15000 | 22 | 45 | EETUQ1V153HJ | 5.6 | 0.35 | 200 |
| | | 25 | 40 | EETUQ1V153JJ | 5.6 | 0.35 | 200 |
| | 18000 | 25 | 45 | EETUQ1V183JJ | 5.7 | 0.35 | 200 |
| | | 30 | 30 | EETUQ1V183KJ | 5.7 | 0.35 | 200 |
| | | 35 | 25 | EETUQ1V183LJ | 5.7 | 0.35 | 200 |
| | 22000 | 25 | 50 | EETUQ1V223JJ | 6.1 | 0.35 | 200 |
| | | 30 | 35 | EETUQ1V223KJ | 6.1 | 0.35 | 100 |
| | | 35 | 30 | EETUQ1V223LJ | 6.1 | 0.35 | 200 |
| | 27000 | 30 | 45 | EETUQ1V273KJ | 6.8 | 0.35 | 100 |
| | | 35 | 35 | EETUQ1V273LJ | 6.8 | 0.35 | 100 |
| | 33000 | 30 | 50 | EETUQ1V333KJ | 7.2 | 0.35 | 100 |
| 35 | | 40 | EETUQ1V333LJ | 7.2 | 0.35 | 100 | |
| * | 39000 | 35 | 45 | EETUQ1V393LJ | 7.7 | 0.41 | 100 |
| * | 47000 | 35 | 50 | EETUQ1V473LJ | 8.5 | 0.49 | 100 |
| 50 | 3300 | 22 | 25 | EETUQ1H332HJ | 2.7 | 0.30 | 200 |
| | 3900 | 22 | 30 | EETUQ1H392HJ | 2.8 | 0.30 | 200 |
| | 4700 | 22 | 30 | EETUQ1H472HJ | 3.0 | 0.30 | 200 |
| | | 25 | 25 | EETUQ1H472JJ | 3.0 | 0.30 | 200 |
| | 5600 | 22 | 35 | EETUQ1H562HJ | 3.4 | 0.30 | 200 |
| | 6800 | 22 | 40 | EETUQ1H682HJ | 3.9 | 0.30 | 200 |
| | | 25 | 30 | EETUQ1H682JJ | 3.9 | 0.30 | 200 |
| | | 30 | 25 | EETUQ1H682KJ | 3.9 | 0.30 | 200 |
| | 8200 | 22 | 45 | EETUQ1H822HJ | 4.4 | 0.30 | 200 |
| | | 25 | 35 | EETUQ1H822JJ | 4.4 | 0.30 | 200 |
| | 10000 | 22 | 50 | EETUQ1H103HJ | 5.0 | 0.30 | 200 |
| | | 25 | 40 | EETUQ1H103JJ | 5.0 | 0.30 | 200 |
| | | 30 | 30 | EETUQ1H103KJ | 5.0 | 0.30 | 200 |
| | | 35 | 25 | EETUQ1H103LJ | 5.0 | 0.30 | 200 |
| | 12000 | 25 | 45 | EETUQ1H123JJ | 5.6 | 0.30 | 200 |
| | | 30 | 35 | EETUQ1H123KJ | 5.6 | 0.30 | 100 |
| | | 35 | 30 | EETUQ1H123LJ | 5.6 | 0.30 | 200 |
| | 15000 | 30 | 40 | EETUQ1H153KJ | 6.4 | 0.30 | 100 |
| 35 | | 35 | EETUQ1H153LJ | 6.4 | 0.30 | 100 | |
| 18000 | 30 | 45 | EETUQ1H183KJ | 6.9 | 0.30 | 100 | |
| | 35 | 40 | EETUQ1H183LJ | 6.9 | 0.30 | 100 | |
| * | 22000 | 35 | 45 | EETUQ1H223LJ | 7.6 | 0.30 | 100 |
| * | 27000 | 35 | 50 | EETUQ1H273LJ | 8.3 | 0.30 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of $\phi 35 \times 45L$ and $\phi 35 \times 50L$ are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|----------------------------------------------------------------------------|------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 63 | 2200 | 22 | 25 | EETUQ1J222HJ | 2.5 | 0.30 | 200 |
| | 2700 | 22 | 30 | EETUQ1J272HJ | 3.7 | 0.30 | 200 |
| | 3300 | 22 | 30 | EETUQ1J332HJ | 4.1 | 0.30 | 200 |
| | | 25 | 25 | EETUQ1J332JJ | 4.1 | 0.30 | 200 |
| | 3900 | 22 | 35 | EETUQ1J392HJ | 4.4 | 0.30 | 200 |
| | | 25 | 30 | EETUQ1J392JJ | 4.4 | 0.30 | 200 |
| | 4700 | 22 | 40 | EETUQ1J472HJ | 4.9 | 0.30 | 200 |
| | | 25 | 35 | EETUQ1J472JJ | 4.9 | 0.30 | 200 |
| | | 30 | 25 | EETUQ1J472KJ | 4.9 | 0.30 | 200 |
| | 5600 | 22 | 45 | EETUQ1J562HJ | 5.4 | 0.30 | 200 |
| | | 25 | 40 | EETUQ1J562JJ | 5.4 | 0.30 | 200 |
| | 6800 | 25 | 45 | EETUQ1J682JJ | 5.8 | 0.30 | 200 |
| | | 30 | 30 | EETUQ1J682KJ | 5.8 | 0.30 | 200 |
| | | 35 | 25 | EETUQ1J682LJ | 6.0 | 0.30 | 200 |
| | 8200 | 25 | 50 | EETUQ1J822JJ | 6.0 | 0.30 | 200 |
| | | 30 | 35 | EETUQ1J822KJ | 6.0 | 0.30 | 100 |
| | | 35 | 30 | EETUQ1J822LJ | 6.5 | 0.30 | 200 |
| | 10000 | 30 | 40 | EETUQ1J103KJ | 6.5 | 0.30 | 100 |
| | | 35 | 35 | EETUQ1J103LJ | 6.5 | 0.30 | 100 |
| | 12000 | 30 | 45 | EETUQ1J123KJ | 7.2 | 0.30 | 100 |
| 35 | | 40 | EETUQ1J123LJ | 7.2 | 0.30 | 100 | |
| * | 15000 | 35 | 45 | EETUQ1J153LJ | 7.9 | 0.30 | 100 |
| * | 18000 | 35 | 50 | EETUQ1J183LJ | 8.6 | 0.30 | 100 |
| 80 | 1500 | 22 | 25 | EETUQ1K152HJ | 2.3 | 0.25 | 200 |
| | 1800 | 22 | 30 | EETUQ1K182HJ | 2.5 | 0.25 | 200 |
| | 2200 | 22 | 35 | EETUQ1K222HJ | 2.7 | 0.25 | 200 |
| | | 25 | 25 | EETUQ1K222JJ | 2.7 | 0.25 | 200 |
| | 2700 | 22 | 40 | EETUQ1K272HJ | 2.8 | 0.25 | 200 |
| | | 25 | 30 | EETUQ1K272JJ | 2.8 | 0.25 | 200 |
| | 3300 | 22 | 45 | EETUQ1K332HJ | 3.2 | 0.25 | 200 |
| | | 25 | 35 | EETUQ1K332JJ | 3.2 | 0.25 | 200 |
| | | 30 | 25 | EETUQ1K332KJ | 3.2 | 0.25 | 200 |
| | 3900 | 22 | 50 | EETUQ1K392HJ | 3.6 | 0.25 | 200 |
| | | 25 | 40 | EETUQ1K392JJ | 3.6 | 0.25 | 200 |
| | 4700 | 25 | 45 | EETUQ1K472JJ | 4.1 | 0.25 | 200 |
| | | 30 | 30 | EETUQ1K472KJ | 4.1 | 0.25 | 200 |
| | 5600 | 25 | 50 | EETUQ1K562JJ | 4.6 | 0.25 | 200 |
| | | 30 | 35 | EETUQ1K562KJ | 4.6 | 0.25 | 100 |
| | | 35 | 30 | EETUQ1K562LJ | 4.6 | 0.25 | 200 |
| | 6800 | 30 | 45 | EETUQ1K682KJ | 5.2 | 0.25 | 100 |
| | | 35 | 35 | EETUQ1K682LJ | 5.2 | 0.25 | 100 |
| | 8200 | 30 | 50 | EETUQ1K822KJ | 5.8 | 0.25 | 100 |
| | | 35 | 40 | EETUQ1K822LJ | 5.8 | 0.25 | 100 |
| * | 10000 | 35 | 45 | EETUQ1K103LJ | 6.4 | 0.25 | 100 |
| * | 12000 | 35 | 50 | EETUQ1K123LJ | 7.0 | 0.25 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|--------------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 100 | 1000 | 22 | 25 | EETUQ2A102HJ | 2.0 | 0.25 | 200 |
| | 1200 | 22 | 30 | EETUQ2A122HJ | 2.3 | 0.25 | 200 |
| | | 25 | 25 | EETUQ2A122JJ | 2.3 | 0.25 | 200 |
| | 1500 | 22 | 30 | EETUQ2A152HJ | 2.6 | 0.25 | 200 |
| | 1800 | 22 | 35 | EETUQ2A182HJ | 2.8 | 0.25 | 200 |
| | | 25 | 30 | EETUQ2A182JJ | 2.8 | 0.25 | 200 |
| | 2200 | 22 | 45 | EETUQ2A222HJ | 3.1 | 0.25 | 200 |
| | | 25 | 35 | EETUQ2A222JJ | 3.1 | 0.25 | 200 |
| | | 30 | 25 | EETUQ2A222KJ | 3.1 | 0.25 | 200 |
| | 2700 | 22 | 50 | EETUQ2A272HJ | 3.7 | 0.25 | 200 |
| | | 25 | 40 | EETUQ2A272JJ | 3.7 | 0.25 | 200 |
| | | 30 | 30 | EETUQ2A272KJ | 3.7 | 0.25 | 200 |
| | | 35 | 25 | EETUQ2A272LJ | 3.7 | 0.25 | 200 |
| | 3300 | 25 | 45 | EETUQ2A332JJ | 4.1 | 0.25 | 200 |
| | | 30 | 35 | EETUQ2A332KJ | 4.1 | 0.25 | 100 |
| | 3900 | 25 | 50 | EETUQ2A392JJ | 4.5 | 0.25 | 200 |
| | | 30 | 40 | EETUQ2A392KJ | 4.5 | 0.25 | 100 |
| | | 35 | 30 | EETUQ2A392LJ | 4.5 | 0.25 | 200 |
| | 4700 | 30 | 45 | EETUQ2A472KJ | 5.1 | 0.25 | 100 |
| | | 35 | 35 | EETUQ2A472LJ | 5.1 | 0.25 | 100 |
| 5600 | 30 | 50 | EETUQ2A562KJ | 5.8 | 0.25 | 100 | |
| | 35 | 40 | EETUQ2A562LJ | 5.8 | 0.25 | 100 | |
| * | 6800 | 35 | 45 | EETUQ2A682LJ | 6.6 | 0.25 | 100 |
| * | 8200 | 35 | 50 | EETUQ2A822LJ | 7.2 | 0.25 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|----------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 160 | 560 | 22 | 25 | EETUQ2C561HJ | 2.25 | 0.15 | 200 |
| | 680 | 22 | 30 | EETUQ2C681HJ | 2.50 | 0.15 | 200 |
| | 820 | 22 | 35 | EETUQ2C821HJ | 2.75 | 0.15 | 200 |
| | 1000 | 22 | 40 | EETUQ2C102HJ | 3.00 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2C102JJ | 3.00 | 0.15 | 200 |
| | 1200 | 22 | 45 | EETUQ2C122HJ | 3.25 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2C122JJ | 3.25 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2C122KJ | 3.25 | 0.15 | 200 |
| | 1500 | 22 | 50 | EETUQ2C152HJ | 3.73 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2C152JJ | 3.73 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2C152KJ | 3.73 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2C152LJ | 3.73 | 0.15 | 200 |
| | 1800 | 25 | 45 | EETUQ2C182JJ | 4.20 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2C182KJ | 4.20 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2C182LJ | 4.20 | 0.15 | 200 |
| | 2200 | 30 | 40 | EETUQ2C222KJ | 4.78 | 0.15 | 100 |
| | | 35 | 35 | EETUQ2C222LJ | 4.78 | 0.15 | 100 |
| | 2700 | 30 | 45 | EETUQ2C272KJ | 5.45 | 0.15 | 100 |
| | | 35 | 40 | EETUQ2C272LJ | 5.45 | 0.15 | 100 |
| | * | 3300 | 35 | 45 | EETUQ2C332LJ | 5.75 | 0.15 |
| * | 3900 | 35 | 50 | EETUQ2C392LJ | 6.00 | 0.15 | 100 |
| 180 | 470 | 22 | 25 | EETUQ2P471HJ | 2.08 | 0.15 | 200 |
| | 560 | 22 | 30 | EETUQ2P561HJ | 2.25 | 0.15 | 200 |
| | 680 | 22 | 30 | EETUQ2P681HJ | 2.50 | 0.15 | 200 |
| | | 25 | 25 | EETUQ2P681JJ | 2.50 | 0.15 | 200 |
| | 820 | 22 | 35 | EETUQ2P821HJ | 2.75 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2P821JJ | 2.75 | 0.15 | 200 |
| | 1000 | 22 | 45 | EETUQ2P102HJ | 3.00 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2P102JJ | 3.00 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2P102KJ | 3.00 | 0.15 | 200 |
| | 1200 | 22 | 50 | EETUQ2P122HJ | 3.31 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2P122JJ | 3.31 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2P122KJ | 3.31 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2P122LJ | 3.31 | 0.15 | 200 |
| | 1500 | 25 | 45 | EETUQ2P152JJ | 3.83 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2P152KJ | 3.83 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2P152LJ | 3.83 | 0.15 | 200 |
| | 1800 | 25 | 50 | EETUQ2P182JJ | 4.32 | 0.15 | 200 |
| | | 30 | 40 | EETUQ2P182KJ | 4.32 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2P182LJ | 4.32 | 0.15 | 200 |
| | 2200 | 30 | 45 | EETUQ2P222KJ | 4.92 | 0.15 | 100 |
| 35 | | 40 | EETUQ2P222LJ | 4.92 | 0.15 | 100 | |
| 2700 | 30 | 50 | EETUQ2P272KJ | 5.52 | 0.15 | 100 | |
| | 35 | 45 | EETUQ2P272LJ | 5.52 | 0.15 | 100 | |
| * | 3300 | 35 | 50 | EETUQ2P332LJ | 5.75 | 0.15 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|----------------------------------------------------------------------------|------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 200 | 390 | 22 | 25 | EETUQ2D391HJ | 1.68 | 0.15 | 200 |
| | 470 | 22 | 30 | EETUQ2D471HJ | 1.85 | 0.15 | 200 |
| | 560 | 22 | 30 | EETUQ2D561HJ | 2.43 | 0.15 | 200 |
| | | 25 | 25 | EETUQ2D561JJ | 2.43 | 0.15 | 200 |
| | 680 | 22 | 35 | EETUQ2D681HJ | 2.68 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2D681JJ | 2.68 | 0.15 | 200 |
| | 820 | 22 | 40 | EETUQ2D821HJ | 2.93 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2D821JJ | 2.93 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2D821KJ | 2.93 | 0.15 | 200 |
| | 1000 | 22 | 45 | EETUQ2D102HJ | 3.25 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2D102JJ | 3.25 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2D102KJ | 3.25 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2D102LJ | 3.25 | 0.15 | 200 |
| | 1200 | 22 | 50 | EETUQ2D122HJ | 3.50 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2D122JJ | 3.50 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2D122KJ | 3.50 | 0.15 | 200 |
| | 1500 | 25 | 50 | EETUQ2D152JJ | 3.87 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2D152KJ | 3.87 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2D152LJ | 3.87 | 0.15 | 200 |
| | 1800 | 30 | 45 | EETUQ2D182KJ | 4.32 | 0.15 | 100 |
| 35 | | 35 | EETUQ2D182LJ | 4.32 | 0.15 | 100 | |
| 2200 | 30 | 50 | EETUQ2D222KJ | 4.92 | 0.15 | 100 | |
| | 35 | 40 | EETUQ2D222LJ | 4.92 | 0.15 | 100 | |
| * | 2700 | 35 | 50 | EETUQ2D272LJ | 5.45 | 0.15 | 100 |
| 220 | 330 | 22 | 25 | EETUQ2Q331HJ | 1.58 | 0.15 | 200 |
| | 470 | 22 | 30 | EETUQ2Q471HJ | 1.99 | 0.15 | 200 |
| | | 25 | 25 | EETUQ2Q471JJ | 1.99 | 0.15 | 200 |
| | 560 | 22 | 35 | EETUQ2Q561HJ | 2.28 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2Q561JJ | 2.28 | 0.15 | 200 |
| | 680 | 22 | 35 | EETUQ2Q681HC | 2.46 | 0.15 | 200 |
| | | 22 | 40 | EETUQ2Q681HJ | 2.46 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2Q681JJ | 2.46 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2Q681KJ | 2.46 | 0.15 | 200 |
| | 820 | 22 | 45 | EETUQ2Q821HJ | 2.81 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2Q821JJ | 2.81 | 0.15 | 200 |
| | 1000 | 25 | 45 | EETUQ2Q102JJ | 3.29 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2Q102KJ | 3.29 | 0.15 | 200 |
| | 1200 | 25 | 50 | EETUQ2Q122JJ | 3.60 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2Q122KJ | 3.60 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2Q122LJ | 3.60 | 0.15 | 200 |
| | 1500 | 30 | 45 | EETUQ2Q152KJ | 3.92 | 0.15 | 100 |
| | | 35 | 35 | EETUQ2Q152LJ | 3.92 | 0.15 | 100 |
| | 1800 | 30 | 50 | EETUQ2Q182KJ | 4.30 | 0.15 | 100 |
| | | 35 | 40 | EETUQ2Q182LJ | 4.30 | 0.15 | 100 |
| * | 2200 | 35 | 50 | EETUQ2Q222LJ | 4.95 | 0.15 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|----------------------------------------------------------------------------|------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 250 | 270 | 22 | 25 | EETUQ2E271HJ | 1.31 | 0.15 | 200 |
| | 330 | 22 | 30 | EETUQ2E331HJ | 1.75 | 0.15 | 200 |
| | 390 | 22 | 30 | EETUQ2E391HJ | 1.91 | 0.15 | 200 |
| | | 25 | 25 | EETUQ2E391JJ | 1.91 | 0.15 | 200 |
| | 470 | 22 | 35 | EETUQ2E471HJ | 2.11 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2E471JJ | 2.11 | 0.15 | 200 |
| | 560 | 22 | 40 | EETUQ2E561HJ | 2.25 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2E561JJ | 2.25 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2E561KJ | 2.25 | 0.15 | 200 |
| | 680 | 22 | 45 | EETUQ2E681HJ | 2.50 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2E681JJ | 2.50 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2E681KJ | 2.50 | 0.15 | 200 |
| | 820 | 22 | 50 | EETUQ2E821HJ | 2.77 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2E821JJ | 2.77 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2E821KJ | 2.77 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2E821LJ | 2.77 | 0.15 | 200 |
| | 1000 | 25 | 45 | EETUQ2E102JJ | 3.32 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2E102KJ | 3.32 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2E102LJ | 3.32 | 0.15 | 200 |
| | 1200 | 30 | 40 | EETUQ2E122KJ | 3.53 | 0.15 | 100 |
| 35 | | 35 | EETUQ2E122LJ | 3.53 | 0.15 | 100 | |
| 1500 | 30 | 50 | EETUQ2E152KJ | 4.04 | 0.15 | 100 | |
| | 35 | 40 | EETUQ2E152LJ | 4.04 | 0.15 | 100 | |
| * | 1800 | 35 | 45 | EETUQ2E182LJ | 4.55 | 0.15 | 100 |
| * | 2200 | 35 | 50 | EETUQ2E222LJ | 4.75 | 0.15 | 100 |
| 315 | 180 | 22 | 25 | EETUQ2F181HJ | 1.21 | 0.15 | 200 |
| | 220 | 22 | 30 | EETUQ2F221HJ | 1.41 | 0.15 | 200 |
| | 270 | 22 | 30 | EETUQ2F271HJ | 1.60 | 0.15 | 200 |
| | 330 | 22 | 40 | EETUQ2F331HJ | 1.82 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2F331JJ | 1.82 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2F331KJ | 1.82 | 0.15 | 200 |
| | 390 | 22 | 45 | EETUQ2F391HJ | 2.01 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2F391JJ | 2.01 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2F391KJ | 2.01 | 0.15 | 200 |
| | 470 | 22 | 50 | EETUQ2F471HJ | 2.27 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2F471JJ | 2.27 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2F471KJ | 2.27 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2F471LJ | 2.27 | 0.15 | 200 |
| | 560 | 25 | 45 | EETUQ2F561JJ | 2.56 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2F561KJ | 2.56 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2F561LJ | 2.56 | 0.15 | 200 |
| | 680 | 30 | 40 | EETUQ2F681KJ | 2.87 | 0.15 | 100 |
| | | 35 | 35 | EETUQ2F681LJ | 2.87 | 0.15 | 100 |
| | 820 | 30 | 45 | EETUQ2F821KJ | 3.25 | 0.15 | 100 |
| | | 35 | 40 | EETUQ2F821LJ | 3.25 | 0.15 | 100 |
| 1000 | 30 | 50 | EETUQ2F102KJ | 3.63 | 0.15 | 100 | |
| | 35 | 45 | EETUQ2F102LJ | 3.63 | 0.15 | 100 | |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|----------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 350 | 150 | 22 | 25 | EETUQ2V151HJ | 1.12 | 0.15 | 200 |
| | 180 | 22 | 30 | EETUQ2V181HJ | 1.22 | 0.15 | 200 |
| | 220 | 22 | 35 | EETUQ2V221HJ | 1.44 | 0.15 | 200 |
| | 270 | 22 | 40 | EETUQ2V271HJ | 1.66 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2V271JJ | 1.66 | 0.15 | 200 |
| | 330 | 22 | 45 | EETUQ2V331HJ | 1.88 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2V331JJ | 1.88 | 0.15 | 200 |
| | 390 | 22 | 50 | EETUQ2V391HJ | 2.06 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2V391JJ | 2.06 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2V391KJ | 2.06 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2V391LJ | 2.06 | 0.15 | 200 |
| | 470 | 25 | 45 | EETUQ2V471JJ | 2.40 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2V471KJ | 2.40 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2V471LJ | 2.40 | 0.15 | 200 |
| | 560 | 25 | 50 | EETUQ2V561JJ | 2.60 | 0.15 | 200 |
| | | 30 | 40 | EETUQ2V561KJ | 2.60 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2V561LJ | 2.60 | 0.15 | 200 |
| | 680 | 30 | 45 | EETUQ2V681KJ | 2.96 | 0.15 | 100 |
| | | 35 | 35 | EETUQ2V681LJ | 2.96 | 0.15 | 100 |
| | 820 | 30 | 50 | EETUQ2V821KJ | 3.25 | 0.15 | 100 |
| 35 | | 45 | EETUQ2V821LJ | 3.25 | 0.15 | 100 | |
| * | 1000 | 35 | 50 | EETUQ2V102LJ | 3.54 | 0.15 | 100 |
| 400 | 120 | 22 | 25 | EETUQ2G121HJ | 1.02 | 0.15 | 200 |
| | 150 | 22 | 30 | EETUQ2G151HJ | 1.16 | 0.15 | 200 |
| | 180 | 22 | 30 | EETUQ2G181HC | 1.44 | 0.15 | 200 |
| | | 22 | 35 | EETUQ2G181HJ | 1.44 | 0.15 | 200 |
| | 220 | 22 | 35 | EETUQ2G221HC | 1.49 | 0.15 | 200 |
| | | 22 | 40 | EETUQ2G221HJ | 1.49 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2G221JJ | 1.49 | 0.15 | 200 |
| | 270 | 22 | 45 | EETUQ2G271HJ | 1.67 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2G271JJ | 1.67 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2G271KC | 1.67 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2G271KJ | 1.67 | 0.15 | 200 |
| | 330 | 22 | 50 | EETUQ2G331HJ | 1.90 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2G331JJ | 1.90 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2G331KJ | 1.90 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2G331LJ | 1.90 | 0.15 | 200 |
| | 390 | 25 | 45 | EETUQ2G391JJ | 2.13 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2G391KJ | 2.13 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2G391LJ | 2.13 | 0.15 | 200 |
| | 470 | 25 | 50 | EETUQ2G471JJ | 2.39 | 0.15 | 200 |
| | | 30 | 40 | EETUQ2G471KJ | 2.39 | 0.15 | 100 |
| 35 | | 30 | EETUQ2G471LJ | 2.39 | 0.15 | 200 | |
| 560 | 30 | 45 | EETUQ2G561KJ | 2.69 | 0.15 | 100 | |
| | 35 | 35 | EETUQ2G561LJ | 2.69 | 0.15 | 100 | |
| 680 | 30 | 50 | EETUQ2G681KJ | 2.96 | 0.15 | 100 | |
| | 35 | 40 | EETUQ2G681LC | 2.96 | 0.15 | 100 | |
| 820 | 35 | 45 | EETUQ2G821LC | 3.25 | 0.15 | 100 | |
| | 35 | 50 | EETUQ2G821LJ | 3.25 | 0.15 | 100 | |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.
Should a safety concern arise regarding this product, please be sure to contact us immediately.

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) |
|-----------------|-------------------------------------|--------------|----------------|--------------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------|----------------------------------|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | |
| 420 | 120 | 22 | 25 | EETUQ2S121HJ | 1.08 | 0.15 | 200 |
| | 150 | 22 | 30 | EETUQ2S151HJ | 1.30 | 0.15 | 200 |
| | | 25 | 25 | EETUQ2S151JJ | 1.30 | 0.15 | 200 |
| | 180 | 22 | 35 | EETUQ2S181HJ | 1.48 | 0.15 | 200 |
| | | 25 | 30 | EETUQ2S181JJ | 1.48 | 0.15 | 200 |
| | 220 | 22 | 40 | EETUQ2S221HJ | 1.65 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2S221JJ | 1.65 | 0.15 | 200 |
| | | 30 | 25 | EETUQ2S221KJ | 1.65 | 0.15 | 200 |
| | 270 | 22 | 45 | EETUQ2S271HJ | 1.94 | 0.15 | 200 |
| | | 25 | 35 | EETUQ2S271JC | 1.94 | 0.15 | 200 |
| | | 25 | 40 | EETUQ2S271JJ | 1.94 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2S271KJ | 1.94 | 0.15 | 200 |
| | 330 | 25 | 45 | EETUQ2S331JJ | 2.17 | 0.15 | 200 |
| | | 30 | 30 | EETUQ2S331KJ | 2.17 | 0.15 | 200 |
| | | 35 | 25 | EETUQ2S331LJ | 2.17 | 0.15 | 200 |
| | 390 | 25 | 50 | EETUQ2S391JJ | 2.27 | 0.15 | 200 |
| | | 30 | 35 | EETUQ2S391KJ | 2.27 | 0.15 | 100 |
| | | 35 | 30 | EETUQ2S391LJ | 2.27 | 0.15 | 200 |
| | 470 | 30 | 40 | EETUQ2S471KJ | 2.61 | 0.15 | 100 |
| | | 35 | 35 | EETUQ2S471LJ | 2.61 | 0.15 | 100 |
| 560 | 30 | 45 | EETUQ2S561KJ | 2.82 | 0.15 | 100 | |
| | 35 | 40 | EETUQ2S561LJ | 2.82 | 0.15 | 100 | |
| * | 680 | 30 | 50 | EETUQ2S681KC | 3.11 | 0.15 | 100 |
| | | 35 | 45 | EETUQ2S681LJ | 3.11 | 0.15 | 100 |
| * | 820 | 35 | 50 | EETUQ2S821LJ | 3.30 | 0.15 | 100 |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of $\phi 35 \times 45L$ and $\phi 35 \times 50L$ are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)

■ Standard Products

| W.V. (V. DC) | Cap. (120 Hz) (±20 %) (μF) | Case size | | Part No. PET sleeve Terminal Length 4.0 mm (Without Top Plate) | Specification | | Min. Packaging Q'ty (pcs) | |
|-----------------|-------------------------------------|--------------|----------------|--------------------------------------------------------------------------------|---------------------------------------------------------|---------------------------------------|----------------------------------|-----|
| | | Dia. (mm) | Length (mm) | | Ripple Current (120 Hz) (+85 °C) (A r.m.s.) | tan δ (120 Hz) (+20 °C) max. | | |
| 450 | 82 | 22 | 25 | EETUQ2W820HJ | 0.83 | 0.15 | 200 | |
| | 100 | 22 | 25 | EETUQ2W101HJ | 0.93 | 0.15 | 200 | |
| | 120 | 22 | 30 | EETUQ2W121HJ | 1.04 | 0.15 | 200 | |
| | 150 | 150 | 22 | 30 | EETUQ2W151HC | 1.19 | 0.15 | 200 |
| | | | 22 | 35 | EETUQ2W151HJ | 1.19 | 0.15 | 200 |
| | | | 25 | 25 | EETUQ2W151JC | 1.19 | 0.15 | 200 |
| | | | 25 | 30 | EETUQ2W151JJ | 1.19 | 0.15 | 200 |
| | 180 | 180 | 22 | 35 | EETUQ2W181HC | 1.35 | 0.15 | 200 |
| | | | 22 | 40 | EETUQ2W181HJ | 1.35 | 0.15 | 200 |
| | | | 25 | 30 | EETUQ2W181JJ | 1.35 | 0.15 | 200 |
| | 220 | 220 | 22 | 45 | EETUQ2W221HJ | 1.55 | 0.15 | 200 |
| | | | 25 | 35 | EETUQ2W221JC | 1.55 | 0.15 | 200 |
| | | | 25 | 40 | EETUQ2W221JJ | 1.55 | 0.15 | 200 |
| | | | 30 | 25 | EETUQ2W221KC | 1.55 | 0.15 | 200 |
| | | | 30 | 30 | EETUQ2W221KJ | 1.55 | 0.15 | 200 |
| | | | 35 | 25 | EETUQ2W221LJ | 1.55 | 0.15 | 200 |
| | 270 | 270 | 22 | 50 | EETUQ2W271HJ | 1.78 | 0.15 | 200 |
| | | | 25 | 40 | EETUQ2W271JJ | 1.78 | 0.15 | 200 |
| | | | 30 | 30 | EETUQ2W271KJ | 1.78 | 0.15 | 200 |
| | | | 35 | 25 | EETUQ2W271LC | 1.78 | 0.15 | 200 |
| | 330 | 330 | 25 | 45 | EETUQ2W331JC | 2.01 | 0.15 | 200 |
| | | | 25 | 50 | EETUQ2W331JJ | 2.01 | 0.15 | 200 |
| | | | 30 | 35 | EETUQ2W331KC | 2.01 | 0.15 | 100 |
| | | | 30 | 40 | EETUQ2W331KJ | 2.01 | 0.15 | 100 |
| | | | 35 | 30 | EETUQ2W331LJ | 2.01 | 0.15 | 200 |
| | 390 | 390 | 30 | 40 | EETUQ2W391KJ | 2.24 | 0.15 | 100 |
| | | | 35 | 30 | EETUQ2W391LC | 2.24 | 0.15 | 200 |
| | | | 35 | 35 | EETUQ2W391LJ | 2.24 | 0.15 | 100 |
| | 470 | 470 | 30 | 45 | EETUQ2W471KJ | 2.53 | 0.15 | 100 |
| | | | 35 | 35 | EETUQ2W471LC | 2.53 | 0.15 | 100 |
| 35 | | | 40 | EETUQ2W471LJ | 2.53 | 0.15 | 100 | |
| 560 | 560 | 30 | 50 | EETUQ2W561KJ | 2.82 | 0.15 | 100 | |
| | | 35 | 40 | EETUQ2W561LC | 2.82 | 0.15 | 100 | |
| * | | 35 | 45 | EETUQ2W561LJ | 2.82 | 0.15 | 100 | |
| * | 680 | 35 | 45 | EETUQ2W681LC | 3.00 | 0.15 | 100 | |

Endurance : 85 °C 2000 h, Terminal Pitch : 10 mm

* When capacitors of φ35×45L and φ35×50L are mounted on PWB, reinforce them with mounting clamp or adhesives.
(Avoid using adhesives including halogenated compositions.)