



Safety Data Sheet

According to Regulation (EC) No. 1907/2006
OSHA Regulation 29 CFR 1910.1200
Canadian Regulation SOR/88-66

Revision Date: 2012-06-01
Reason for Revision: Reviewed Only

SECTION 1: IDENTIFICATION OF THE PRODUCT AND COMPANY

Product Name: HI 70031 Conductivity Solution

Additional Product Codes: HI 70031C
HI 70031P

Application: For Calibrating Electrodes

Company Information (USA):

Hanna Instruments, Inc.
584 Park East Dr, Woonsocket, Rhode Island, USA 02895

Technical Service Contact Information:

1-800-426-6287 (8:30AM - 5:00PM ET)
+1-401-766-4260 (8:30AM - 5:00PM ET)

USA Emergency Contact Information:

1-800-424-9300 (Chemtrec 24Hr. Emergency)

International Emergency Contact Information:

+1-703-527-3887 (Chemtrec 24Hr. Emergency)

E-mail Address:

tech@hannainst.com

SECTION 2: HAZARD IDENTIFICATION

Non-hazardous product as specified in Directives 67/548/EEC and 1999/45/EC.
Non-hazardous product as specified in OSHA Regulation 29 CFR 1910.1200.
Non-hazardous product as specified in Canadian Regulation SOR/88-66.

SECTION 3: COMPOSITION AND COMPONENT INFORMATION

Aqueous Solution

SECTION 4: FIRST AID MEASURES

After Inhalation: Remove to fresh air. Call a physician if breathing becomes difficult.

After Skin Contact: Wash affected area with water and soap.

After Eye Contact: Rinse out with plenty of water for at least 15 minutes. If pain persists, summon medical advice.

After Swallowing: Wash out mouth with plenty of water, provided person is conscious. Obtain medical attention if feeling unwell.

General Information: Not available

SECTION 5: FIRE-FIGHTING MEASURES

Suitable Extinguishing Media:

Water Spray, Foam, Dry Powder, Carbon Dioxide

Special Risks:

Non-combustible.

Special Protective Equipment:

Do not stay in dangerous zone without suitable chemical protection clothing and self-contained breathing apparatus.

Additional Information:

Contain escaping vapors with water.

SECTION 6: ACCIDENTAL RELEASE MEASURES

Personal Precautions:

None

Environmental Precautions:

None

Additional Notes:

None

Safety Data Sheet

According to Regulation (EC) No. 1907/2006
OSHA Regulation 29 CFR 1910.1200
Canadian Regulation SOR/88-66

SECTION 7: HANDLING AND STORAGE

Handling:

No restrictions

Storage:

Keep container closed and protected from direct sunlight. Store at room temperature (+15°C to +25°C).

SECTION 8: EXPOSURE CONTROL/PERSONAL PROTECTION

Engineering:

Maintain general industrial hygiene practice.

Personal Protective Equipment:

As appropriate to quantity handled.

Respiratory Protection:

Required when vapors/aerosols are generated.

Protective Gloves:

Rubber or plastic

Eye Protection:

Goggles or face mask

Industrial Hygiene:

Change contaminated clothing. Wash hands after working with substance.

SECTION 9: PHYSICAL/CHEMICAL PROPERTIES

Appearance: Colorless liquid

Odor: Odorless

Density at 20°C: ~ 1 g/cm³

Melting Point: NA

Boiling Point: > 100 °C

Solubility: Soluble

pH at 20°C: ~ 7

Explosion Limit: NA

Flash Point: NA

Thermal Decomp.: NA

SECTION 10: STABILITY AND REACTIVITY

Conditions to be Avoided:

Strong Heating (above boiling point). Stable in the recommended storage conditions.

Hazardous Decomposition Products:

In the event of fire: See section 5.

Hazardous Polymerization:

Will not occur.

Substances to be Avoided:

The generally known reaction partners of water

Further Information:

Not available

SECTION 11: TOXICOLOGICAL INFORMATION

Product Toxicity

Quantitative data on the toxicity of this product is not available.

Potential Health Effects:

Further Data: Hazardous properties cannot be excluded, but are relatively unlikely because of the low concentration of the dissolved substances, when the product is handled appropriately. The product should be handled with the usual care when dealing with chemicals.

Component Toxicity

Acute Toxicity:

Not Available

Chronic Toxicity:

Not Available

Additional Data:

Not Available

Safety Data Sheet

According to Regulation (EC) No. 1907/2006
 OSHA Regulation 29 CFR 1910.1200
 Canadian Regulation SOR/88-66

SECTION 12: ECOLOGICAL INFORMATION

Quantitative data on the ecological effect of this product is not available.

Further Data: No ecological problems are to be expected when the product is handled and used with due care and attention.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste Disposal: Can be safely disposed of as ordinary refuse.

SECTION 14: TRANSPORTATION INFORMATION

Land:

Not subject to transport regulations

Sea:

Not subject to transport regulations

Air:

Not subject to transport regulations

SECTION 15: REGULATORY INFORMATION

Labeling according to EC Directives:

Non-hazardous according to Directives 67/548/EEC and 1999/45/EC.

SECTION 16: OTHER INFORMATION

Text of R-phrases under Section 3

NA

Revision Information

Revision Date: 2012-06-01

Supersedes edition of: 2009-06-10

Reason for revision: Reviewed Only

Legend

NA: Not Applicable
 ND: Not Determined

THE INFORMATION CONTAINED HEREIN IS BASED ON THE PRESENT STATE OF OUR KNOWLEDGE. IT CHARACTERIZES THE PRODUCT WITH REGARD TO THE APPROPRIATE SAFETY PRECAUTIONS. IT DOES NOT REPRESENT A GUARANTEE OF THE PROPERTIES OF THE PRODUCT.