1.5V Drive Nch MOSFET

RUF025N02

●Structure

Silicon N-channel MOSFET

● Features

- 1) Low On-resistance.
- 2) Space saving, small surface mount package (TUMT3).
- 3) Low voltage drive (1.5V drive).


Applications

Switching


Packaging specifications

	Package	Taping	
Type	Code	TL	
	Basic ordering unit (pieces)	3000	
RUF025N02	0		

●Dimensions (Unit:mm)



●Inner circuit



● Absolute maximum ratings (Ta=25°C)

Parameter		Symbol	Limits	Unit	
Drain-source voltage		V_{DSS}	20	V	
Gate-source voltage		V _{GSS}	±10	V	
Drain current	Continuous	I_D	±2.5	Α	
Drain current	Pulsed	I _{DP} *1	±5	Α	
Source current	Continuous	Is	0.6	Α	
(Body diode)	Pulsed	I _{SP} *1	5	Α	
Total power dissipation		P _D *2	0.8	W	
Channel temperature		Tch	150	°C	
Range of storage temperature		Tstg	-55 to +150	°C	

^{*1} Pw≤10μs, Duty cycle≤1% *2 Mounted on a ceramic board

Thermal resistance

Parameter	Symbol	Limits	Unit
Channel to ambient	Rth(ch-a)*	156	°C/W

^{*} Mounted on a ceramic board

●Electrical characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Gate-source leakage	I _{GSS}	-	-	±10	μΑ	V _{GS} =±10V, V _{DS} =0V
Drain-source breakdown voltage	V _{(BR) DSS}	20	_	_	V	I _D = 1mA, V _{GS} =0V
Zero gate voltage drain current	IDSS	_	_	1	μΑ	V _{DS} = 20V, V _{GS} =0V
Gate threshold voltage	VGS (th)	0.3	ı	1.3	V	V _{DS} = 10V, I _D = 1mA
Static drain-source on-state resistance	R _{DS} (on)*	-	39	54	mΩ	I _D = 2.5A, V _{GS} = 4.5V
		_	49	68	mΩ	I _D = 2.5A, V _{GS} = 2.5V
		_	65	91	mΩ	I _D = 1.3A, V _{GS} = 1.8V
		_	80	160	mΩ	ID= 0.5A, VGS= 1.5V
Forward transfer admittance	Y _{fs} *	3.6	_	_	S	V _{DS} = 10V, I _D = 2.5A
Input capacitance	Ciss	-	370	_	pF	V _{DS} = 10V
Output capacitance	Coss	_	90	_	pF	V _{GS} =0V
Reverse transfer capacitance	Crss	_	50	_	pF	f=1MHz
Turn-on delay time	t _{d (on)} *	_	7	_	ns	ID= 1.3A
Rise time	tr *	_	15	_	ns	VDD≒ 10V
Turn-off delay time	td (off) *	-	35	_	ns	V _{GS} = 4.5V R _L =7.7Ω
Fall time	t _f *	_	15	-	ns	R _G =10Ω
Total gate charge	Qg *	_	5	-	nC	I _D = 2.5A, V _{DD} ≒ 10V
Gate-source charge	Q _{gs} *	_	0.9	_	nC	V _{GS} = 4.5V
Gate-drain charge	Q _{gd} *	1	0.8	_	nC	RL≒4Ω, R _G =10Ω

^{*}Pulsed

●Body diode characteristics (Source-drain) (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Forward voltage	Vsp *	_	_	1.2	V	Is= 0.6A, V _{GS} =0V

^{*}Pulsed

•Electrical characteristics curves




Fig.1 Typical Capacitance vs. Drain-Source Voltage




Fig.2 Switching Characteristics




Fig.3 Dynamic Input Characteristics




Fig.4 Typical Transfer Characteristics




Fig.5 Static Drain-Source On-State Resistance vs. Gate-Source Voltage




Fig.6 Source Current vs. Source-Drain Voltage




Fig.7 Static Drain-Source On-State Resistance vs. Drain Current (I)




Fig.8 Static Drain-Source On-State Resistance vs. Drain Current (II)





Fig.9 Static Drain-Source On-State Resistance vs. Drain Current(III)



●Measurement circuit




Fig.13 Switching Time Measurement Circuit




Fig.14 Switching Waveforms




Fig.15 Gate Charge Measurement Circuit




Fig.16 Gate Charge Waveform

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any
 means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the
 product described in this document are for reference only. Upon actual use, therefore, please request
 that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard
 use and operation. Please pay careful attention to the peripheral conditions when designing circuits
 and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or
 otherwise dispose of the same, no express or implied right or license to practice or commercially
 exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

It is our top priority to supply products with the utmost quality and reliability. However, there is always a chance of failure due to unexpected factors. Therefore, please take into account the derating characteristics and allow for sufficient safety features, such as extra margin, anti-flammability, and fail-safe measures when designing in order to prevent possible accidents that may result in bodily harm or fire caused by component failure. ROHM cannot be held responsible for any damages arising from the use of the products under conditions out of the range of the specifications or due to non-compliance with the NOTES specified in this catalog.

Thank you for your accessing to ROHM product informations.

More detail product informations and catalogs are available, please contact your nearest sales office.

ROHM Customer Support System

THE AMERICAS / EUROPE / ASIA / JAPAN

www.rohm.com

Contact us : webmaster@rohm.co.jp

Copyright © 2008 ROHM CO.,LTD.

ROHM CO., LTD. 21 Saiin Mizosaki-cho, Ukyo-ku, Kyoto 615-8585, Japan

FAX:+81-75-315-0172

TEL:+81-75-311-2121

