

NCS2004

3.5 MHz, Wide Supply, Rail-to-Rail Output Operational Amplifier

The NCS2004 operational amplifier provides rail-to-rail output operation. The output can swing within 70 mV to the positive rail and 30 mV to the negative rail. This rail-to-rail operation enables the user to make optimal use of the entire supply voltage range while taking advantage of 3.5 MHz bandwidth. The NCS2004 can operate on supply voltage as low as 2.5 V over the temperature range of -40°C to 105°C . The high bandwidth provides a slew rate of $2.4\text{ V}/\mu\text{s}$ while only consuming a typical $390\ \mu\text{A}$ of quiescent current. Likewise the NCS2004 can run on a supply voltage as high as 16 V making it ideal for a broad range of battery operated applications. Since this is a CMOS device it has high input impedance and low bias currents making it ideal for interfacing to a wide variety of signal sensors. In addition it comes in a small SC-88A package allowing for use in high density PCB's.

Features

- Rail-To-Rail Output
- Wide Bandwidth: 3.5 MHz
- High Slew Rate: $2.4\text{ V}/\mu\text{s}$
- Wide Power Supply Range: 2.5 V to 16 V
- Low Supply Current: $390\ \mu\text{A}$
- Low Input Bias Current: 1 pA
- Wide Temperature Range: -40°C to 105°C
- Small Package: 5-Pin SC-88A (same as SC-70-5)
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Notebook Computers
- Portable Instruments




ON Semiconductor®

<http://onsemi.com>



SC-88A
(SC-70-5)
SN SUFFIX
CASE 419A

MARKING DIAGRAM




ADK = Specific Device Code

M = Date Code

▪ = Pb-Free Package

(Note: Microdot may be in either location)

PIN CONNECTIONS



ORDERING INFORMATION

| Device | Package | Shipping† |
|---------------|---------------------|-----------------------|
| NCS2004SQ3T2G | SC-88A (Pb-Free) | 3000 / Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

MAXIMUM RATINGS

| Symbol | Rating | Value | Unit |
|------------------|--|-------------------------------------|------|
| V _{DD} | Supply Voltage | 16.5 | V |
| V _{ID} | Input Differential Voltage | ± Supply Voltage | V |
| V _I | Input Common Mode Voltage Range | -0.2 V to (V _{DD} + 0.2 V) | V |
| I _I | Maximum Input Current | ± 10 | mA |
| I _O | Output Current Range | ± 100 | mA |
| | Continuous Total Power Dissipation (Note 1) | 200 | mW |
| T _J | Maximum Junction Temperature | 150 | °C |
| θ _{JA} | Thermal Resistance | 333 | °C/W |
| T _{stg} | Operating Temperature Range (free-air) | -40 to 105 | °C |
| T _{stg} | Storage Temperature | -65 to 150 | °C |
| | Mounting Temperature (Infrared or Convection – 20 sec) | 260 | °C |
| V _{ESD} | Machine Model Human Body Model | 300 2000 | V |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. Continuous short circuit operation to ground at elevated ambient temperature can result in exceeding the maximum allowed junction temperature of 150°C. Output currents in excess of 45 mA over long term may adversely affect reliability. Shorting output to either V₊ or V₋ will adversely affect reliability.

DC ELECTRICAL CHARACTERISTICS (V_{DD} = 2.5 V, 3.3 V, 5 V and ±5 V, T_A = 25°C, R_L ≥ 10 kΩ unless otherwise noted)

| Parameter | Symbol | Conditions | Min | Typ | Max | Unit |
|----------------------------------|-------------------|--|-------------------------|-----|------|-------|
| Input Offset Voltage | V _{IO} | VIC = V _{DD} /2, V _O = V _{DD} /2, R _L = 10 kΩ, R _S = 50 Ω | | 0.5 | 5.0 | mV |
| | | T _A = -40°C to +105°C | | | 7.0 | |
| Offset Voltage Drift | ICV _{OS} | VIC = V _{DD} /2, V _O = V _{DD} /2, R _L = 10 kΩ, R _S = 50 Ω | | 2.0 | | μV/°C |
| Common Mode Rejection Ratio | CMRR | 0 V ≤ VIC ≤ V _{DD} - 1.35 V, R _S = 50 Ω | V _{DD} = 2.5 V | 55 | 94 | dB |
| | | T _A = -40°C to +105°C | | 52 | | |
| | | 0 V ≤ VIC ≤ V _{DD} - 1.35 V, R _S = 50 Ω | V _{DD} = 5 V | 65 | 130 | |
| | | T _A = -40°C to +105°C | | 62 | | |
| | | 0 V ≤ VIC ≤ V _{DD} - 1.35 V, R _S = 50 Ω | V _{DD} = ±5 V | 69 | 140 | |
| T _A = -40°C to +105°C | 66 | | | | | |
| Power Supply Rejection Ratio | PSRR | V _{DD} = 2.5 V to 16 V, VIC = V _{DD} /2, No Load | 70 | 135 | | dB |
| | | T _A = -40°C to +105°C | 65 | | | |
| Large Signal Voltage Gain | A _{VD} | V _{O(pp)} = V _{DD} /2, R _L = 10 kΩ | V _{DD} = 2.5 V | 90 | 130 | dB |
| | | T _A = -40°C to +105°C | | 76 | | |
| | | V _{O(pp)} = V _{DD} /2, R _L = 10 kΩ | V _{DD} = 3.3 V | 92 | 123 | |
| | | T _A = -40°C to +105°C | | 76 | | |
| | | V _{O(pp)} = V _{DD} /2, R _L = 10 kΩ | V _{DD} = 5 V | 95 | 127 | |
| | | T _A = -40°C to +105°C | | 86 | | |
| | | V _{O(pp)} = V _{DD} /2, R _L = 10 kΩ | V _{DD} = ±5 V | 95 | 130 | |
| T _A = -40°C to +105°C | 90 | | | | | |
| Input Bias Current | I _B | V _{DD} = 5 V, VIC = V _{DD} /2, V _O = V _{DD} /2, R _S = 50 Ω | T _A = 25°C | 45 | 150 | pA |
| | | T _A = 105°C | | | 1000 | |

NCS2004

DC ELECTRICAL CHARACTERISTICS ($V_{DD} = 2.5\text{ V}, 3.3\text{ V}, 5\text{ V}$ and $\pm 5\text{ V}$, $T_A = 25^\circ\text{C}$, $R_L \geq 10\text{ k}\Omega$ unless otherwise noted)

| Parameter | Symbol | Conditions | Min | Typ | Max | Unit | |
|-------------------------------|------------|--|---------------------------|------|------|------------|----|
| Input Offset Current | I_{IO} | $V_{DD} = 5\text{ V}$, $V_{IC} = V_{DD}/2$, $V_O = V_{DD}/2$, $R_S = 50\ \Omega$ | $T_A = 25^\circ\text{C}$ | | 45 | 150 | pA |
| | | | $T_A = 105^\circ\text{C}$ | | | 1000 | |
| Differential Input Resistance | $r_{i(d)}$ | | | 1000 | | G Ω | |
| Common-mode Input Capacitance | C_{IC} | $f = 21\text{ kHz}$ | | 8.0 | | pF | |
| Output Swing (High-level) | V_{OH} | $V_{IC} = V_{DD}/2$, $I_{OH} = -1\text{ mA}$ | $V_{DD} = 2.5\text{ V}$ | 2.35 | 2.43 | | V |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 2.28 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -1\text{ mA}$ | $V_{DD} = 3.3\text{ V}$ | 3.15 | 3.21 | | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 3.00 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -1\text{ mA}$ | $V_{DD} = 5\text{ V}$ | 4.8 | 4.93 | | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 4.75 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -1\text{ mA}$ | $V_{DD} = \pm 5\text{ V}$ | 4.92 | 4.96 | | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 4.9 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -5\text{ mA}$ | $V_{DD} = 2.5\text{ V}$ | 1.7 | 2.14 | | V |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 1.5 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -5\text{ mA}$ | $V_{DD} = 3.3\text{ V}$ | 2.5 | 2.89 | | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 2.1 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -5\text{ mA}$ | $V_{DD} = 5\text{ V}$ | 4.5 | 4.68 | | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 4.35 | | | |
| | | $V_{IC} = V_{DD}/2$, $I_{OH} = -5\text{ mA}$ | $V_{DD} = \pm 5\text{ V}$ | 4.7 | 4.78 | | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 4.65 | | | |
| Output Swing (Low-level) | V_{OL} | $V_{IC} = V_{DD}/2$, $I_{OL} = -1\text{ mA}$ | $V_{DD} = 2.5\text{ V}$ | | 0.03 | 0.15 | V |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 0.22 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -1\text{ mA}$ | $V_{DD} = 3.3\text{ V}$ | | 0.03 | 0.15 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 0.22 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -1\text{ mA}$ | $V_{DD} = 5\text{ V}$ | | 0.03 | 0.1 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 0.15 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -1\text{ mA}$ | $V_{DD} = \pm 5\text{ V}$ | | 0.05 | 0.08 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 0.1 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -5\text{ mA}$ | $V_{DD} = 2.5\text{ V}$ | | 0.15 | 0.7 | V |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 1.1 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -5\text{ mA}$ | $V_{DD} = 3.3\text{ V}$ | | 0.13 | 0.7 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 1.1 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -5\text{ mA}$ | $V_{DD} = 5\text{ V}$ | | 0.13 | 0.4 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 0.5 | |
| | | $V_{IC} = V_{DD}/2$, $I_{OL} = -5\text{ mA}$ | $V_{DD} = \pm 5\text{ V}$ | | 0.16 | 0.3 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | | 0.35 | |

NCS2004

DC ELECTRICAL CHARACTERISTICS ($V_{DD} = 2.5\text{ V}, 3.3\text{ V}, 5\text{ V}$ and $\pm 5\text{ V}$, $T_A = 25^\circ\text{C}$, $R_L \geq 10\text{ k}\Omega$ unless otherwise noted)

| Parameter | Symbol | Conditions | Min | Typ | Max | Unit | |
|--------------------------------|----------|---|-------------------------|-----|------|------|---------------|
| Output Current | I_O | $V_O = 0.5\text{ V}$ from rail, $V_{DD} = 2.5\text{ V}$ | Positive rail | | 4.0 | | mA |
| | | | Negative rail | | 5.0 | | |
| | | $V_O = 0.5\text{ V}$ from rail, $V_{DD} = 5\text{ V}$ | Positive rail | | 7.0 | | |
| | | | Negative rail | | 8.0 | | |
| | | $V_O = 0.5\text{ V}$ from rail, $V_{DD} = 10\text{ V}$ | Positive rail | | 13 | | |
| | | | Negative rail | | 12 | | |
| Power Supply Quiescent Current | I_{DD} | $V_O = V_{DD}/2$ | $V_{DD} = 2.5\text{ V}$ | | 380 | 560 | μA |
| | | | $V_{DD} = 3.3\text{ V}$ | | 385 | 620 | |
| | | | $V_{DD} = 5\text{ V}$ | | 390 | 660 | |
| | | | $V_{DD} = 10\text{ V}$ | | 400 | 800 | |
| | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | | 1000 | | |

AC ELECTRICAL CHARACTERISTICS ($V_{DD} = 2.5\text{ V}, 5\text{ V}$, & $\pm 5\text{ V}$, $T_A = 25^\circ\text{C}$, and $R_L \geq 10\text{ k}\Omega$ unless otherwise noted)

| Parameter | Symbol | Conditions | Min | Typ | Max | Unit | |
|--------------------------------------|------------|--|--|---|-------|------------------------------|------------------------|
| Unity Gain Bandwidth | UGBW | $R_L = 2\text{ k}\Omega$, $C_L = 10\text{ pF}$ | $V_{DD} = 2.5\text{ V}$ | | 3.2 | | MHz |
| | | | $V_{DD} = 5\text{ V}$ to 10 V | | 3.5 | | |
| Slew Rate at Unity Gain | SR | $V_{O(pp)} = V_{DD}/2$, $R_L = 10\text{ k}\Omega$, $C_L = 50\text{ pF}$ | $V_{DD} = 2.5\text{ V}$ | | 1.35 | 2.0 | $\text{V}/\mu\text{S}$ |
| | | | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 1 | |
| | | $V_{O(pp)} = V_{DD}/2$, $R_L = 10\text{ k}\Omega$, $C_L = 50\text{ pF}$ | $V_{DD} = 5\text{ V}$ | | 1.45 | 2.3 | |
| | | | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 1.2 | |
| | | $V_{O(pp)} = V_{DD}/2$, $R_L = 10\text{ k}\Omega$, $C_L = 50\text{ pF}$ | $V_{DD} = \pm 5\text{ V}$ | | 1.8 | 2.6 | |
| | | | | $T_A = -40^\circ\text{C}$ to $+105^\circ\text{C}$ | | 1.3 | |
| Phase Margin | θ_m | $R_L = 2\text{ k}\Omega$, $C_L = 10\text{ pF}$ | | 45 | | $^\circ$ | |
| Gain Margin | | $R_L = 2\text{ k}\Omega$, $C_L = 10\text{ pF}$ | | 14 | | dB | |
| Settling Time to 0.1% | t_S | $V\text{-step}(pp) = 1\text{ V}$, $AV = -1$, $R_L = 2\text{ k}\Omega$, $C_L = 10\text{ pF}$ | $V_{DD} = 2.5\text{ V}$ | | 2.9 | | μS |
| | | $V\text{-step}(pp) = 1\text{ V}$, $AV = -1$, $R_L = 2\text{ k}\Omega$, $C_L = 68\text{ pF}$ | $V_{DD} = 5\text{ V}$, $\pm 5\text{ V}$ | | 2.0 | | |
| Total Harmonic Distortion plus Noise | THD+N | $V_{DD} = 2.5\text{ V}$, $V_{O(pp)} = V_{DD}/2$, $R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$ | $AV = 1$ | | 0.004 | | % |
| | | | $AV = 10$ | | 0.04 | | |
| | | | $AV = 100$ | | 0.3 | | |
| | | $V_{DD} = 5\text{ V}$, $\pm 5\text{ V}$, $V_{O(pp)} = V_{DD}/2$, $R_L = 2\text{ k}\Omega$, $f = 10\text{ kHz}$ | $AV = 1$ | | 0.004 | | |
| | | | $AV = 10$ | | 0.04 | | |
| | | | $AV = 100$ | | 0.03 | | |
| Input-Referred Voltage Noise | e_n | $f = 1\text{ kHz}$ | | 30 | | $\text{nV}/\sqrt{\text{Hz}}$ | |
| | | $f = 10\text{ kHz}$ | | 20 | | | |
| Input-Referred Current Noise | i_n | $f = 1\text{ kHz}$ | | 0.6 | | $\text{fA}/\sqrt{\text{Hz}}$ | |




Figure 1. CMRR vs. Frequency




Figure 2. Input Bias and Offset Current vs. Temperature




Figure 3. 2.5 V V_{OL} vs. I_{out}




Figure 4. 2.5 V V_{OH} vs. I_{out}




Figure 5. 3.3 V V_{OL} vs. I_{out}




Figure 6. 3.3 V V_{OH} vs. I_{out}




Figure 7. V_{OL} vs. I_{out}




Figure 8. V_{OH} vs. I_{out}




Figure 9. 10 V V_{OL} vs. I_{out}




Figure 10. 10 V V_{OH} vs. I_{out}




Figure 11. Peak-to-Peak Output vs. Supply vs. Frequency




Figure 12. Supply Current vs. Supply Voltage




Figure 13. PSRR vs. Frequency




Figure 14. Open Loop Gain and Phase vs. Frequency




Figure 15. Gain Bandwidth Product vs. Temperature




Figure 16. Slew Rate vs. Supply Voltage




Figure 17. Slew Rate vs. Temperature




Figure 18. Voltage Noise vs. Frequency




Figure 19. 2.5 V Inverting Large Signal Pulse Response




Figure 20. 2.5 V Non-Inverting Large Signal Pulse Response




Figure 21. 2.5 V Inverting Small Signal Pulse Response






Figure 22. 2.5 V Non-Inverting Small Signal Pulse Response




500 ns/div

Figure 23. 3 V Inverting Large Signal Pulse Response




500 ns/div

Figure 24. 3 V Non-Inverting Large Signal Pulse Response




500 ns/div

Figure 25. 3 V Inverting Small Signal Pulse Response




500 ns/div

Figure 26. 3 V Non-Inverting Small Signal Pulse Response



500 ns/div

Figure 27. 6 V Inverting Large Signal Pulse Response



500 ns/div

Figure 28. 6 V Non-Inverting Large Signal Pulse Response




Figure 29. 6 V Inverting Small Signal Pulse Response




Figure 30. 6 V Non-Inverting Small Signal Pulse Response

APPLICATIONS




Figure 31. Voltage Reference




Figure 32. Wien Bridge Oscillator





Figure 33. Comparator with Hysteresis



Given: f_o = center frequency
 $A(f_o)$ = gain at center frequency

Choose value f_o, C
 Then: $R_3 = \frac{Q}{\pi f_o C}$
 $R_1 = \frac{R_3}{2 A(f_o)}$
 $R_2 = \frac{R_1 R_3}{4Q^2 R_1 - R_3}$


For less than 10% error from operational amplifier,
 $((Q_o f_o)/BW) < 0.1$ where f_o and BW are expressed in Hz.
 If source impedance varies, filter may be preceded with
 voltage follower buffer to stabilize filter parameters.

Figure 34. Multiple Feedback Bandpass Filter

NCS2004

PACKAGE DIMENSIONS

SC-88A (SC-70-5/SOT-353)
CASE 419A-02
ISSUE K



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. 419A-01 OBSOLETE. NEW STANDARD 419A-02.
4. DIMENSIONS A AND B DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.

| DIM | INCHES | | MILLIMETERS | |
|-----|-----------|-------|-------------|------|
| | MIN | MAX | MIN | MAX |
| A | 0.071 | 0.087 | 1.80 | 2.20 |
| B | 0.045 | 0.053 | 1.15 | 1.35 |
| C | 0.031 | 0.043 | 0.80 | 1.10 |
| D | 0.004 | 0.012 | 0.10 | 0.30 |
| G | 0.026 BSC | | 0.65 BSC | |
| H | --- | 0.004 | --- | 0.10 |
| J | 0.004 | 0.010 | 0.10 | 0.25 |
| K | 0.004 | 0.012 | 0.10 | 0.30 |
| N | 0.008 REF | | 0.20 REF | |
| S | 0.079 | 0.087 | 2.00 | 2.20 |

ON Semiconductor and are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com
Order Literature: <http://www.onsemi.com/orderlit>
For additional information, please contact your local Sales Representative