

Cable and Wire

MC55 181616 Series

pro-POWER



Features:

- 18 AWG (16 / 0.254 mm) tinned copper
- Heat resisting PVC insulated

Specifications:

Conductors

16 AWG (26 / 0.254 mm) tinned annealed copper bunch
Minimum Cross-Sectional Area : 0.82 mm²

Insulation

PVC Compound Meeting the Requirement of Class 43 PVC and Class 28

Minimum Average Thickness : 0.38 mm

Nominal Overall Diameter : 2.01 mm

Lay Up : Not Applicable

Screen : Not Applicable

Sheath : Not Applicable

Part Number Table

Description	Part Number
Wire, Black, 16 / 30 AWG, 305 m	MC55 181616 BLK
Wire, Blue, 16 / 30 AWG, 305 m	MC55 181616 BLU
Wire, Red, 16 / 30 AWG, 305 m	MC55 181616 RED

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

pro-POWER