433 / 868MHz Antenna

PUK Dual Band Antenna

Features

- Omni directional Antenna
- Low Profile Package
- Rugged Screw Fix Mount
- 50Ω Impedance
- 1.5metres RG174 Cable
- SMA Male Connector
- M14 Screw Fix connector
- ABS / Rubber Housing
- Operates from $-35 \text{ to} + 85^{\circ}\text{C}$



Applications

- . General Low Power Radio
- M2M Applications
- Telemetry

A Rugged antenna for demanding applications. This antenna provides operation at both 433 and 868MHz with 2dBi gain. Housed in a rugged low profile ABS, this antenna is compact and resistant to Vandalism.

Ordering Information


PART No	Description
ANT-PUKDB	Miniature Puck Antenna






ANT-PUKDB Antenna






Performance Data — VSWR



www.rfsolutions.co.uk

ANT-PUKDB Antenna

Performance Data — RETURN LOSS



White the information in this document is believed to be correct at the on issue, RF Solutions Ltd ubes not accept any induity whatsoever for its accuracy, adequacy or completeness. No express or implied warranty or representation is given relating to the information contained in this document. RF Solutions Ltd reserves the right to make changes and improvements to the product(s) described herein without notice. Buyers and other users should determine for themselves the suitability of any such information or products for their own particular requirements or specification(s). RF Solutions Ltd shall not be liable for any loss or damage caused as a result of user's own determination of how to deploy or use RF Solutions Ltd's products. Use of RF Solutions Ltd products or components in life support and/or safety applications is not authorised except with express written approval. No licences are created, implicitly or otherwise, under any of RF Solutions Ltd's intellectual property rights. Liability for loss or damage resulting or caused by reliance on the information contained herein or from the use of the product (including liability resulting from negligence or where RF Solutions Ltd was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict RF Solutions Ltd's liability for death or personal injury resulting from its negligence.

'n

www.rfsolutions.co.uk

RF Solutions Ltd

Unit 21 Cliffe Industrial Estate, Lewes, East Sussex, United Kingdom, BN8 6JL Tel. Sales: +44 (0)1273 898 000 • Tech. Support: +44 (0)1273 898 007