



Introducing Mini SAS HD Interconnect

TE's Mini SAS HD receptacle assembly is the next-generation SAS high-density high-speed IO interface. This interface was adopted for the SAS 2.1 standard and proposed for SAS 3.0 standard, and is designed to support 6G and future 12G SAS applications. The assembly is offered in 4x, 8x, and 16x versions. The reduced size of the Mini SAS HD system provides additional space for system designers. While a low profile PCIe card can accept four 4x Mini SAS connectors, it can only accept two of Mini SAS connectors.

The passive Mini SAS HD copper cable assembly is designed for broadband operation optimized for 6 and 12 Gbps. The EEPROM signature enables the host to identify what type and length of cable is connected to its port, and can be customized for any application. An improved latch design reduces the insertion force and increases the retention force. MADISON CABLE brand TurboTwin bulk cable and the dual 4 pair cable exit backshell provide flexibility for routing.

KEY FEATURES

- SFF-8644 and SAS 2.1 compliant and capable for SAS 3.0
- Broad band design for 6 and 12Gbps
- Board receptacle assembly provide 1x1(4x), 1x2(8x) and 1x4(16x) configuration
- Pre-assembled, one piece connector and cage assembly offers one-step placement to the board
- Lightpipe option available
- REACH and RoHS compliant
- Improved cable latch design
- Enhanced EMI skirt design
- Scalable 4x and 8x cable plug options
- 26, 28, and 30 AWG bulk cable

**APPLICATIONS**

- Serial Attached SCSI (SAS 2.1)
- Serial data transmission
- HBA (Host Bus Adapter)
- RAID (Redundant Arrays of Inexpensive Disks)
- Workstations
- Rack-mount server
- Servers
- Storage rack
- High performance computer
- Switches

ELECTRICAL

- Connector signal integrity performance meets requirements of current SAS 2.1 at 6Gbps, and capable of compliance with SAS 3.0 at 12Gbps
- Voltage rating: 120 volts AC
- Current rating: Signal application only
- Cable assemblies are fully compliant to SAS 2.1 and SFF-8449 HD management interface

MECHANICAL

- Plug insertion force: 100N Max
- Plug extraction force: 50N Max
- Latch retention: 133.5N Min
- Durability: 250 cycles
- Cable backshell is fully compliant to the SFF-8644 mini-multilane interface specification
- Cable construction consists of 8 differential pairs bundled as 2 cables with 4 pairs in each cable

MATERIALS**Connector**

- Receptacle housing: LCP
- Shield assembly: Nickel Silver
- Contacts: Copper Alloy
- EMI Spring: Copper Alloy
- Threaded nut: Brass
- Chicklets: LCP

Cable Assembly

- PCB paddle card interface
- 30 m gold plated contact pads
- Tin plated zinc diecast backshells
- Tin over nickel plated copper alloy EMI spring

TECHNICAL DOCUMENTS

- Product Specification — 108-2462
- Application Specification — 114-13316

INDUSTRY STANDARDS

- SAS 2.1
- SFF-8644

MINI SAS HD PART NUMBER CHART


TE Part No.	Product Description
2149027-1	Mini SAS HD 1x1 Receptacle Assembly
2149966-1	Mini SAS HD 1x2 Receptacle Assembly
2149375-1	Mini SAS HD 1x4 Receptacle Assembly
2198484-1	Mini SAS HD 1X1 Receptacle Assy W/LP
2198483-1	Mini SAS HD 1x2 Receptacle Assy w/ LP
2180736-1	Mini SAS HD 1x4 Receptacle Assy w/ LP

PRODUCT OFFERING


Mini SAS HD Direct Attach Copper Cable Assembly Part Number Selection Guide					
Base P/N	Description	Data Rate	AWG	Minimum Cable Length	Maximum Cable Length
2202501-1 thru -8	4x Passive Mini SAS HD	6/12 Gbps	26	0.5m	7m
2202502-1 thru -6	4x Passive Mini SAS HD	6/12 Gbps	28	0.5m	5m
2202503-1 thru -4	4x Passive Mini SAS HD	6/12 Gbps	30	0.5m	3m
2202504-1 thru -8	8x Passive Mini SAS HD	6/12 Gbps	26	0.5m	7m
2202505-1 thru -6	8x Passive Mini SAS HD	6/12 Gbps	28	0.5m	5m
2202506-1 thru -4	8x Passive Mini SAS HD	6/12 Gbps	30	0.5m	3m
2202507-1 thru -8	4x Passive Mini SAS HD Hybrid	6 Gbps	26	0.5m	7m
2202508-1 thru -6	4x Passive Mini SAS HD Hybrid	6 Gbps	28	0.5m	5m
2202509-1 thru -4	4x Passive Mini SAS HD Hybrid	6 Gbps	30	0.5m	3m

CABLE ASSEMBLY REPRESENTATIVE DRAWING

L = Length



CONNECTOR REPRESENTATIVE DRAWING



FOR MORE INFORMATION

TE Technical Support Center

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

Part numbers in this brochure are RoHS Compliant*, unless marked otherwise.

*as defined www.te.com/leadfree

te.com

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All Rights Reserved.

7-1773461-9 CIS LUG PDF 03/2012

MADISON CABLE, TurboTwin, TE Connectivity and the TE connectivity (logo) are trademarks. Other logos, product and/or company names might be trademarks of their respective owners.

EEPROM is a trademark of NEC Electronics Corporation.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

