

### SUBMINIATURE SOLID STATE LAMP

Part Number: KM2520SGD09 Super Bright Green


### **Features**

- Subminiature package.
- Z-bend lead.
- Long life solid state reliability.
- Low package profile.
- Moisture sensitivity level : level 3.
- Package: 1000pcs / reel.
- RoHS compliant.


### Description


The Super Bright Green source color devices are made with Gallium Phosphide Green Light Emitting Diode.

### **Package Dimensions**









### Notes:

SPEC NO: DSAA5684

APPROVED: WYNEC

- All dimensions are in millimeters (inches).
   Tolerance is ±0.25(0.01") unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.
- 4. The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
- 5. The device has a single mounting surface. The device must be mounted according to the specifications.

**REV NO: V.10B** 

CHECKED: Allen Liu

DATE: MAY/03/2012 PAGE: 1 OF 5 DRAWN: C.H.Han ERP: 1202000647

### **Selection Guide**

Part No.	Dice	Lens Type	Lens Type Iv (mcd) [2] @ 20mA		Viewing Angle [1]
			Min.	Тур.	201/2
KM2520SGD09	Super Bright Green (GaP)	Green Diffused	5	12	40°

### Notes:

- $1. \theta 1/2$  is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
- Luminous intensity/ luminous Flux: +/-15%.
   Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

## Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Green	565		nm	IF=20mA
λD [1]	Dominant Wavelength	Super Bright Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Green	30		nm	IF=20mA
С	Capacitance	Super Bright Green	15		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Super Bright Green	2.2	2.5	V	I=20mA
lR	Reverse Current	Super Bright Green		10	uA	V <sub>R</sub> =5V

### Notes:


- 1.Wavelength: +/-1nm. 2. Forward Voltage: +/-0.1V.
- 3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

### Absolute Maximum Ratings at TA=25°C

arameter Super Bright Green		Units	
Power dissipation	62.5	mW	
DC Forward Current	25	mA	
Peak Forward Current [1]	140	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		


Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAA5684 **REV NO: V.10B** DATE: MAY/03/2012 PAGE: 2 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: C.H.Han ERP: 1202000647





RELATIVE INTENSITY Vs. WAVELENGTH


### Super Bright Green KM2520SGD09











SPATIAL DISTRIBUTION


 SPEC NO: DSAA5684
 REV NO: V.10B
 DATE: MAY/03/2012
 PAGE: 3 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: C.H.Han
 ERP: 1202000647

### KM2520SGD09

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.

  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.


  3.Number of reflow process shall be 2 times or less.


**Recommended Soldering Pattern** (Units: mm; Tolerance: ± 0.1)



**Tape Dimensions** (Units : mm)

### **Reel Dimension**






SPEC NO: DSAA5684 **REV NO: V.10B** DATE: MAY/03/2012 PAGE: 4 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: C.H.Han ERP: 1202000647

20K / 56# BOX

# PACKING & LABEL SPECIFICATIONS USER DIRECTION OF FEED LABEL 1,000pcs / Reel 1 Reel / Bag OUTSIDE LABEL Kingbright Kingbright



SPEC NO: DSAA5684 APPROVED: WYNEC REV NO: V.10B CHECKED: Allen Liu DATE: MAY/03/2012 DRAWN: C.H.Han

10K / 55# Box

PAGE: 5 OF 5 ERP: 1202000647