



GP1001 THRU GP1007

10.0 AMPS. Glass Passivated Rectifiers



Voltage Range
50 to 1000 Volts
Current
10.0 Amperes



Features

- ◇ Low forward voltage drop
- ◇ High current capability
- ◇ High reliability
- ◇ High surge current capability

Mechanical Data

- ◇ Cases: TO-220 molded plastic
- ◇ Epoxy: UL 94V-0 rate flame retardant
- ◇ Terminals: Leads solderable per MIL-STD-202, Method 208 guaranteed
- ◇ Polarity: As marked
- ◇ High temperature soldering guaranteed: 260°C/10 seconds .16", (4.06mm) from case.
- ◇ Weight: 2.24 grams

TO-220



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60 Hz, resistive or inductive load.
For capacitive load, derate current by 20%

Type Number	Symbol	GP 1001	GP 1002	GP 1003	GP 1004	GP 1005	GP 1006	GP 1007	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current .375"(9.5mm) Lead Length @ $T_c = 100^\circ C$	$I_{(AV)}$	10.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	125							A
Maximum Instantaneous Forward Voltage @ 5.0A	V_F	1.1							V
Maximum DC Reverse Current @ $T_c=25^\circ C$ at Rated DC Blocking Voltage	I_R	5.0							uA
Typical Junction Capacitance (Note 1)	C_j	30							pF
Typical Thermal Resistance (Note 2)	$R_{\theta JC}$	3.0							$^{\circ}C/W$
Operating and Storage Temperature Range	T_J, T_{STG}	- 65 to + 150							$^{\circ}C$

Notes: 1. Measured at 1 MHz and Applied Reverse Voltage of 4.0 Volts D.C.

2. Thermal Resistance from Junction to Case Mounted on Heatsink size 2" x 3" x 0.25" Al-Plate

RATINGS AND CHARACTERISTIC CURVES (GP1001 THRU GP1007)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER LEG




FIG.4- TYPICAL REVERSE CHARACTERISTICS PER LEG




FIG.5- TYPICAL JUNCTION CAPACITANCE

