

**ADDA USA
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
15 X 15 X 6	AD1505MX-K90	HYPRO	5	0.08	0.36	17000	0.15	1.83	23	3	0,6	CE		
20 X 20 X 6	AD2005MX-K70	HYPRO	5	0.1	0.5	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005MB-K70	BALL	5	0.1	0.5	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005LX-K70	HYPRO	5	0.08	0.4	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005LB-K70	BALL	5	0.05	0.25	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2005DX-K70	HYPRO	5	0.05	0.25	7000	1.01	3.59	10.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012MB-K70	BALL	12	0.06	0.72	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012MX-K70	HYPRO	12	0.06	0.72	14000	1.12	4.54	27.1	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012LB-K70	BALL	12	0.06	0.72	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 6	AD2012LX-K70	HYPRO	12	0.05	0.6	10500	1.04	3.9	17	4	0	UL,CUL,TUV,CE	600	12.28
20 X 20 X 10	AD2005MX-G70	HYPRO	5	0.09	0.45	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2005MB-G70	BALL	5	0.07	0.35	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2005LX-G70	HYPRO	5	0.08	0.4	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2005LB-G70	BALL	5	0.06	0.3	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012MX-G70	HYPRO	12	0.05	0.61	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012MB-G70	BALL	12	0.05	0.6	11500	0.62	2.46	20	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012LX-G70	HYPRO	12	0.06	0.72	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
20 X 20 X 10	AD2012LB-G70	BALL	12	0.06	0.7	9000	0.44	1.5	14.8	5	0,6	UL,CUL,TUV,CE	900	17.6
25 X 25 X 6	AD0205MX-K50	HYPRO	5	0.11	0.55	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0205MB-K50	BALL	5	0.08	0.4	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0205LX-K50	HYPRO	5	0.08	0.4	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0205LB-K50	BALL	5	0.05	0.25	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212MX-K50	HYPRO	12	0.07	0.84	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212MB-K50	BALL	12	0.07	0.84	12000	2.62	5.87	27.5	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212LX-K50	HYPRO	12	0.06	0.72	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 6	AD0212LB-K50	BALL	12	0.05	0.6	9000	1.92	3.13	17.6	5	0	UL,CUL,TUV,CE	600	13.6
25 X 25 X 10	AD2005HX-G50	HYPRO	5	0.08	0.65	12000	2.56	6.73	29	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2005MX-G50	HYPRO	5	0.06	0.42	10000	2.14	4.93	26.9	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2005LX-G50	HYPRO	5	0.05	0.25	8000	1.69	3.23	24.1	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2012HX-G50	HYPRO	12	0.09	1.02	12000	2.56	6.73	29	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2012MX-G50	HYPRO	12	0.06	0.68	10000	2.14	4.93	26.9	6	0,6	UL,CUL,TUV,CE	600	15
25 X 25 X 10	AD2012LX-G50	HYPRO	12	0.04	0.5	8000	1.69	3.23	24.1	6	0,6	UL,CUL,TUV,CE	600	15
30 X 30 X 6	AD0305MX-K70	HYPRO	5	0.11	0.55	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0305MB-K70	BALL	5	0.08	0.4	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0305LX-K70	HYPRO	5	0.09	0.45	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0305LB-K70	BALL	5	0.07	0.35	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312MX-K70	HYPRO	12	0.06	0.72	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312MB-K70	BALL	12	0.06	0.72	9000	3.44	3.75	24.8	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312LX-K70	HYPRO	12	0.05	0.65	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 6	AD0312LB-K70	BALL	12	0.05	0.65	7500	2.81	2.76	18.5	6	0	UL,CUL,TUV,CE	400	12.3
30 X 30 X 10	AD0305MX-G50	HYPRO	5	0.12	0.6	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305MB-G50	BALL	5	0.12	0.6	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305LX-G50	HYPRO	5	0.09	0.45	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305LB-G50	BALL	5	0.09	0.45	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305DX-G50	HYPRO	5	0.05	0.25	5500	2.46	1.97	14.6	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0305DB-G50	BALL	5	0.05	0.25	5500	2.46	1.97	14.6	8	0,6	UL,CUL,TUV,CE	400	14

B= Ball H= Hypro S= Sleeve

ADDA USA CORP. ALL RIGHTS RESERVED

All specifications subject to change without notice.

**ADDA USA
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
30 X 30 X 10	AD0312MX-G50	HYPRO	12	0.09	1.08	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0312MB-G50	BALL	12	0.09	1.08	9000	4.52	4.51	28.2	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0312LX-G50	HYPRO	12	0.07	0.84	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
30 X 30 X 10	AD0312LB-G50	BALL	12	0.07	0.84	8000	4	3.81	23.8	8	0,6	UL,CUL,TUV,CE	400	14
35 X 35 X 6	AD3505MX-K70	HYPRO	5	0.11	0.55	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3505MB-K70	BALL	5	0.09	0.45	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3505LX-K70	HYPRO	5	0.1	0.5	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3505LB-K70	BALL	5	0.08	0.4	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512MX-K70	HYPRO	12	0.08	0.96	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512MB-K70	BALL	12	0.08	0.96	8000	5.37	3.5	25.9	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512LX-K70	HYPRO	12	0.06	0.72	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
35 X 35 X 6	AD3512LB-K70	BALL	12	0.06	0.72	6500	4.3	2.45	19.7	7	0	UL,CUL,TUV,CE	400	13
40 X 40 X 6	AD0405HX-K90	HYPRO	5	0.12	0.6	6200	6.39	2.55	25.8	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405HB-K90	BALL	5	0.12	0.6	6800	6.71	2.75	27.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405MX-K90	HYPRO	5	0.09	0.45	5500	5.39	1.87	22.2	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405MB-K90	BALL	5	0.09	0.45	5800	5.59	2.06	23.4	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405LX-K90	HYPRO	5	0.07	0.35	4500	4.26	1.29	16.6	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0405LB-K90	BALL	5	0.07	0.35	4800	4.69	1.46	18.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412HX-K90	HYPRO	12	0.08	0.96	6200	6.39	2.55	25.8	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412HB-K90	BALL	12	0.08	0.96	6800	6.71	2.75	27.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412MX-K90	HYPRO	12	0.07	0.84	5500	5.39	1.87	22.2	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412MB-K90	BALL	12	0.07	0.84	5800	5.59	2.06	23.4	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412LX-K90	HYPRO	12	0.06	0.72	4500	4.26	1.29	16.6	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 6	AD0412LB-K90	BALL	12	0.06	0.72	4800	4.69	1.46	18.3	9	0,6	UL,CUL,TUV,CE	400	13.2
40 X 40 X 10	AD0405HX-G70	HYPRO	5	0.19	0.95	6000	7.11	3.89	27.5	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0405MX-G70	HYPRO	5	0.11	0.55	4200	4.9	1.91	15.9	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0412HX-G70	HYPRO	12	0.1	1.2	6000	7.11	3.89	27.5	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0412MX-G70	HYPRO	12	0.08	1.08	4200	4.9	1.91	15.9	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 10	AD0412LX-G70	HYPRO	12	0.08	0.96	3300	3.43	0.36	14	14	0,6	UL,CUL,TUV,CE	560	32.12
40 X 40 X 15	AD0412HB-D50	BALL	12	0.09	0.99	8000	9.2	7.3	39.3	24	0,6	CE	500	44
40 X 40 X 15	AD0412MB-D50	BALL	12	0.08	0.88	7000	7.5	5.36	31.8	24	0,6	CE	500	44
40 X 40 X 15	AD0412LB-D50	BALL	12	0.07	0.84	6000	6.8	4.03	27.5	24	0,6	CE	500	44
40 X 40 X 20	AD0412HX-C50	H or S	12	0.11	1.32	7500	10	7.83	31.1	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412HB-C50	BALL	12	0.1	1.2	7800	10.5	8.69	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MX-C50	H or S	12	0.08	0.96	6700	9	6.71	27.6	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412MB-C50	BALL	12	0.08	0.96	6900	9.2	6.79	28.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LX-C50	H or S	12	0.07	0.84	6000	7.9	5.14	24.2	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0412LB-C50	BALL	12	0.07	0.84	6200	8.2	5.49	25.2	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HX-C50	H or S	24	0.09	2.16	7500	10	7.83	31.1	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424HB-C50	BALL	24	0.09	2.16	7800	10.5	8.69	31.9	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MX-C50	H or S	24	0.07	1.68	6700	9	6.71	27.6	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424MB-C50	BALL	24	0.07	1.68	6900	9.2	6.79	28.3	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LX-C50	H or S	24	0.06	1.44	6000	7.9	5.14	24.2	28	0,6	UL,CUL,TUV,CE	500	36.96
40 X 40 X 20	AD0424LB-C50	BALL	24	0.06	1.44	6200	8.2	5.49	25.2	28	0,6	UL,CUL,TUV,CE	500	36.96
45 X 45 X 6	AD4505HX-K90	HYPRO	5	0.13	0.67	6300	9.09	2.78	27.6	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505HB-K90	BALL	5	0.16	0.79	6600	9.5	3.02	29.2	10	0,6	Pending	560	19.3

B= Ball H= Hypro S= Sleeve

ADDA USA CORP. ALL RIGHTS RESERVED

All specifications subject to change without notice.

**ADDA USA
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
45 X 45 X 6	AD4505MX-K90	HYPRO	5	0.09	0.44	5300	7.57	2.22	23.2	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505MB-K90	BALL	5	0.1	0.5	5600	8.09	2.39	24.4	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505LX-K90	HYPRO	5	0.06	0.28	4300	6.15	1.5	17.7	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4505LB-K90	BALL	5	0.06	0.31	4600	6.61	1.72	19.1	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512HX-K90	HYPRO	12	0.07	0.83	6300	9.09	2.78	27.6	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512HB-K90	BALL	12	0.07	0.8	6600	9.5	3.02	29.2	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512MX-K90	HYPRO	12	0.06	0.68	5300	7.57	2.22	23.2	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512MB-K90	BALL	12	0.05	0.64	5600	8.09	2.39	24.4	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512LX-K90	HYPRO	12	0.04	0.51	4300	6.15	1.5	17.7	10	0,6	Pending	560	19.3
45 X 45 X 6	AD4512LB-K90	BALL	12	0.04	0.5	4600	6.61	1.72	19.1	10	0,6	Pending	560	19.3
45 X 45 X 10	AD4505HX-G70	HYPRO	5	0.2	1	5000	8.95	3.08	26.8	16	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4505MX-G70	BALL	5	0.16	0.8	4200	7.25	2.56	20.2	16	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512HX-G70	HYPRO	12	0.09	1.08	5000	8.95	3.08	26.8	16	0,6	UL,CUL,TUV,CE	500	24.64
45 X 45 X 10	AD4512MX-G70	BALL	12	0.07	0.84	4200	7.25	2.56	20.2	16	0,6	UL,CUL,TUV,CE	500	24.64
50 X 50 X 8	AD0505LX-J90	HYPRO	5							29		CE	480	31.9
50 X 50 X 8	AD0505MB-J90(S)	1B & 1S	5	0.1	0.5	5200	7.2	0.86	26.5	29		CE	480	31.9
50 X 50 X 10	AD0512MX-G70	HYPRO	12	0.07	0.84	4600	11.03	2.92	25.2	17	0,6	UL,CUL,TUV,CE	560	32.12
50 X 50 X 10	AD0512MB-G70	BALL	12	0.07	0.84	4600	11.03	2.92	25.2	17	0,6	UL,CUL,TUV,CE	560	32.12
50 X 50 X 10	AD0512LX-G70	HYPRO	12	0.06	0.72	3900	9.35	2.09	19.9	17	0,6	UL,CUL,TUV,CE	560	32.12
50 X 50 X 10	AD0512LB-G70	BALL	12	0.06	0.72	3900	9.35	2.09	19.9	17	0,6	UL,CUL,TUV,CE	560	32.12
52 X 52 X 15	AD0505HX-D70	HYPRO	5	0.26	1.3	4600	12	4.22	28.7	37	0,1,2,3,6	CUL,UL,CE	480	46.2
52 X 52 X 15	AD0505MX-D70	HYPRO	5	0.16	0.8	3700	9.7	2.69	22.6	37	0,1,2,3,6	CUL,UL,CE	480	46.2
52 X 52 X 15	AD0512HX-D70	HYPRO	12	0.1	1.2	4600	12	4.22	28.7	37	0,1,2,3,6	CUL,UL,CE	480	46.2
52 X 52 X 15	AD0512MX-D70	HYPRO	12	0.09	1.08	3700	9.7	2.69	22.6	37	0,1,2,3,6	CUL,UL,CE	480	46.2
60 X 60 X 10	AD0605HX-G90	H,S,or X	5	0.28	1.4	4200	16.6	2.88	32.8	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0605MX-G90	H,S,or X	5	0.23	1.15	3600	14.1	2.16	28.5	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0605LX-G90	H,S,or X	5	0.15	0.75	3000	11.9	1.49	23.1	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0612HX-G90	H,S,or X	12	0.14	1.68	4200	16.6	2.88	32.8	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0612MX-G90	H,S,or X	12	0.12	1.44	3600	14.1	2.16	28.5	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 10	AD0612LX-G90	H,S,or X	12	0.11	1.32	3000	11.9	1.49	23.1	27	0,6	UL,CUL,TUV,CE	480	35.5
60 X 60 X 15	AD0605HX-D71GL	H,S,or X	5	0.37	1.85	4500	16.6	3.86	32.4	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0605MX-D71GL	H,S,or X	5	0.25	1.25	3900	14.2	3	28.8	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0605LX-D71GL	H,S,or X	5	0.2	1	3500	13.5	2.3	27.6	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0612HX-D71GL	H,S,or X	12	0.13	1.56	4500	16.6	3.86	32.4	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0612MX-D71GL	H,S,or X	12	0.11	1.32	3900	14.2	3	28.8	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 15	AD0612LX-D71GL	H,S,or X	12	0.06	0.72	3500	13.5	2.3	27.6	39	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	25.7
60 X 60 X 20	AD0605HX-C70GL	H,S,or X	5	0.3	1.5	4500	16.4	3.53	29.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0605MX-C70GL	H,S,or X	5	0.24	1.2	3900	14.5	2.82	25.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0612HX-C70GL	H,S,or X	12	0.16	1.92	4500	16.4	3.53	29.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0612HX-C70GL	H,S,or X	12	0.13	1.56	3900	14.5	2.82	25.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0612MX-C70GL	H,S,or X	12	0.08	0.96	3500	13.3	2.44	21.6	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 20	AD0624HX-C70GL	H,S,or X	24	0.09	2.16	4500	16.4	3.53	29.7	50	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	40
60 X 60 X 25	AD0605MX-A70GL	H,S,or X	5	0.32	1.6	3500	18	3	24	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0605LX-A70GL	H,S,or X	5	0.22	1.1	2500	13.2	16	16.1	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612UX-A70GL	H or S	12	0.25	3	5300	28.3	6.35	37	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612UB-A70GL	BALL	12	0.22	2.64	5300	28.3	6.35	37	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44

B= Ball H= Hypro S= Sleeve

ADDA USA CORP. ALL RIGHTS RESERVED

All specifications subject to change without notice.

ADDA USA
DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAg)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
60 X 60 X 25	AD0612HX-A70GL	H,S,or X	12	0.23	2.76	4500	23.2	4.78	32.3	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612MX-A70GL	H,S,or X	12	0.14	1.68	3500	18	3	24	58	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	300	44
60 X 60 X 25	AD0612LX-A70GL	H,S,or X	12	0.08	0.96	2500	13.2	1.6	16.1	58	0,1,2,3,4,6,7,9	CE	300	44
80 X 80 X 15	AD0805HX-D71	H,S,or X	5	0.43	2.15	3200	29.9	3.28	31.4	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0805MX-D71	H,S,or X	5	0.24	1.2	2440	22.4	2.11	26	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812HX-D71	H,S,or X	12	0.19	2.28	3200	29.9	3.28	31.4	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 15	AD0812MX-D71	H,S,or X	12	0.15	1.8	2440	22.4	2.11	26	65	0,1,3,4,6,7,9,	UL,CUL,TUV,CE	200	32.34
80 X 80 X 20	AD0805HX-C70	H,S,or X	5	0.4	5.16	3010	27.3	3.25	31.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0812HX-C70	H,S,or X	12	0.24	2.88	3010	27.3	3.25	31.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0812MX-C70	H,S,or X	12	0.16	1.92	2440	22.1	2.21	25.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0824HX-C70	H,S,or X	24	0.15	3.6	3010	27.3	3.25	31.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 20	AD0824MX-C70	H,S,or X	24	0.13	3.12	2440	22.1	2.21	25.4	66	0,1,2,3	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812UX-A71GL	H,S,or X	12	0.45	5.4	3900	50	6.81	40.6	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812HX-A70GL	H,S,or X	12	0.25	3	3010	38.6	4.06	34	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812MX-A70GL	H,S,or X	12	0.15	1.8	2440	31.4	2.9	28.3	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812LX-A70GL	H,S,or X	12	0.12	1.44	2030	26.2	1.98	22.5	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812DX-A70GL	H,S,or X	12	0.08	0.96	1600	20.5	1.27	15	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0824UX-A71GL	H,S,or X	24	0.26	6.24	3900	50	7.09	41	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0812HX-A70GL	H,S,or X	24	0.16	3.84	3010	38.6	4.06	34.4	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0824MX-A70GL	H,S,or X	24	0.1	2.4	2440	31.4	2.9	28.3	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
80 X 80 X 25	AD0824LX-A70GL	H,S,or X	24	0.09	2.16	2030	26.2	1.98	22.5	82	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	35.2
92 X 92 X 20	AD0912HX-C70	H,S,or X	12	0.25	3	2740	32.8	2.69	32.8	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 20	AD0912MX-C70	H,S,or X	12	0.16	1.92	2430	29	2.11	28.9	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 20	AD0924HX-C70	H,S,or X	24	0.14	3.36	2740	32.8	2.69	32.8	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 20	AD0924MX-C70	H,S,or X	24	0.1	2.4	2430	29	2.11	28.9	78	0,1,2,3	UL,CUL,TUV,CSA,CE	200	41.3
92 X 92 X 25	AD0912UX-A71GL	H or S	12	0.39	4.68	3200	57.8	3.96	38.6	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912UB-A71GL	BALL	12	0.39	4.68	3200	60	4.15	39.4	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912HX-A70GL	H or S	12	0.25	3	2700	50	2.93	33.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912HB-A70GL	BALL	12	0.25	3	2900	52.5	3.32	35	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912MX-A70GL	H or S	12	0.17	2.04	2400	43.5	2.34	31.3	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912MB-A70GL	BALL	12	0.17	2.04	2600	47.2	2.69	32.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912LX-A70GL	H or S	12	0.12	1.44	2100	37.9	1.87	26.5	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0912LB-A70GL	BALL	12	0.12	1.44	2300	41.6	2.18	29.8	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924UX-A71GL	H or S	24	0.21	5.04	3200	57.8	3.96	38.6	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924UB-A71GL	BALL	24	0.21	5.04	3300	60	4.15	39.4	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924HX-A70GL	H or S	24	0.15	3.6	2700	50	2.93	33.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924HB-A70GL	BALL	24	0.15	3.6	2900	52.5	3.32	35	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924MX-A70GL	H or S	24	0.12	2.88	2400	43.5	2.34	31.3	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924MB-A70GL	BALL	24	0.12	2.88	2600	47.2	2.69	32.7	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924LX-A70GL	H or S	24	0.08	1.92	2100	37.9	1.87	26.5	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
92 X 92 X 25	AD0924LB-A70GL	BALL	24	0.08	1.92	2300	41.6	2.18	29.8	103	0,1,2,3,4,6,7,9	UL,CUL,TUV,CSA,CE	200	52.36
120 X 120 X 25	AD1212UX-A71GL	H,S,or X	12	0.5	6	2500	98.6	4.48	43.3	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212HX-A71GL	H or S	12	0.44	5.28	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212HB-A71GL	BALL	12	0.37	4.44	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212MX-A71GL	H or S	12	0.34	4.08	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1212MB-A71GL	BALL	12	0.33	3.96	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8

B= Ball H= Hypro S= Sleeve

ADDA USA CORP. ALL RIGHTS RESERVED

All specifications subject to change without notice.

**ADDA USA
DC FAN SPECIFICATIONS**

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow	Pressure (mmAq)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
120 X 120 X 25	AD1212LX-A71GL	H,S,or X	12	0.24	2.88	1800	72	2.41	34.4	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224HX-A71GL	H or S	24	0.24	5.76	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224HB-A71GL	BALL	24	0.19	4.56	2200	85.2	3.45	39.1	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224MX-A71GL	H or S	24	0.2	4.8	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224MB-A71GL	BALL	24	0.17	4.08	2050	80.5	2.97	38	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 25	AD1224LX-A71GL	H,S,or X	24	0.14	3.36	1800	72	2.41	34.4	164	1,2,3,4,7,9	UL,CUL,TUV,CSA,CE	90	30.8
120 X 120 X 38	AD1212HB-F51	H,S,or X	12	0.5	6	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212MX-F51	H,S,or X	12	0.35	4.2	2540	94	6.2	41	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1212LX-F51	H,S,or X	12	0.24	2.88	1950	72.3	3.43	32.9	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224UB-F51	H,S,or X	24	0.35	8.4	3200	125.1	9.5	48.1	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HB-F51	BALL	24	0.34	8.16	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1224HX-F51	H or S	24	0.32	7.68	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248HX-F51	H,S,or X	48	0.2	9.6	2800	104.8	6.86	42.8	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248MB-F51	H,S,or X	48	0.14	6.72	2540	94	6.2	41	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66
120 X 120 X 38	AD1248LB-F51	H,S,or X	48	0.1	4.8	1950	72.3	3.43	32.9	320	1,2,3,4,7,8,9,A	UL,CUL,TUV,CSA,CE	40	33.66

<http://www.addausa.com/>

HOME