# **3**M Scotch-Weld<sup>™</sup> **Epoxy Adhesives** DP-100 Clear • DP-100 NS Translucent

Mix Ratio (B:A)

Worklife<sup>2</sup>

Technical Data				June, 2002	
Product Description	3M <sup>™</sup> Scotch-Weld adhesives offering	1 2	sives DP-100 and DP-1 chinability.	00NS are two-part	
	Available in larger or 100 NS B/A.	containers like 3	M <sup>™</sup> Scotch-Weld <sup>™</sup> E	poxy Adhesives 100 B/A	
Features	Easy mixing				
	• High Flow (Scotch-Weld DP-100 Clear)				
	Non-Sag (Scotch-Weld DP-100 NS Translucent)				
	• Fast Cure				
	• Scotch-Weld DP-	-100 meets UL 9	4 HB		
Typical Uncured Physical Properties			nation and data should l be used for specification	be considered representative n purposes.	
Thysical Toperaes			Scotch-Weld DP-100 Clear	Scotch-Weld DP-100 NS Translucent	
	Product		Adhesive	Adhesive	
	Viscosity <sup>1</sup> @ 73°F (23°C)	Base Accelerator	8,000-15,000 cps 9,000-16,000 cps	90,000-150,000 cps 50,000-85,000 cps	
	Base Resin		Ероху	Ероху	
	Color		Clear/Lt. Amber	Translucent	
	Net Weight (Lbs./Gallon)	Base Accelerator	9.5-9.9 9.2-9.6	9.6-10.0 9.2-9.6	

Volume

Weight

10 g mixed @ 73°F (23°C) 1. Viscosity determined using 3M test method C-1d. Procedure involves Brookfield RVF, #6 spindle, 20 rpm and 80°F (27°F).

1:1

5 minutes

1:0.98

1:1

1:0.96

5 minutes (Gel time<sup>3</sup>)

(100 Clear) and #6 spindle, 4 rpm and 80°F (27°F) (100 NS). Measurement taken after 1 minute. 2. Worklife determined using 3M test method C-548. Procedure involves periodically measuring a 10 gram mixed mass for

spreading and wetting properties. This time approximates the usable worklife in an EPX applicator nozzle.

3. Gel time determined using 3M test method C-554. Procedure involves periodically checking a 10 gram mixed mass for flowing properties.

## Scotch-Weld<sup>™</sup> Epoxy Adhesives

DP-100 Clear • DP-100 NS Translucent

#### Typical Cured Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Product	Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive
Physical:		
Color	Translucent	Translucent
Shore D Hardness (ASTM D 2240)	80-85	80-85
Time to Handling Strength <sup>4</sup>	15-20 min. @ 23°C (73°F)	15-20 min. @ 23°C (73°F)
Cure Time <sup>5</sup>	24-48 hours @ 23°C (73°F)	24-48 hours @ 23°C (73°F)

Thermal:		
Wt. loss by Thermal Gravimetric Analysis <sup>6</sup>	5% @ 307°C (585°F)	
Glass Transition Temp <sup>7</sup>	33°C (91°F)	34°C (86°F)
Coefficient of Thermal <sup>8</sup> Expansion (in./in./°C)	60 x 10 <sup>-6</sup> (-40°C to +20°C) (-38°F to +68°F) 209 x 10 <sup>-6</sup> (60°C to 120°C) (+140°F to +248°F)	29 x 10 <sup>-6</sup> (-50°C to +30°C) (-56°F to +86°F) 149 x 10 <sup>-6</sup> (50°C to 110°C) (+122°F to +230°F)
Thermal Conductivity <sup>9</sup> (btu-ft./sq. fthr. °F)	0.107 @ 46°C (115°F)	0.106 @ 45°C (113°F)

Electrical:		
Dielectric Strength (ASTM D 149)	860 volts/mil	1100 volts/mil
Volume Resistivity (ASTM D 257)	3.5 x 10 <sup>12</sup> ohm-cm	2.2 x 10 <sup>14</sup> ohm-cm

4. Handling strength determined per 3M test method C-3179. Time to handling strength is the time required to achieve 50 psi OLS strength to aluminum.

5. The cure time is defined as the time required for the adhesive to achieve a minimum of 80% of its ultimate OLS on aluminum.

Weight loss by Thermal Gravimetric Analysis reported as that temperature at which 5% weight loss occurs by TGA in air at 5°C (41°F) rise per minute per ASTM 1131-86 Test Procedures.

7. Glass transition temperature (Tg) determined using Perkin Elmer (DSC) Analyzer with a heating rate of 20°C (68°F) per minute. Second heat values given.

 Coefficient of thermal expansion determined using DuPont (TMA) using a heating rate of 10°C (50°F) per minute. Second heat values given.

9. Thermal conductivity determined using ASTM C177 and C-matic Instrument with 2 in. diameter samples.

## Scotch-Weld<sup>™</sup> Epoxy Adhesives DP-100 Clear • DP-100 NS Translucent

Handling/Curing Information	1. For optimum strength structural bonds, paint, oxide films, oils, dust, mold release agents and all other surface contaminants must be completely removed. However, the amount of surface preparation directly depends on the required bond strength and the environmental aging resistance desired by user. For specific surface preparations on common substrates, see the following section on Surface Preparation.				
	2. Use gloves to minimize skin contact with adhesive.				
	3. These products consist of two parts.				
	Mixing and Applying				
	For Duo-Pak Cartridges - 50 ml				
	3M <sup>TM</sup> Scotch-Weld <sup>TM</sup> DP-100 and DP-100 NS Adhesives are suppled in a dual syringe plastic Duo-Pak cartridge as part of the 3M <sup>TM</sup> Scotch-Weld <sup>TM</sup> EPX <sup>TM</sup> Applicator system. To use, simply insert the Duo-Pak cartridge into the EPX applicator and start the plunger into the cylinders using light pressure on the trigger. Next, remove the Duo-Pak cartridge cap and expel a small amount of adhesive to be sure both sides of the Duo-Pak cartridge are flowing evenly and freely. If mixing of Part A and Part B is desired, attach the EPX mixing nozzle to the Duo-Pak cartridge and begin dispensing the adhesive. For hand mixing, expel the desired amount of adhesive and mix thoroughly. Mix approximately 15 seconds after uniform color is obtained.				
	For Duo-Pak Cartridges - 200/400 ml				
	<b>Directions for Use:</b> While holding cartridge in an upright position, remove insert from Duo-Pak cartridge by unscrewing plastic nut. Detach metal removal disc from insert to free plastic nut for nozzle attachment. Clear orifices if necessary. Attach mixing nozzle and secure with plastic nut. Place cartridge into EPX Applicator. Dispense a small quantity of adhesive to assure both components are dispensing equally. Apply adhesive to clean surfaces, join parts, secure until set up (20 minutes @ 75°F [24°C]). Leave nozzle attached to store. Replace nozzle after storage.				
	For Bulk Containers				
	Mix thoroughly by weight or volume in the proportions specified in the Typical Uncured Properties section. Mix approximately 15 seconds after uniform color is obtained.				
	4. For maximum bond strength apply adhesive evenly to both surfaces to be joined.				
	5. Application to the substrates should be make within 5 minutes. Larger quantities and/or higher temperatures will reduce this working time.				
	<ol> <li>Join the adhesive coated surfaces and allow to cure at 60°F (16°C) or above until completely firm. Heat, up to 200°F (93°C), will speed curing. These products will fully cure in 24-48 hours @ 75°F (24°C).</li> </ol>				
	7. Keep parts from moving during cure. Contact pressure is necessary. Maximum shear strength is obtained with a 3-5 mil bond line.				
	8. Excess uncured adhesive can be cleaned up with ketone type solvents.*				
	*Note: When using solvents, extinguish all ignition sources and follow the manufacturer's precautions and directions for use.				
	Adhesive Coverage: A 0.005 in. thick bondline will typically yield a coverage of 320 sq. ft./gallon.				

### Scotch-Weld<sup>™</sup> Epoyy Adhesiyes

**Epoxy Adhesives** DP-100 Clear • DP-100 NS Translucent

Surface Preparation	<ul> <li>For optimum strength structural bonds, paint, of agents and all other surface contaminants must amount of surface preparation directly depends environmental aging resistance desired by the The following cleaning methods are suggested Steel:</li> <li>1. Wipe free of dust with oil-free solvent such</li> <li>2. Sandblast or abrade using clean fine grit abia</li> <li>3. Wipe again with solvent to remove loose paints</li> <li>4. If a primer is used, it should be applied with If 3M<sup>TM</sup> Scotch-Weld<sup>TM</sup> Structural Primer (0.5 mils) on the metal surfaces to be bonds for 30 minutes at 180°F (82°C) prior to bords</li> </ul>	be completely removed. However, the s on the required bond strength and the user. for common surfaces: as acetone or isopropyl alcohol.* rasives. as acetone or isopropyl alcohol.* rasives. hin 4 hours after surface preparation. 1945 B/A is used, apply a thin coating ed, air dry for 10 minutes, then cure		
	Aluminum:			
	1. Vapor Degrease: Perchlorethylene condensi	ng vapors for 5-10 minutes.		
	<ol> <li>Alkaline Degrease: Oakite 164 solution (9-11 oz./gallon water) at 190°F ± 10°F (88°C ± 5°C) for 10-20 minutes. Rinse immediately in large quantities of cold running water.</li> <li>Acid Etch: Place panels in the following solution for 10 minutes at 150°F ± 5°F (66°C ± 2°C).</li> </ol>			
	Sodium Dichromate Sulfuric Acid, 66°Be 2024-T3 aluminum (dissolved) Tap Water as needed to balance	4.1 - 4.9 oz./gallon 38.5 - 41.5 oz./gallon 0.2 oz./gallon minimum		
	<ul> <li>4. Rinse: Rinse panels in clear running tap water.</li> <li>5. Dry: Air dry 15 minutes and force dry 10 minutes at 150°F ± 10°F (66°C ± 5°C).</li> <li>6. If primer is to be used, it should be applied within 4 hours after surface preparation.</li> <li>Plastics/Rubber:</li> </ul>			
	1. Wipe with isopropyl alcohol.*			
	2. Abrade using fine grit abrasives.			
	3. Wipe with isopropyl alcohol.*			
	*Note: When using solvents, extinguish all ignition sources and follow the manufacturer's precautions and directions for use.			
Application Equipment Suggestions	For small or intermittent applications the 3M <sup>TM</sup> Scotch-Weld <sup>TM</sup> EPX <sup>TM</sup> applicator is a convenient method of application.			
	For larger applications these adhesives may be applied by use of flow equipment.			
	Two-part meter/mixing/dispensing equipment production line use. These systems may be des size and flow rate characteristics and are adapt	irable because of their variable shot		

## $\textbf{Scotch-Weld}^{{}^{\scriptscriptstyle{\mathsf{TM}}}}$ **Epoxy Adhesives** DP-100 Clear • DP-100 NS Translucent

Typical Adhesive Performance Characteristics	<ul> <li>Note: The following product performance data was obtained in the 3M laboratory under the conditions specified. The following data shows typical results obtained with 3M<sup>TM</sup> Scotch-Weld<sup>TM</sup> Epoxy Adhesives DP-100 and DP-100 NS when applied to properly prepared substrates, cured for 7 days at 73°F (23°C) under 2 psi cure pressure, and tested according to the test methods indicated.</li> <li>The following technical information and data should be considered representative or typical only and should not be used for specification purposes.</li> </ul>				
					A. Overlap Shear Overlap shear (OLS) strengths were measured on 1 in. wide 1/2 in. overlap specimens. These bonds were made individually using 1 in. x 4 in. pieces of substrate except for aluminum. Two panels 0.063 in. thick, 4 in. x 7 in. of 2024 T-3 clad aluminum were bonded and cut into 1 in. wide samples after 24 hours. The thickness of the bond line was 0.005 - 0.008 in. All strengths were measured at 73°F (23°C) except where noted. (Tests per ASTM D 1002-72.)
		The separation rate of the testing jaws was 0.1 in. per minute for metals, 2 in. per minute for plastics and 20 in. per minute for rubbers. The thickness of the substrates were: steel, 0.060 in., other metals, 0.05-0.064 in.; rubbers, 0.125 in.; plastics, 0.125 in.			
	<b>B. T-peel</b> T-peel strengths were measured on 1 in. wide bonds at 73°F (23°C). The testing jaw separation rate was 20 inches per minute. The substrates were 0.032 in. thick. (Tests per ASTM D 1876-61T.)				
	-	aging.	testing or subjecte	ll bonds were cured d to further conditioning	
	Test Temp. °F (°C)		Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive	
	-67°F (-53°C)		900	900	
	73°F (23°C)	vin \1	1500	1500	
	180°F (82°C) (15 min.) <sup>1</sup> 300         300 <sup>1</sup> Represents time in test chamber oven before test.         300         300				
	Metals, Overlap Sh				
			Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive	
	Aluminum-	Etched MEK/abrade/MEK	1500 950	1500 570	
	Cold Rolled Steel- Copper- Brass-	MEK/abrade/MEK MEK/abrade/MEK MEK/abrade/MEK	1000 950 700	890 1140 500	
	Stainless Steel- Galvanized Steel-	MEK/abrade/MEK MEK/abrade/MEK	750 900	840 1080	

### Scotch-Weld<sup>™</sup> Epoxy Adhesives DP-100 Clear • DP-100 NS Translucent

Typical Adhesive<br/>PerformanceNote: The following technical information and data should be considered representative<br/>or typical only and should not be used for specification purposes.Characteristics<br/>(continued)Aluminum, T-peel (piw), tested @ 73°F (23°C) (psi)

		Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive
Aluminum etched	17-20 mil bondline 5-8 mil bondline	2 2	2 2
Cold Rolled Steel	17-20 mil bondline MEK/abrade/MEK	2	2

### Other Substrates, Overlap Shear tested @ 73°F (23°C) (psi)

All cleaned by alcohol wipe, abrade, alcohol wipe.

	Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive
ABS	490	180
PVC	330	240
Polycarbonate	250	120
Polyacrylic	100	150
FRP	950	680
SBR/Steel	125	230
Neoprene/Steel	140	60
Nitrile/Steel	140	90

**Note:** The data shown here was generated using the 3M<sup>TM</sup> Scotch-Weld<sup>TM</sup> EPX<sup>TM</sup> Applicator System equipped with an EPX static mixer according to manufacturer's directions. Thorough hand mixing will afford comparable results.

Rate of Strength Build-Up

Aluminum, Overlap Shear (7 mil Bondline) (psi) Bonds Tested at 73°F (23°C)

Time	Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive
10 minutes	0	200
20 minutes	400	220

Compression Strength (ASTM D 695-68T)

Scotch-Weld DP-100 Clear Adhesive	8400 psi @ 73°F (23°C)
Scotch-Weld DP-100 NS Translucent Adhesive	8400 psi @ 73°F (23°C)

## Scotch-Weld<sup>™</sup> Epoxy Adhesives DP-100 Clear • DP-100 NS Translucent

Typical Adhesive Performance	Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.
Characteristics	Environmental Resistance
(continued)	Aluminum (Etched)

Aluminum (Etched) Measured by Overlap Shear tested 73°F (23°C) psi<sup>1</sup>

Environment	Condition	Scotch-Weld DP-100 Clear Adhesive	Scotch-Weld DP-100 NS Translucent Adhesive
73°F (23°C)/50% RH	30 days	1500	1500
Water Vapor	160°F/100 RH, 3 days	1500	1500

#### Solvent Resistance:<sup>10</sup>

(Visual check after immersion in specified solvent at 73°F [23°C]).

	Scotch-Weld DP-100 Clear Adhesive		Scotch-Weld DP-100 NS Translucent Adhesive	
	1 Hour	1 Month	1 Hour	1 Month
Acetone	A	A	A	A
Isopropyl Alcohol	A	В	A	В
Freon TF	A	A	A	A
Freon TMC	A	A	A	A
1, 1, 1-Trichlorethane	A	В	A	В
RMA Flux	A	A	A	A

Key: A - Unaffected; B - Slight Attack; C - Moderate/Severe Attack

 Viscosity determined using 3M test method C-1d. Procedure involves Brookfield RVF, #6 spindle, 20 rpm and 80°F (27°F). (100 Clear) and #6 spindle, 4 rpm and 80°F (27°F) (100 NS). Measurement taken after 1 minute.

10. Solvent resistance was determined using cured (24 hrs RT + 2 hrs 160°F [71°C]) samples (1/2 in. x 4 in. x 1/8 in. thickness) immersed in the test solvent for 1 hour and 1 month. After the allowed period of time, the sample was removed and visually examined for surface attack as compared to the control.

 $\textbf{Scotch-Weld}^{{}^{\scriptscriptstyle{\mathsf{TM}}}}$ 

**Epoxy Adhesives** DP-100 Clear • DP-100 NS Translucent

Storage and Shelf Life	<b>Storage:</b> Store products at 60-80°F (16-27°C) for maximum storage life. Rotate on "first in-first out" basis.			
	Shelf Life: When stored as recommended in original unopened container, this product has a shelf life of 15 months.			
Precautionary Information	Refer to Product Label and Material Safety Data Sheet for health and safety information before using this product. For additional health and safety information, call 1-800-364-3577 or (651) 737-6501.			
For Additional Information	To request additional product information or to arrange for sales assistance, call toll free 1-800-362-3550 or visit www.3M.com/adhesives. Address correspondence to: 3M Engineered Adhesives Division, 3M Center, Building 220-7E-01, St. Paul, MN 55144-1000. Our fax number is 651-733-9175. In Canada, phone: 1-800-364-3577. In Puerto Rico, phone: 1-787-750-3000. In Mexico, phone: 52-70-04-00.			
Important Notice	3M MAKES NO WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of application. Please remember that many factors can affect the use and performance of a 3M product in a particular application. The materials to be bonded with the product, the surface preparation of those materials, the product selected for use, the conditions in which the product is used, and the time and environmental conditions in which the product is expected to perform are among the many factors that can affect the use and performance of a 3M product. Given the variety of factors that can affect the use and performance of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method of application.			
Limitation of Remedies and Liability	If the 3M product is proved to be defective, THE EXCLUSIVE REMEDY, AT 3M'S OPTION, SHALL BE TO REFUND THE PURCHASE PRICE OF OR TO REPAIR OR REPLACE THE DEFECTIVE 3M PRODUCT. 3M shall not otherwise be liable for loss or damages, whether direct, indirect, special, incidental, or consequential, regardless of the legal theory asserted, including, but not limited to, contract, negligence, warranty, or strict liability.			
	This Engineered Adhesives Division product was manufactured under a 3M quality system registered to ISO 9002 standards.			



**Engineered Adhesives Division** 3M Center, Building 220-7E-01 St. Paul, MN 55144-1000

