



REVISIONS

DOC. NO. SPC-F004 * Effective: 7/8/02 * DCP No: 1388

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1754	A	Released	JWM	8/8/05	JN	2/18/08	JN	2/18/08



OUTPUT	Voltage	18V
	Current	20A
CONSTANT VOLTAGE OPERATION	Regulation	Line regulation <5mV Load regulation <5mV
	Ripple & Noise	<5mVrms, 100mVp-p 20Hz ~ 20MHz
	Recovery Time	<500 μS (50% Load change, Minimum load 0.5A)
	Temp. Coefficient	<100ppm / °C
	Output Range	0 to rating voltage continuously adjustable
	CONSTANT CURRENT OPERATION	Regulation
Ripple Current		<10mArms (SPS-1820)
Output Range		0 to rating current continuously adjustable (HI/LO range switchable)
METER	Digital	3 1/2 digits, 0.39" LED display Accuracy ±(0.5% of rdg + 2digits)
INSULATION	Chassis and Terminal	20MΩ or above (DC 500V)
	Chassis and AC Cord	30MΩ or above (DC 500V)
POWER SOURCE	AC 115V/ 230V ± 15 %, 50/60Hz	
ACCESSORIES	Instruction manual x 1 , Power cord x 1, Test lead (3A) x 1	
DIMENSIONS & WEIGHT	128(W) x 145(H) x 285(D) mm, Approx. 3.2kg	

SPC-F004.DWG

TOLERANCES: UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.	DRAWN BY:	DATE:	DRAWING TITLE:			
	Jeff McVicker	8/8/05	Switching DC Power Supply			
	CHECKED BY:	DATE:	SIZE	DWG. NO.	ELECTRONIC FILE	REV
	Jason Nash	2/18/08	A	72-7690	96H1237.dwg	A
APPROVED BY:	DATE:	SCALE:		U.O.M.:		SHEET:
Jason Nash	2/18/08	NTS		Millimeters		1 OF 1

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY. DISCLAIMER: ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.