


Features

- Size: 11.8 mm diameter, 17.5 mm length
- High power rating
- High voltage range
- RoHS compliant*
-  UL Recognized

Applications

- Industrial equipment/electronics
- Telecommunications electronics

2097 Series High-Voltage 2-Electrode Gas Discharge Tube

Characteristics

Test Methods per ITU-T (CCITT) K.12 and IEC 61643-311.

Characteristic	Model No.					
	2097-100	2097-120	2097-140	2097-160	2097-200	2097-220
DC Sparkover $\pm 20\%$ @ 100 V/s	1000 V	1200 V	1400 V	1600 V	2000 V	2200 V
Impulse Sparkover						
100 V/ μ s	< 1500 V	< 1800 V	< 2000 V	< 2300 V	< 2600 V	< 2700 V
1000 V/ μ s	< 1700 V	< 2000 V	< 2200 V	< 2500 V	< 2700 V	< 2800 V

Insulation Resistance (IR) ¹	500/1000 Vdc.....	> 10 G Ω
Glow Voltage	10 mA.....	~ 60 V
Arc Voltage	1 A.....	~ 15 V
Glow-Arc Transition Current		< 1 A
Capacitance.....	1 MHz	< 1.0 pF
Impulse Discharge Current.....	25,000 A, 8/20 μ s.....	1 operation
	20,000 A, 8/20 μ s.....	5 operations
Alternating Discharge Current	20 Arms, 50 Hz, 1 second.....	1 operation min.
	120 Arms, 50 Hz, 9 cycles	1 operation min.
Impulse Life	500 A, 10/1000 μ s.....	> 400 operations
Operating Temperature.....		-30 to +85 °C
Storage Temperature.....		-40 to +115 °C
Climatic Category (IEC 60068-1).....		40 / 90 / 21

Notes:

- ¹ Insulation Resistance measured at 1000 V for GDTs with >2000 V DCBD.
- UL Recognized component: UL File E135337.
- At delivery AQL 0.65 Level II, DIN ISO 2859.

BOURNS®

Asia-Pacific: Tel: +886-2 2562-4117 • Fax: +886-2 2562-4116

Europe: Tel: +41-41 768 5555 • Fax: +41-41 768 5510


The Americas: Tel: +1-951 781-5500 • Fax: +1-951 781-5700

www.bourns.com

2097 Series High-Voltage 2-Electrode Gas Discharge Tube

BOURNS®

Product Dimensions



Packaging Specifications

Model 2097 ships standard bulk, 35 pcs. per tray; 3 trays per box (105 units).

How to Order

