


PicoScope® 3425

DIFFERENTIAL PC OSCILLOSCOPE

For high-accuracy floating measurements



4 channels
12-bit precision
5 MHz bandwidth
20 MS/s sampling
Spectrum analyzer

Advanced digital triggering 400 V differential and common-mode range

USB 2.0 Hi-Speed






Supplied with a full SDK including example programs • Software compatible with Windows XP, Windows Vista and Windows 7 • Free technical support

PicoScope 3425 4-Channel Differential Oscilloscope - Specifications

Channels	4	
Bandwidth (–3 dB)	5 MHz (3 MHz on 100 mV range)	
Resolution	12 bits (16 bits in enhanced resolution mode)	
Maximum sampling rate Single channel Two channels Three or four channels	20 MS/s 10 MS/s 5 MS/s	
Buffer memory One channel enabled	512 k samples per channel	
Two channels enabled Three or four channels enabled	256 k samples per channel 128 k samples per channel	
Input type	Differential voltage Selectable AC or DC coupling Touch-proof BNC connectors and 4 mm GND sockets	
Input impedance	12.4 M Ω (on 100 mV to 5 V ranges) 10.1 M Ω (on 10 V to 400 V ranges)	
Input capacitance	12 pF	
Common-mode voltage range to ensure measurement accuracy	30 V (on 100 mV to 5 V ranges) 400 V (on 10 V to 400 V ranges)	
Maximum safe voltages Differential Any input above scope GND	400 V 400 V (600 V transient)	
Measurement category rating	CATI	
Voltage ranges	±100 mV to ±400 V in 12 ranges	
Accuracy Voltage Time	± 1% 50 ppm	
Linearity	12 bits	
Noise	< 10 LSB	
Operating environment		
Temperature range Humidity range	0 °C to 40 °C (20 °C to 30 °C for quoted accuracy) Minimum 5% RH non-condensing Maximum 80% RH non-condensing, decreasing linearly to 50% at 40 °C	
Storage environment Temperature range	-20 °C to 60 °C	
Humidity range	5% to 90% RH non-condensing	
Other environmental conditions	Dry environments, Altitude up to 2000 m, No pollution, or only dry, non-conductive pollution	
PC connection	USB 2.0 Compatible with USB 1.1	
Power supply	From USB port 4.6 V to 5.25 V DC @ approx. 500 mA No external power supply required	
Dimensions	255 mm \times 170 mm \times 40 mm (approximately 10 in \times 6.7 in \times 1.6 in)	
Weight	920 g (approximately 2 lb)	

PicoScope 3425 4-Channel Differential Oscilloscope



The 3425 kit is packaged in a tough carry case and includes all the accessories you need:

- Four screened BNC to 4 mm plug leads
- 4 current clamp adaptors
- 2 test probes
- 8 large crocodile clips
- USB cable
- Software and Reference CD
- Ouick Start Guide

The PicoScope 3425 has powerful display and analysis capabilities:

- Multiple scope and spectrum views
- Automatic measurements
- Data export in text, binary and graphical formats
- Waveform buffer for storing multiple events
- Mask limit testing
- Serial data decoding
- Spectrum analysis

Most oscilloscopes can only measure signals referenced to ground and have what are known as "single-ended inputs". The PicoScope 3425 has four fully differential inputs that allow you to measure signals that are not referenced to ground. With a maximum common mode and differential range of 400 V, the PicoScope 3425 is capable of measuring both high voltage and low level signals. Typical high voltage applications include capturing waveforms from switch mode power supplies, telephone cables, motor inverters and hybrid vehicles. The high impedance differential inputs also allow measurements on sensitive amplifiers and from bridge type sensors for pressure, load and strain. They also allow you to measure floating voltages, and signals where common-mode noise is present, with ease and without the need for expensive differential preamplifiers or probes.

The PicoScope 3425 USB Oscilloscope comes in a tough carry case complete with all the probes, leads, clips and adaptors you need to start taking differential measurements. Just install the user-friendly software, connect the oscilloscope to a USB port on your Windows PC and you're ready to go. No complicated setup procedures. No effort required.

Its small, lightweight design means the PicoScope 3425 doesn't need to be confined to your lab or workbench. It is the perfect portable differential oscilloscope, while the anti-slip case means that your scope can be used either horizontally or vertically – ideal when space is at a premium. The included accessories and easy-to-use software allow you to get the maximum from your PicoScope.

Ordering information

ORDER CODE	DESCRIPTION	£	US\$*	€*
PP454	PicoScope 3425 Differential PC Oscilloscope Kit	975	1609	1180



Pico Technology, James House, Colmworth Business Park, St. Neots, Cambridgeshire, PE19 8YP, United Kingdom

+44 (0) 1480 396 395

44 +44 (0) 1480 396 296

⊠ sales@picotech.com

*US\$ and € prices are correct at the time of publication. Please contact Pico Technology for the latest prices before ordering. Errors and omissions excepted. Copyright © 2012 Pico Technology Ltd. All rights reserved.