

List Price \$435.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.****Technical Characteristics**

Actuator Type	Diaphragm (Low Pressure)
External Range Adjustment	None
Switch Type	Single Stage
Enclosure Rating	NEMA 4/4X/13
Differential Type	Fixed
Differential	6.0 PSIG (+/- 0.8)
Pressure Range on Decreasing	3.0 to 150 PSIG
Fluid Connection	1/4" 18 NPTF (internal)
Range Scale Window	None
Flange Material	Zinc Plated Steel
Pilot Light	LED (24 Vdc) - Red Lens
Diaphragm Material	Nitrile (Buna-N)
Contact Arrangement	SPDT (isolated)
Enclosure Type	Water tight, Dust tight, Oil tight and Corrosion Resistant (Indoor/Outdoor)
Maximum Allowable Pressure	475 PSIG
Fluid Characteristics	Hydraulic Oils, Air, Non-Corrosive Liquids and Non-Corrosive Gas
Locking	None
Electrical Connection	1/2" 14 NPT
Maximum Voltage Rating	600V
Continuous Current Rating	10A
Shock Resistance	50 g
Media Temperature Range	-40° to 250°F (-40° to 120°C)
Ambient Temperature Range	-10° to 185°F (-23° to 85°C)
Operating Cycles/Min	120 operating cycles per minute (max)
Drift	+/- 1% of the adjustable range over 1 million operations
Repeat Accuracy	+/- 0.1 to 1%
RoHS	No
Conformity to Standards	UL 508, CSA 3211-03, IEC 60957.5.1, CE
Certifications	UL Listed and CSA Certified as industrial control equipment

**Shipping and Ordering**

Category	21522 - Pressure Switches, Machine Tool & Industrial, Control Circuit Rated, Type G,
Discount Schedule	DS1
GTIN	00785901048404
Package Quantity	1
Weight	2.89 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

Generated: 08/06/2012 07:25:50

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/06/2012 07:25:50