

Neon Lamp




Feature:

- Neon lamp without series resistor

Specifications:

Lamp Base Type	: Wire Ended
Bulb Size	: 6mm / T-2
Lead Length	: 30mm



Dimensions : Millimetres

Part Number Table

Description	Maximum Strike Voltage		Nominal Current (mA)	Recommended Series Resistor		Brightness	Body Length	Lead Length	Wire Ended Types	Part Number
	AC	DC		110V AC	240V AC					
Neon Lamp, Wire Ended, T2	65	90	0.55	100K 1/4W	330K 1/4W	Standard	30	6mm, T2	MC08320000	
	95	135	4.5	12K 1/4W	39K 1/4W	High			MC08310015	
	65	90	0.8	68K 1/4W	220K 1/4W	Green	12.5		MC08130000	
			1.2	56K 1/4W	180K 1/4W		16		MC08330000	

Dimensions : Millimetres

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.