



Blue Shower II Cleaner/Degreaser

1667

Maintenance cleaners clean oil and contaminants off of metal parts, printed circuit boards, barcode instruments, switch boxes, gear boxes, and engines.

Techspray has produced Blue Shower maintenance cleaners for over 30 years, making Blue Shower a staple in maintenance departments all over the world!

Contact cleaners remove oxidation, oil, and other contaminants off of contacts, metal switches, motors, relays, generators, edge connectors, buss bars, circuit breakers, scales and sensors. Contact cleaners are used in electrical maintenance and to repair faulty contacts by removing insulative contamination.

Techspray offers a variety of solvents and waterbased cleaners that allow customers to match the right products with their cleaning needs. Choosing a strong, high quality cleaner saves time and money. Grease and oil flow right off, reducing the time and materials needed to scrub off stubborn soils.



Powerful AK225-based solvent cleaner

Non-flammable, high precision cleaner that is ideally suited for sensitive plastics often used in seals and outer casings.

- Ideal for sensitive plastics
- Non-flammable
- High Precision — Residue Free
- Safe on electronics
- Rapid evaporation
- Zero residue
- Safe on most plastics
- EPA SNAP approved
- Low VOC

Product Packaging

1667-8S
Blue Shower II Cleaner/Degreaser
8 oz
12 units/case



1667-18S
Blue Shower II Cleaner/Degreaser
18 oz
12 units/case



1667-5G
Blue Shower II Cleaner/Degreaser
50 lbs
1 units/case



Instructions

Disconnect equipment from power source. Make sure opening of sprayhead is pointing toward surface to be cleaned. Hold can 6-8 inches away. Direct spray to saturate soiled surface. A TechBrush® (2000 Series) may be utilized to help in the removal of heavy soils. When used as a general cleaner, start at top of area to be cleaned using a sweeping motion and spray the area, slowly working toward the bottom. To clean in hard to reach areas, insert extension tube in sprayhead to direct spray. Allow components to dry completely before applying current.

Chemical & Physical Properties

Appearance	Clear, colorless liquid
------------	-------------------------





Odor	Faint ethereal odor
Flash Point	none
VOC (EPA)	9% (aerosol)
VOC (CARB)	75% (aerosol)
Boiling Point	54°C (129°F)
Density	

Chemical Composition

CHEMICAL NAME	CAS #
3,3-Dichloro-1,1,1,2,2-pentafluoropropane (HCFC-225ca)	422-56-0
1,3-Dichloro-1,1,2,2,3-pentafluoropropane (HCFC-225cb)	507-55-1
Ethanol	64-17-5
Nitromethane	75-52-5
1,1,1,2-Tetrafluoroethane (aerosol)	811-97-2
Carbon dioxide (aerosol)	124-38-9

Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email tsales@techspray.com or visit our web site at: www.techspray.com.

North America

Techspray
P.O. Box 949
Amarillo, TX 79105
800-858-4043
email: tsales@techspray.com

Europe

ITW Contamination Control BV
Saffierlaan 5
2132 VZ Hoofddorp
The Netherlands
+31 88 1307 400
email: info@itw-cc.com

Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

