



**Anti-Static Freezer**

1747

Rapidly evaporating liquid that super-chills isolated areas. Used as a troubleshooting aid for intermittently faulting capacitors, resistors, semiconductors, and other defective components. It also increases visibility of cold solder joints, cracks in printed circuit boards and oxidized junctions.



**Diagnostic freeze spray for static sensitive assemblies**

Rapidly evaporating liquid that super-chills isolated areas. Used as a troubleshooting aid for intermittently faulting capacitors, resistors, semiconductors, and other defective components. It also increases visibility of cold solder joints, cracks in printed circuit boards and oxidized junctions. Contains additive that avoids static build-up, critical when working with ESD-sensitive components.

- Avoids static build-up
- Non-flammable
- Non-ozone depleting
- Moisture free
- Zero residue
- Safe on plastics
- Chills down to -40°F (-40°C)

**Product Packaging**

1747-10S  
Anti-Static Freezer  
10 oz  
12 units/case



**Instructions**

Can must be held in an upright position when spraying. Do not tilt can more than 40 degrees during spraying operation or shake during use. Before use, press actuator to clear valve of any liquid product. Use short burst to prevent cooling of can. Note: Do not use on photographic negatives without first clearing valve.

**Chemical & Physical Properties**

Appearance	Colorless gas
Odor	Faint ethereal odor
Flash Point	none
VOC (EPA)	0%
VOC (CARB)	0%
Boiling Point	-26.2°C (-15.1°F)
Density	



# TECHSPRAY®

## Technical Data Sheet

### Chemical Composition

CHEMICAL NAME	CAS #
1,1,1,2-Tetrafluoroethane (aerosol)	811-97-2
Methanol	67-56-1

### Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

### Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

#### North America

Techspray  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
email: [tsales@techspray.com](mailto:tsales@techspray.com)

#### Europe

ITW Contamination Control BV  
Saffierlaan 5  
2132 VZ Hoofddorp  
The Netherlands  
+31 88 1307 400  
email: [info@itw-cc.com](mailto:info@itw-cc.com)

#### Countries Outside US

Call to locate a distributor in your country

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.