






Platinum Temperature Sensor with metallised backside and inversed leads

P0K1.232.3FW.A.010.M.U






Product



Features

- Fast response time
- Small dimensions
- Excellent long-term stability
- Vibration and temperature shock resistant
- Low self-heating
- Simple interchangeability
- Optimal price/performance ratio



Technical Data

Nominal resistance: 100 Ohm at 0°C
Temperature range: -200°C - +300°C
Characteristic curve: 3850 ppm/K

Long term stability: < less than 0.04% @ 1000 hrs. max. temperature Response time (t 63%): Water (v=0.4 m/s) 0.12 s

Air (v=1m/s) 3.6 s

Self heating: Water (v=0 m/s) 40 mW/K

Air (v=0 m/s) 4 mW/K

Dimensions (LxWxH): 2.3 x 2 x 1.3 mm (LxWxH)

Tolerance: DIN EN 60751 F 0,15 (class A)

Contacts: Nickel flat wire gold coated, 0.2 x 0.35 mm (HxW), 10 mm long

Special: Contacts inversed; metallised backside

Recommended applied current: 1mA (100 Ohm)



