



## USB Rover 1650/2650



- ❖ Extends the range of USB up to 50 meters using Category 5 cable.
- ❖ Requires no external power adapter.
- ❖ Transmits power and data over the same Category 5 cable.
- ❖ Contains internal USB hub.
- ❖ Provides support for any full-speed (12 Mb/s) or low-speed (1.5 Mb/s) USB device.
- ❖ Ideal for use with USB 1.1 keyboards and mice.
- ❖ System includes local and remote units, USB cable and user guide.

### Icron Technologies Corporation

4664 Lougheed Highway  
Suite 275  
Burnaby, BC  
V5C 5T5  
Canada

tel: 604-638-3920

fax: 604-638-3930

email: [sales@icron.com](mailto:sales@icron.com)

[www.icron.com](http://www.icron.com)



©2003

Icron Technologies Corporation  
US Patent 6,381,666 B1  
90-00101-A02



## ORDERING INFORMATION

USB Rover products are supplied complete with a Local Extender (LEX) unit, a Remote Extender (REX) unit, a USB cable, mounting hardware and user guide.

Name	Part Number	Description
USB Rover 1650	00-00084	1-port extender
USB Rover 2650	00-00085	2-port extender

## SPECIFICATIONS

Range (over Category 5 UTP cable)	50 meters (165 ft)
# USB device ports (at REX)	Rover 1650: 1 Rover 2650: 2
USB device support (connected directly to REX)	Any full-speed (12 Mb/s) or low-speed (1.5 Mb/s) device
USB hub support	Up to 3 hubs can be connected in series with the Rover 1650/2650. Each hub reduces the maximum range by 10 meters.
Maximum power available to USB at REX	300 mA when LEX is supplied with 500 mA; 600 mA when LEX is supplied with 1000 mA
USB cable	2 meters (6.6 ft)
LEX connector (upstream)	1 x USB Type B
LEX connector (downstream)	1 x RJ-45
REX connector (upstream)	1 x RJ-45
REX connector (downstream)	Rover 1650: 1 x USB Type A Rover 2650: 2 x USB Type A
LEX dimensions	100 mm x 70 mm x 30 mm (4.0" x 2.8" x 1.2")
LEX weight	0.1 kg (0.2 lb)
REX dimensions	100 mm x 70 mm x 30 mm (4.0" x 2.8" x 1.2")
REX weight	0.1 kg (0.2 lb)
Total system shipping weight	0.4 kg (0.8 lb)
Temperature range	4°C to 40°C
Regulatory testing	FCC, CE Class B