

Linemaster Switch Corporation

29 Plaine Hill Road POB 238

Woodstock, CT 06281-0238 USA

Toll Free: (800) 974-3668 (US Only) Telephone: (860) 974-1000 Fax: (860) 974-0691

E-Mail: service_266@linemaster.com Web site: www.linemaster.com

Item # TWIN 635-S, Clipper Foot Switch

TWIN with DIVIDER BAR

Clipper Foot Switch

The rugged, long life clipper switch models have proved themselves in the field over many years of usage. All maintained models offer "Push on Push Off" action through a molded nylon actuating cam mechanism that insures long trouble-free performance. The wide treadle models offer a large seven inch target for the operator's foot. Cast iron housing. Nonskid base pad. Complete with adjustable strain relief connector. Black finish.

SPECIFICATIONS

Style/Series	Regular
Description	Momentary
Circuit	Each Side DPDT
Form	C
Electrical Rating	15 A 125 VAC 10 A 250 VAC 1/2 H.P. 125-250 VAC
Standard	EN 60529 Degree of Protection IP20
Size	8 3/8 x 4 1/2 x 1 1/2 Inch
Weight Approx.	5 lbs