


Inductive Rectangular Sensors



Housing Style - Rectangular	Part Number	ID Number	Features	Embeddable	Sensing Range (mm)	Output
10 mm - Embeddable/Nonembeddable, Potted-In Cable 	Bi 2-Q10S-AN6X	S1619310		•	2	3-Wire DC NPN
	Ni 5U-Q10S-AN6X	S1609365	<i>uprox+</i>		5	
	Bi 2-Q10S-AP6X	S1609360		•	2	3-Wire DC PNP
	Ni 5U-Q10S-AP6X	S1609364	<i>uprox+</i>			
	Bi 2-Q10S-VN6X	S1609341	Comp. Outputs	•	2	4-Wire DC NPN
	Bi 2-Q10S-VP6X	S1609340	Comp. Outputs	•	2	4-Wire DC PNP
	Bi 2-Q10S-AZ31X	S1309100		•	2	2-Wire AC/DC
	Bi 2-Q10S-Y0X	S4012130		•	2	2-Wire NAMUR
Bi 2-Q10S-Y1X	S4012130		•	2		
11 mm - Embeddable/Nonembeddable, Potted-In Cable 	Bi 2-Q11S-AD4X	M4405040		•	2	2-Wire DC
	Ni 4-Q11S-AZ31X	M4348000			4	2-Wire AC/DC

For detailed sensor specifications see Section M.
Normally Closed versions available upon request, consult factory.



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Face	Power LED	Output LED	Cable Length /Jacket	Wiring Diagram #	Wiring Diagrams
10-30 VDC	2000	≤150	-25 to +70	IP 67	PP-GF20	N/A	YE	2M/PUR	1	1	Diagram 1
	1000	≤150	-30 to +85	IP 68	PP-GF20	N/A	YE	2M/PUR			
10-30 VDC	2000	≤150	-25 to +70	IP 67	PP-GF20	N/A	YE	2M/PUR	2	2	Diagram 2
	1000	≤150	-30 to +85	IP 68	PP-GF20	N/A	YE	2M/PUR			
10-30 VDC	2000	≤150	-25 to +70	IP 67	PP-GF20	N/A	YE	2M/PUR	3	3	Diagram 3
10-30 VDC	2000	≤150	-25 to +70	IP 67	PP-GF20	N/A	YE	2M/PUR	4	4	
20-250 VAC 10-300 VDC	60	≤100	-25 to +70	IP 67	PP-GF20	N/A	RD	2M/PUR	5	5	Diagram 4
5-30 VDC	1000	Remote	-25 to +70	IP 67	PP-GF20	N/A	YE	2M/PVC	6	6	Diagram 5
	1000	Remote	-25 to +70	IP 67	PP-GF20	N/A	YE	2M/PVC			
10-65 VDC	2000	≤100	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	7	Diagram 6
20-250 VAC 10-300 VDC	20	≤100	-25 to +70	IP 67	PBT	PBT	N/A	YE	2M/PVC	5	Diagram 7

Rectangular

For material descriptions see page M36.