

# Inductive Sensors



Housing Style	Part Number	ID Number	Features	Sensing Range (mm)	Output
<b>30 mm - Embeddable, eurofast<sup>+</sup> Connection</b> 	Bi 10-M30-AD4X-H1141	T4417500		10	2-Wire DC
	Bi 12-M30-AD4X-H1141	T4417041	<b>Extended Range</b>	12	
	Bi 10U-M30-AD4X-H1144	M4405072	<b>uproxx+</b>	10	
	Bi 10-M30-AN6X-H1141	T4617600		10	3-Wire DC NPN
	Bi 10U-EM30-AN6X-H1141	M1636350	<b>Uprox</b>	10	
	Bi 10U-EM30H-AN6X2-H1141	M1636407	<b>Uprox, Stoneface</b>	10	
	Bi 10U-EM30H-AN6X2-H1141/S1589	M1636490	<b>weldguard<sup>+</sup>, Uprox</b>	10	
	Bi 10U-M30-AN6X-H1141	M1636150	<b>Uprox</b>	10	
	Bi 15-M30-AN6X-H1141	T4618600	<b>Extended Range</b>	15	
	Bi 15-EM30H-AN6X-H1141	T4618692	<b>Stoneface, Ext. Range</b>	15	
	Bi 15U-M30-AN6X-H1141	M1636736	<b>Uprox+</b>	15	
	Bi 10-M30-AP6X-H1141	T4617500		10	3-Wire DC PNP
	Bi 10U-EM30-AP6X-H1141	M1636340	<b>Uprox</b>	10	
	Bi 10U-EM30H-AP6X2-H1141/S1589	M1636491	<b>weldguard, Uprox</b>	10	
	Bi 10U-M30-AP6X-H1141	M1636140	<b>Uprox</b>	10	
	Bi 10U-M30-AP6X2-H1141	M1636145	<b>Uprox</b>	10	
	Bi 15-M30-AP6X-H1141	T4618500	<b>Extended Range</b>	15	
	Bi 15-EM30H-AP6X-H1141	T4618592	<b>Stoneface, Ext. Range</b>	15	
	Bi 15-EM30H-AP6X-H1141/S1589	T4618593	<b>weldguard</b>	15	
	Bi 15U-EM30-AP6X-H1141	M1636733	<b>uproxx+</b>	15	
Bi 15U-M30-AP6X-H1141	M1636732	<b>Stainless steel uproxx+</b>	15		
<b>30 mm - Embeddable, eurofast<sup>+</sup> Connection</b> 	Bi 15-EM30H-AP6X-H1141/S1610	T4618589	<b>Weld/armorguard</b>	15	3-Wire DC PNP
<b>30 mm - Embeddable, eurofast<sup>+</sup> Connection</b> 	Bi 10-M30-VN4X-H1141	T1571600	<b>Comp. Outputs</b>	10	4-Wire DC NPN
	Bi 10U-M30-VN4X-H1141	M1582352	<b>Uprox, Comp. Outputs</b>	10	
	Bi 15-M30-VN4X-H1141	T4570711	<b>Comp. Outputs</b>	15	
	Bi 10-M30-VP4X-H1141	T1561600	<b>Comp. Outputs</b>	10	4-Wire DC PNP
	Bi 10U-M30-VP4X-H1141	M1582253	<b>Uprox, Comp. Outputs</b>	10	
	Bi 15-M30-VP4X-H1141	T4570710	<b>Comp. Outputs</b>	15	
	Bi 10-M30-Y1X-H1141	M4020200			10

For detailed sensor specifications see Section M.  
 Normally Closed versions available upon request, consult factory.



Voltage	Switching Freq. (Hz)	Operating Current (mA)	Operating Temp. (°C)	Protection	Housing	Face	Power LED	Output LED	Mating Cordset	Wiring Diagram #	Wiring Diagrams
10-65 VDC	500	≤100	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.2T-*	1	<b>Diagram 1</b> 
	500	≤100	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.2T-*	1	
	1000	≤100	-30 to +85	IP 68	CPB	LCP	N/A	YE	RK 4T-*	2	
10-30 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	3	<b>Diagram 2</b>  <b>Diagram 3</b> 
	2000	≤200	-30 to +85	IP 68	SS	PA 12	N/A	YE	RKV 4T-*	3	
	2000	≤200	-30 to +85	IP 68	SS	SF	GN	YE	RKV 4T-*	3	
	2000	≤200	-30 to +85	IP 68	SS	WG	GN	YE	RKC 4T-*/S1587	3	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	3	
	300	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	3	
	300	≤200	-25 to +70	IP 67	SS	SF	N/A	YE	RKC 4T-*/S1587	3	
750	≤200	-30 to +85	IP 68	CPB	LCP	N/A	YE	RK 4T-*	3		
10-30 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	4	<b>Diagram 4</b>  <b>Diagram 5</b> 
	2000	≤200	-30 to +85	IP 68	SS	PA 12	N/A	YE	RKV 4T-*	4	
	2000	≤200	-30 to +85	IP 68	SS	WG	GN	YE	RKC 4T-*/S1587	4	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	4	
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	GN	YE	RK 4T-*	4	
	300	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4T-*	4	
	300	≤200	-25 to +70	IP 67	SS	SF	N/A	YE	RKV 4T-*	4	
	300	≤200	-25 to +70	IP 67	SS	WG	N/A	YE	RKC 4T-*/S1587	4	
	750	≤200	-30 to +85	IP 68	SS	LCP	N/A	YE	RK 4T-*	4	
10-30 VDC	300	≤200	-25 to +70	IP 67	AG	WG	N/A	YE	RKC 4T-*/S1587	4	<b>Diagram 6</b> 
	750	≤200	-30 to +85	IP 68	CPB	LCP	N/A	YE	RK 4T-*	4	<b>Diagram 7</b> 
10-65 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	5	<b>Diagram 7</b> 
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	5	
	500	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	5	
10-65 VDC	500	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	6	<b>Diagram 7</b> 
	2000	≤200	-30 to +85	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	6	
	300	≤200	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.4T-*	6	
5-30 VDC	2000	Remote	-25 to +70	IP 67	CPB	PA 12	N/A	YE	RK 4.21T-*	7	<b>Diagram 7</b> 

Barrels

\* Length in meters.

For material descriptions see page M36.