

Tamper-proof Dual Thermostat (Pre-set) FTD 011 Series



NO and NC in one casing

Default temperature settings

High switching accuracy

Clip fixing

Two thermostats in one casing:

Tamper-proof (Pre-set) Thermostat/Contact breaker (NC) for regulating heaters or for switching signal devices when temperature has fallen below the minimum value. The contact opens when temperature is rising.


Tamper-proof (Pre-set) Thermostat/Contact maker (NO) for regulating filter fans, heat exchangers or for switching signal devices when temperature limit has been exceeded. The contact closes when temperature is rising.


Heaters and cooling equipment can be switched independently from each other with a temperature offset as opposed to the usual change-over contacts.



Technical Data

| Sensor element | thermostatic bimetal | | |
|--------------------------------|---|--|--|
| Contact type | snap-action contact | | |
| Service life | > 100,000 cycles | | |
| Max. switching capacity | 250VAC, 5 (1.6) A | | |
| | 120VAC, 10 (2) A | | |
| | 30WDC | | |
| Max. inrush current | 16AAC for 10 sec. | | |
| Connection | 4-pole terminal for 2.5mm², torque 0.8Nm max. | | |
| Mounting | clip for 35mm DIN rail, EN 60715 | | |
| Casing | plastic according to UL94 V-0, light grey | | |
| Dimensions | 47 x 63 x 33mm | | |
| Weight | approx. 40g | | |
| Fitting position | variable | | |
| Operating / Storage temperaure | -40 to +80°C (-40 to +176°F) / -45 to +80°C (-49 to +176°F) | | |
| Operating / Storage humidity | max. 90% RH (non-condensing) | | |
| Protection type | IP20 | | |
| Approvals | VDE + UL File No. E164102 | | |





Example of connection

| Art. No. | Contact breaker (NC) | | Contact maker (NO) | |
|------------|---------------------------------|---|---------------------------------|---------------------------------|
| | Switch-off temperature | Switch-on temperature | Switch-on temperature | Switch-off temperature |
| 01163.0-00 | +15°C / +59°F (± 5K tolerance) | +5°C / +41°F (± 5K tolerance) | +50°C / +122°F (± 6K tolerance) | +40°C / +104°F (± 7K tolerance) |
| 01163.0-01 | +25°C / +77°F (± 5K tolerance) | +15°C / +59°F (± 5K tolerance) | +60°C / +140°F (± 6K tolerance) | +50°C / +122°F (± 7K tolerance) |
| 01163.0-02 | +15°C / +59°F (± 5K tolerance) | +5°C / +41°F (± 5K tolerance) | +35°C / +95°F (± 6K tolerance) | +25°C / +77°F (± 7K tolerance) |
| 01163.0-03 | +25°C / +77°F (± 5K tolerance) | +15°C / +59°F (± 5K tolerance) | +50°C / +122°F (± 6K tolerance) | +40°C / +104°F (± 7K tolerance) |
| Art. No. | Contact maker (NO) | | Contact maker (NO) | |
| | Switch-on temperature | Switch-off temperature | Switch-on temperature | Switch-off temperature |
| 01164.0-00 | +50°C / +122°F (± 6K tolerance) | $+40^{\circ}$ C / $+104^{\circ}$ F (± 7K tolerance) | +60°C / +140°F (± 6K tolerance) | +50°C / +122°F (± 7K tolerance) |