



- **Adjustable temperature**
- **High switching capacity**
- **Small hysteresis**
- **Terminals easily accessible**
- **Clip fixing**
- **Change-over contact**




The mechanical thermostat is used for controlling heating and cooling equipment, filter fans or signal devices. The thermostat registers the surrounding air and can switch both inductive and resistive loads via snap-action contact. Due to the integrated thermal feedback the switch temperature difference could be reduced. **Functionality:** The temperature setting on the scale equals to the upper switch point, which means that the NC contact opens. The temperature setting minus switch temperature difference (and tolerances) equals to the lower switch point, which means that the NC contact closes.



Technical Data

Switch temperature difference	5K (-3/+2K tolerance)*
Sensor element	thermostatic bimetal
Contact type	change-over snap-action contact
Service life	> 100,000 cycles
Min. switching capacity	10mA
Max. switching capacity, NC	250VAC, 10 (4) A 120VAC, 10 (4) A 30WDC
Max. switching capacity, NO	250VAC, 5 (2) A 120VAC, 5 (2) A 30WDC
Max. inrush current	16AAC for 10 sec.
Connection	4-pole terminal, clamping torque 0.5Nm max.: rigid wire 2.5mm ² stranded wire (with wire end ferrule) 1.5mm ²
Mounting	clip for 35mm DIN rail, EN 60715
Casing	plastic according to UL94 V-0, light grey
Dimensions	67 x 50 x 38mm
Weight	approx. 0.1kg
Fitting position	variable
Operating / Storage temperature	-45 to +65°C (-49 to +149°F)
Operating / Storage humidity	max. 90% RH (non-condensing)
Protection type	IP20
Approvals	UL File No. E164102

*If the Normally Closed contact is used, the switch temperature difference could be reduced by connecting terminal "N" (RF heating resistor). It causes the thermal feedback which is subject to surrounding conditions and thus has to be determined for each individual application.



Art. No.	Operating voltage	Setting range
01170.0-00	230VAC	+5 to +60°C
01170.0-01	230VAC	+40 to +140°F
01170.0-02	230VAC	-20 to +35°C
01170.9-00	120VAC	+40 to +140°F
01170.9-01	120VAC	+5 to +60°C