Product data sheet Characteristics

RE48AML12MW

time delay relay 2 functions - 0.02 s..300 h - 24..240 V AC - 2 OC



Main

- Tricking	
Range of product	Zelio Time
Product or component type	Electronic timing relay
Electrical connection	Plug-in sub-base 11 pin(s)
Discrete output type	Relay
Contacts type and composition	2 C/O timed contacts, AgNi (cadmium free)
Component name	RE48A
Time delay type	A B C Di
Time delay range	0.021.2 s 0.053 s 0.212 h 0.212 min 0.212 s 0.530 h 0.530 min 0.530 s 2120 h 2120 min 2120 s 5300 h 5300 min 5300 s
[Us] rated supply voltage	24240 V AC/DC 50/60 Hz
Voltage range	0.851.1 Us AC 0.91.1 Us DC
[In] rated current	5 A

Complementary

Product front plate size	48 x 48 mm
Control type	Selector switch on front panel
Housing material	Self-extinguishing
Repeat accuracy	+/- 0.2 % of the maximum setting value conforming to IEC 61812-1
Temperature drift	+/- 0.02 %/°C of the maximum setting value conforming to IEC 61812-1
Voltage drift	+/- 0.2 %/V of the maximum setting value 48240 V +/- 1 %/V of the maximum setting value 2448 V
Setting accuracy of time delay	+/- 5 % of full scale at 25 °C conforming to IEC 61812-1
Minimum pulse duration	20 ms
Reset time	>= 25 ms on de-energisation
Pick up duration	55 ms
On-load factor	100 %
Maximum power consumption	1.1 VA 24 V 4.8 VA 240 V
Maximum power consumption	0.5 W 24 V 1.7 W 240 V
Breaking capacity	1250 VA
Minimum switching current	100 mA
Maximum switching current	5 A
Maximum switching voltage	250 V AC/DC
Electrical durability	100000 cycles

Mechanical durability	30000000 cycles
Output voltage	240 V 5 A AC-12 30 V 2 A DC-13 240 V 1.5 A AC-15
Marking	CE
Surge withstand	1 kV (differential mode) conforming to IEC 61000-4-5 level 3 2 kV (common mode) conforming to IEC 61000-4-5 level 3
Mounting support	Base mounted: socket Panel mounted: system supplied with the product
Local signalling	1 LED yellow output relay state LED indicator green flashing: relay energised timing in progress LED indicator green on steady: relay energised, no timing in progress
Product weight	0.14 kg
Environment	
Humidity drift	+/- 0.05 %/%RH of the maximum setting value conforming to IEC 61812-1
Immunity to microbreaks	< 10 ms
Dielectric strength	1 kV 1 mA/1 minute conforming to IEC 61812-1
Protection against electric shocks	4 kV category 3 conforming to IEC 60664-1 4 kV category 3 conforming to IEC 61812-1
Standards	73/23/EEC 89/336/EEC 93/68/EEC EN 50081-1/2 EN 50082-1/2 IEC 60669-2-3 IEC 61812-1
Product certifications	CSA C-Tick CULus GL UL
Ambient air temperature for storage	-4070 °C
Ambient air temperature for operation	-2050 °C
IP degree of protection	IP40 (housing) conforming to IEC 60529 IP50 (front face) conforming to IEC 60529
Vibration resistance	0.35 mm (f = 1055 Hz) conforming to IEC 60068-2-6
Relative humidity	93 % without condensation conforming to IEC 60068-2-3
Resistance to electrostatic discharge	6 kV (in contact) conforming to EN/IEC 61000-4-2 level 3 8 kV (in air) conforming to EN/IEC 61000-4-2 level 3
Resistance to electromagnetic fields	10 V/m, 26 MHz to 1 GHz conforming to IEC 61000-4-3 level 3
Resistance to fast transients	2 kV, capacitive connecting clip conforming to EN/IEC 61000-4-4 level 4 4 kV, direct conforming to EN/IEC 61000-4-4 level 4
Immunity to radioelectric fields	10 V (0.1580 MHz) conforming to EN/IEC 61000-4-6 level 3
Immunity to voltage dips	30 %/10 ms conforming to EN/IEC 61000-4-11 60 %/100 ms conforming to EN/IEC 61000-4-11 95 %/5 s conforming to EN/IEC 61000-4-11
Disturbance radiated/conducted	Class B (0.1530 MHz) conforming to EN 55022 (EN 55011 group 1)
RoHS EUR status	Compliant



0622

RoHS EUR conformity date


Product data sheet Technical Description

RE48AML12MW

Function A: Delay on Energisation

Description

The timing period T begins on energisation. After timing, the output R closes.




T = t1 + t2 + t3

Function B: Timing on Impulse, One Shot

Description

After power-up, pulsing or maintaining control contact C starts the timing T. The output R closes for the duration of the timing period T then reverts to its initial state.




T = t1 + t2 + t3

Function C: Timing After of Control Contact

Description

After power-up and closing of the control contact, the output closes. When control contact re-opens, timing T starts. At the end of the timing period, the output reverts to their initial state.




T = t1 + t2 + t3

Function Di: Symmetrical Flashing, Start with Output in Operating Position

Description

Repetitive cycle with two timing periods T of equal duration, with output changing state at the end of each timing period T.



Legend

Relay de-energised
Relay energised

Output open
Output closed

C Control contact

G Gate

R Relay or solid state output

R1/ 2 timed outputs

R2

R2 The second output is instantaneous if the right position is selected inst.

T Timing period

Ta Adjustable On-delay


Tr Adjustable Off-delay


U Supply

Product data sheet Dimensions Drawings

RE48AML12MW

Width 48 mm






RE48AML12MW

Panel Cut-Out and Mounting


Panel Cut-Out



n Number of devices mounted side-by-side

Mounting

Cover positioning and mounting



- e Panel thickness
- 1 Protective cover
- 2 Panel mounting frame
- 3 Locating screw

Product data sheet Connections and Schema

RE48AML12MW

Wiring Diagram

