

**Cable glands
VG 21-MS54**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



An economical plastic cable gland, such as you often find in industrial applications. With their soft rubber seal, they offer a secure fit for the cable and a good IP protection degree (IP 54). In addition, the nickel-plated brass gives you good corrosion protection from external influences.

General ordering data

Order No.	0260900000
Type	VG 21-MS54
Version	Cable glands, Cable gland, Brass, nickel-plated, PG 21
GTIN (EAN)	4008190120528
Qty.	50 pc(s).

**Cable glands
VG 21-MS54**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	29.5 mm	Net weight	45.28 g
--------	---------	------------	---------

General information

AF size 1	28 mm	AF size 2	30 mm
Cable gland	PG	Clamping range, bolted connection , max.	17 mm
Clamping range, min. test adapter	15 mm	DIN	DIN 46320 / C4
External thread	PG 21	Length of thread	7 mm
Material	Brass, nickel-plated	Operating temperature range, max.	60 °C
Operating temperature range, min.	-20 °C	Protection degree with GWDR	IP 65
Seal insert	NBR	Torque for cap nut, max.	18.87 Nm
Torque for cap nut, min.	18.87 Nm	Torque for connecting adapter, max.	28.3 Nm
Torque for connecting adapter, min.	28.3 Nm		

Classifications

ETIM 2.0	EC000441	ETIM 3.0	EC000441
UNSPSC	30-21-18-01	eClass 4.1	27-14-12-09
eClass 5.1	27-14-91-09	eClass 6.0	27-14-91-11
eClass 7.0	27-14-91-11		

Approvals

Approvals

